

Enameled copper wire
CUL 100/0,75



Picture shows CUL 100/0,22

Advantages

Insulating varnish basis min. polyurethane, mod.

Grade 1, TJ min. 302 °F / 155 °C

Solderable

Applications

Enameled copper wire for the production of coils and windings and for general laboratory needs. Please consider the relevant standards.

Approvals



Enameled copper wire **CUL 100/0,75**

Type

CUL 100/0,75

Type

CUL 100/0,75



Electrical data



Mechanical data

Operating data

Current rating 1.55 A

Environment

Heat resistance 311 °F (CLF)

Insulating varnish min. Polyurethan, mod.

Tin-plate >662 °F

Measures and weights

Length m (min.) 20

Wire diameter 0.030 inch

Weight 0.22 lbs

Subject to change.