# Megger.

# DLRO10HD 10 Amp Digital Low Resistance



DESCRIPTION

Augmenting Megger's DLRO10 and 10X range the DLRO10HD combines ultimate simplicity of operation with a rugged IP65 case designed for stable ground and bench operation.

The unit is powered from either its rechargeable battery or line power making it suitable for continuous testing in production line/repetitive use environments.

Rotary switch controls are simple and easy to operate in all weather conditions and with gloved hands. A large, clear, backlit LCD display is easy to read from a distance. The DLRO10HD provides significantly enhanced compliance and is capable of delivering 10 A into measurements up to 250 m $\Omega$  and 1 A into measurements up to 2.5  $\Omega$ . The duration of each test may be up to 60 seconds.

The DLRO10HD is rated CATIII 300 V provided the optional terminal cover is fitted to the instrument. Details of which can be found in the ordering information panel of this data sheet.

The DLRO10HD provides five test modes each of which is selected through a simple rotary control.

### **ADDITONAL FEATURES AND BENEFITS**

- Rugged case well suited to transportation with shoulder strap and lead set pouch
- Removable lid facilitates easy test lead connection
- Operational ingress protection is IP 54 (battery power only) ensuring protection from the elements
- 7Ah lead acid battery provides extended operation and can be charged whilst operating from line power
- Rotary mode switch with bidirectional (current reversal with averaging cancels thermal EMFs), unidirectional, automatic, continuous and inductive modes
- Large, clear LCD display with backlight and contrast adjustment

- High or low output power selection for condition diagnosis
- Rechargeable battery or line power supply, continuous operation, even with dead battery
- 10 A for 60 seconds, less time waiting to cool, great for charging inductance
- High input protection to 600 V, inadvertent connection to line or UPS voltage will not blow a fuse
- Heavy duty case: IP 65 lid closed, IP54 operational (battery operation only)
- Rotary switch selects one of five test modes, including auto start on connection, giving ease of use
- Auto power off function conserves battery

### **APPLICATIONS**

The DLRO10HD measures low resistance values in applications ranging from railways and aircraft to resistance of components in industry.

Any metallic joint can be measured but users must be aware of measurement limitations depending on application. For example, if a cable manufacturer plans to make resistive measurements on a thin wire, a low test current should be selected to prevent heating the wire thereby changing its resistance.

Measurements on electric motors and generators will be inductive and require the user to understand the inductive mode and charging process before a correct result is achieved.

The DLRO10HD is well suited to measuring thick conductors, bonds and quality of welding because of its 10 A range for resistance values up to 250 m $\Omega$ .

Electromagnetic noise induced into the leads can interfere with a reading. A noise symbol alerts the user and prevents a measurement when the instrument detects noise above its threshold.

When dissimilar metals are joined a thermocouple effect is created. Users should select a bidirectional mode to ensure cancellation of this effect. The instrument measures with current flowing in both directions and averages the result.

Normal mode is initiated by pressing the 'Test' button after connecting the test leads to the unit under test. Continuity of all four connections is checked. Current is applied in both forward and reverse direction following which measurement is displayed.

# Megger

Automatic mode is started as soon as the probes make contact. Forward and reverse current measurements are made and the average value is displayed. This mode is ideal when working with the supplied DH4 handspikes. Each time the probes are removed and reconnected to the load a new test will be performed without the need to press the test button.

## **TEST modes**

Automatic unidirectional mode applies current in one direction only to speed up the measurement process. However thermal EMF resulting from dissimilar metal bonds can cause lower accuracy. Test starts automatically when probes are connected.

Continuous mode allows repeated measurements to be made on the same sample. Simply connect the test leads and press the test button. The measurement is updated every three seconds until the circuit is broken.

Inductive mode is selected when measuring resistance on, for example, motors and generators. When measuring inductive loads it is necessary to wait for the voltage to stabilise as the inductive element is charged. Test leads are firmly connected to the device under test and the 'Test' button pressed. The instrument will pass the selected current through the sample continuously in one direction only and take repetitive readings that will gradually decrease to the true value as the voltage stabilises. The operator decides when the result is stable and presses the 'Test' button to terminate the test.

#### **ELECTRICAL SPECIFICATIONS**

#### **Resistance/Current Ranges**

The green resistance ranges on the keypad indicate low output power (<0.25 W) outputs. Red ranges indicate higher 2.5 W (1 A) and 25 W (10 A) power outputs.

#### **Resolution and Accuracy**

Test current accuracy  $\pm 10\%$ Voltmeter input impedance >200 k $\Omega$ 

Test current	Resistance range	Resolution (as displayed)	Basic accuracy*	Full scale voltage	Max. power output
0.1 mA	0 to 2500.0 Ω	0.1 Ω	±0.2%	25 mV	25 μW
0.1 mA	0 to 250.00 Ω	0.01 Ω	±0.2%	25 mV	2.5 μW
1 mA	0 to 25.000 Ω	$1 \text{ m}\Omega$	±0.2%	25 mV	25 μW
10 mA	0 to 2500.0 mΩ	0.1 m <b>Ω</b>	±0.2%	25mV	250 μW
100 mA	0 to 250.00 mΩ	0.01 m <b>Ω</b>	±0.2%	25 mV	2.5 mW
1 A	0 to 25.000 mΩ	1 μΩ	±0.2%	25 mV	25 mW
10 A	0 to 2500.0 μ <b>Ω</b>	0.1 μΩ	±0.2%	25 mV	0.25 W
1 A	0 to 2500.0 mΩ	0.1 m <b>Ω</b>	±0.2%	2.5 V	2.5 W
10 A	0 to 250.00 mΩ	0.01 m <b>Ω</b>	±0.2%	2.5 V	25 W

Inductive mode or undirectional mode will introduce an undefined error if an external EMF is present.

Basic accuracy at reference conditions.

### **GENERAL SPECIFICATIONS**

Temperature coefficient	< 0.01% per °C, from 5 °C to 40 °C		
Maximum altitude	2000m (6562 ft) to full safety specifications		
Display size/type	Main 5 digit + 2 x 5 digit secondary displays		
Battery type	6 V, 7Ah sealed lead acid		
Voltage input range	90 - 264 V, 50-60 Hz		
Charge time	8 hours		
Backlight	LED backlight		
Battery life	>1000 Auto (3 sec) tests		
Auto power down	300s		
Mode selection	Rotary switch		
Range selection	Rotary switch		
Weight	6.7 kg		
Case dimensions	L315 mm x W285 mm x H181 mm		
Pouch for test leads	Yes (lid mounted)		
Test leads	DH4 lead set included		
IP rating	IP65 case closed, IP54 battery operation		

#### Safety rating

In accordance with IEC61010-1, CATIII 300V when used with optional terminal cover (details in ordering information)

Operating temperature and humidity	-10 °C to +50 °C (14 °F to 122 °F) <90% RH
Reference conditions	20 °C ±3 °C
Storage temperature and humidity	-25 °C to +60 °C, <90% RH

# EMC

In accordance with IEC61326-1 (Heavy industrial)

#### Noise rejection

Less than  $1\% \pm 20$  digits additional error with 100 mV peak 50/60 Hz. on the potential leads. Warning will show if hum or noise exceeds this level.

### Maximum lead resistance

100 m $\!\Omega$  total for 10 A operation irrespective of battery condition.

# Megger.

# **DLRO10HD** 10 A Digital Low Resistance Ohmmeter

# **OPTIONAL TERMINAL COVER**



The CATIII 300 V rating on the DLRO10HD is only valid when the instrument is fitted with the optional terminal cover to provide the required creepage and clearances at the instrument terminals. Although the terminal cover may be used with any test

leads, only the Megger DH4 and DH5 duplex handspikes have suitable probe insulation to comply with the requirements of IEC61010-1 and the CATIII 300 V rating.



	<b>ORDERING I</b>	NFORMATION		
ltem (Qty)	Order No.	Item (Qty)		Order No.
DLRO10HD Low Resistance Ohmmeter	1000-348	Straight Duplex Handspikes (2)		
Included accessories		Heavy Duty with fixed	contacts.	
DH4 duplex handspike 1.2m	6111-503		2m/7ft	242002-7
Test lead pouch (lid mounted)	1000-036		5.5m/18ft	242002-18
DLRO10HD user guide CD	1000-869	9m/30ft		242002-30
Warranty book.	6170-618	Duplex Heavy Duty 5cm (2")		
Optional Accessories at extra cost		C-Clamps. (2)		
Calibration Shunt, 10 $\Omega$ , current rating 1 mA.	249000		2m/7ft	242004-7
Calibration Shunt, 1 $\Omega$ , current rating 10 mA.	249001		5.5m/18ft	242004-18
Calibration Shunt, 100 m $\Omega$ current rating 1A.	249002		9m/30ft	242004-30
Calibration Shunt, 10 m $\Omega$ current rating 10 A.	249003	Duplex handspikes with replaceable		
Certificate of Calibration for Shunts, NIST	CERT-NIST	Needle Points	2m/7ft	242003-7
Replacement tips for DH4 and DH5 handspikes.		Duplex 1.27 cm (1/2 ")	)	
Needle point	25940-012	Kelvin Clips. (2)		
Serrated end	25940-014	gold pla	ted 2m/7ft	241005-7
Optional Test Leads at extra cost		silver plated 2m/7ft		242005-7
Duplex Leads		Duplex 3.8 cm (11/2")		
DH5 straight duplex handspikes (2).		Kelvin Clips. (2)	2m/7ft	242006-7
One has indicator lights. 2.5m/8ft	6111-517		5.5m/18ft	242006-18
Terminal cover (use in conjunction with DH4 test			9m/30ft	242006-30
as standard, or optional DH5 test leads for CATIII compliance)	300 V 1002-390	Single Leads		
Duplex Handspikes (2) with spring loaded helical		Single handspike (1) f	or potential measureme	nt.
2m/7ft	242011-7		2m/7ft	242021-7
DH1 2.5m/8ft	6111-022		5.5m/18ft	242021-18
5.5m/18ft	242011-18		9m/30ft	242021-30
only 1 lead supplied	242011-18	Current clip (1) for cu	rrent connections.	
DH2 6m/20ft	6111 022		2m/7ft	242041-7
9m/30ft	6111-023 242011-30		5.5m/18ft	242041-18
DH3 9m/30ft	6111-024		9m/30ft	242041-30
	0111-024	Note: For more detail lead datasheet DLRO_	s of optional leadsets se _TL_DS_en_V01.pdf	e separate test

UK

UK Archcliffe Road Dover CT17 9EN England T +44 (0) 1304 502101 F +44 (0) 1304 207342 UKsales@megger.com

# **UNITED STATES** 4271 Bronze Way Dallas TX 75237-1019 USA T 800 723 2861 (USA only) T +1 214 333 3201

F +1 214 331 7399 USsales@megger.com

#### OTHER TECHNICAL SALES OFFICES

Valley Forge USA, College Station USA, Sydney AUSTRALIA, Täby SWEDEN, Ontario CANADA, Trappes FRANCE, Oberursel GERMANY, Aargau SWITZERLAND, Kingdom of BAHRAIN, Mumbai INDIA, Johannesburg SOUTH AFRICA, Chonburi THAILAND, Malaga SPAIN

#### CERTIFICATION ISO

Registered to ISO 9001:2008 Cert. no. Q 09250 Registered to ISO 14001-2004 Cert. no. EMS 61597

DLRO10HD\_DS\_EN\_V04 www.megger.com Megger is a registered trademark