

# DIGITUS Wall Mounting Cabinet Unique Series - double sectioned, pivoted

DN-19 20-U-3  
EAN 4016032190820



**20U wall mounting cabinet, Unique, 998x600x600 mm double sectioned, pivotable, grey (RAL 7035)**

The Wall Mounting Cabinets of the Unique Series were designed for the user friendly installation of active- and passive network components accompanied by a neat cable management. Each rack consists of up to 1.5 mm strong steel sheet material which ensures a very good stability as a robust steel construction. The color is created by powder coating in grey (RAL 7035) and black (RAL 9005). Wall installation can be done easily. Separately leveling feet or castors are available for free standing purposes. Door and side panels are easy to detach and the door stop can be changed from right to left. The roof contains air ventilation slots for a better air circulation. Each wall mounting cabinet contains one pair (two pieces) of mounted 483 mm (19") profile rails inside. They are galvanized, with height unit marking (countable from both directions) and variable in depth. Furthermore, the rear frame is outfitted with 483 mm (19") punch outs. An important aspect for each installation is the cable management. The roof of each cabinet is equipped with a sliding cable entry panel with rubber sealing. Punched out cable entries with plastic cover are present on the rear wall and base. The rear frame is also equipped with brushes on top and base side. An extensive portfolio of accessories for cable management, shelves, etc. will help to meet many requirements in daily use.

**The DIGITUS® Professional Unique Series is made for high demand IT-Infrastructure Solutions - designed and developed on highest standard in Germany**

- Safety class rating IP20
- Lockable safety-glass door with steel frame
- 210° door opening angle

- Housing is connected to rear frame with separate locking mechanism (incl. individual key)
- 102° pivotable angle of the housing from the frame
- 1-point-locking-mechanism on the front door
- Side panels are lockable and removable
- 483 mm (19") profile rails mounted on the front side inside of the cabinet, galvanized
- 483 mm (19") profile rails are adjustable in depth and with height unit marking
- Rear frame with 483 mm (19") punch outs
- Max. installation depth: 440 mm
- Cable entry on the rear side and base with plastic cover and top with sliding cover
- Rear frame with brush strip for cable entry on top and base
- Roof is prepared for fan units (punched out entries)
- Ventilation slots for active and passive ventilation and exhausting
- Several earthing points for rack components
- Incl. installation set (screws, cage nuts, washers)
- Incl. installation set (screws, cage nuts, washers)
- Rack is completely mounted
- Equipment mounting depth min.-max.: 375-440 mm
- IP protection class: IP20
- Color: light grey, RAL 7035
- Depth: 600 mm
- Front door: Glass door, single opening
- Units: 20
- Load capacity: 100 kg
- Mounted: yes
- Cabinet type: Wall mounting cabinet
- Width: 600 mm

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm <sup>3</sup>
Packaging Unit Carton	1	58.50	65.00	65.00	104.80	442,780.00
Packaging Unit Inside	1	58.50	65.00	65.00	104.80	442,780.00
Packaging Unit Single	1	58.50	65.00	65.00	104.80	442,780.00
Net single without Packaging	1	56.17	65.00	65.00	104.80	442,780.00

More images:

