

DIGITUS 1.25 Gbps copper SFP-module, RJ45

DN-81005
EAN 4016032389484



1.25 Gbps Copper SFP Module, RJ45 10/100/1000Base-T, up to 100m

The DIGITUS® Mini GBIC (SFP) transceiver modules offer the highest quality and reliability. The module offers a perfect opportunity for you to extend your Gigabit network switch with a free SFP Uplink Port around an additional RJ45 connection. Thanks to the hot-plug capability, you can install the module without any interruption to the network traffic or restart of the device. In addition, conformity with the MSA (Multi Source Agreement) standard provides compatibility with the current network switch manufacturers.

The plug and play extension for your network switch

- Mini GBIC SFP (Small Form Factor Pluggable) module
- Compatible with the following manufacturers: Ubiquiti, Allied Telesis, Allnet, CISCO, D-Link, Edimax, Intellinet, KTI Networks, Level One, PLANET, Tenda, TP-Link, TRENDnet, ZyXEL, ZTE, Avaya, Mikrotik, ENTERASYS, FINISAR, FORCE 10, RIVERSTONE, Fortinet
- Up to 1.25 Gbps bidirectional maximum data rate
- Compliant to IEEE 802.3z Gigabit Standard

- High quality and excellent reliability
- Easy plug-and-play installation
- MSA (Multi Source Agreement) compliant
- Hot pluggable - installation possible while in operation
- Auto MDI/MDI-X
- Connection: 1x RJ45, CAT 5
- Distance: up to 100 m
- Operating temperature: 0 °C ~ 70 °C
- Manufacturer compatibility: Universal (MSA)
- Connector: RJ45
- DDM Support: no
- Distance (km): 0.1
- Mode: Copper
- Ethernet speed: Gigabit

Package contents

- SFP module

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm ³
Packaging Unit Carton	120	7.00	25.40	39.40	55.00	55,041.80
Packaging Unit Inside	30	1.75	7.00	20.00	30.00	4,200.00
Packaging Unit Single	1	0.06	3.20	9.30	12.00	357.12
Net single without Packaging	1	0.02	1.50	1.50	7.00	0.00

More images:

SFP Modules						
Part Number	Data Rate	Speed	Distance	Connector	Wavelength	Operating Temperature
284-0101	1000000000	1000000000	1000000000	LC Duplex	1310nm	0 to 70 °C
284-0102	1000000000	1000000000	1000000000	LC Duplex	1550nm	0 to 70 °C
284-0103	1000000000	1000000000	1000000000	LC Duplex	1310nm	0 to 70 °C
284-0104	1000000000	1000000000	1000000000	LC Duplex	1550nm	0 to 70 °C
284-0105	1000000000	1000000000	1000000000	LC Duplex	1310nm	0 to 70 °C
284-0106	1000000000	1000000000	1000000000	LC Duplex	1550nm	0 to 70 °C
284-0107	1000000000	1000000000	1000000000	LC Duplex	1310nm	0 to 70 °C
284-0108	1000000000	1000000000	1000000000	LC Duplex	1550nm	0 to 70 °C
284-0109	1000000000	1000000000	1000000000	LC Duplex	1310nm	0 to 70 °C
284-0110	1000000000	1000000000	1000000000	LC Duplex	1550nm	0 to 70 °C
284-0111	1000000000	1000000000	1000000000	LC Duplex	1310nm	0 to 70 °C
284-0112	1000000000	1000000000	1000000000	LC Duplex	1550nm	0 to 70 °C
284-0113	1000000000	1000000000	1000000000	LC Duplex	1310nm	0 to 70 °C
284-0114	1000000000	1000000000	1000000000	LC Duplex	1550nm	0 to 70 °C
284-0115	1000000000	1000000000	1000000000	LC Duplex	1310nm	0 to 70 °C
284-0116	1000000000	1000000000	1000000000	LC Duplex	1550nm	0 to 70 °C
284-0117	1000000000	1000000000	1000000000	LC Duplex	1310nm	0 to 70 °C
284-0118	1000000000	1000000000	1000000000	LC Duplex	1550nm	0 to 70 °C
284-0119	1000000000	1000000000	1000000000	LC Duplex	1310nm	0 to 70 °C
284-0120	1000000000	1000000000	1000000000	LC Duplex	1550nm	0 to 70 °C

