### Technical data:

- die nests are distinctly laser marked
- adjustable if changes occur, ie after many crimps
- tested with Elpress terminals
- ratchet system which guarantees a fully closed crimp
- emergency release if the crimp sequence must be interrupted
- weight 0,35 kg, length 192 mm, width 66 mm
- unique design makes the tools compact and handy
- requires minimum of muscle force for a perfect crimp
- designed to fit both right- and left-handed users
- at least 50,000 crimps

Crimp range 0.14 - 1.5 mm<sup>2</sup>

**DSA0115** 

Elpress crimp tool for symmetrical crimping of pre-insulated terminals.

Crimp range 0.5 - 2.5 mm<sup>2</sup>

## DSA0725

Elpress crimp tool for symmetrical crimping of pre-insulated terminals.

### Particulars:

■ die nest wear inspection easily made with go/no-go gauge ESAQ 0760

## Crimp type

DSA0115

Crimp type

DSA0725



# ESAQ 0760 - die nest gauge

Elpress go/no-go gauge for inspection of die nests in the following crimp tools: DSA0115, DSA0725, ESA0760(C) and ESEA0340C.

## Particulars:

- weight 0,025 kg, length 55 mm
- grip Ø 8 mm
- supplied in practical plastic box
- a simple way to secure proper tool performance
- easy to use, with a GO-position and a NO GO-position for each die nest of the crimp tool.

Please contact Elpress for more information on tool calibration and QA.

Tool	Checks die nest
DSA0115	
DSA0725	
ESA0760(C)	
ESEA0340C	