


PmodDIP™ Reference Manual

Revised April 24, 2015
This manual applies to the PmodDIP rev. A

Overview

The Digilent PmodDIP is a 12-pin Dual-Inline Package (DIP) that also includes a 2×6 female Pmod header, allowing users to easily separate and process any signals traveling to and from their 12-pin Pmod.



Features include:

- 100 mil spaced DIP package
- 100 mil spaced 2×6 female Pmod header
- 12 pass-through channels

The PmodDIP.

1 Functional Description

The PmodDIP utilizes its 12 pass-through channels to route both digital and analog signals to and from the attached Pmod or other module. By being able to plug in the PmodDIP into a solderless breadboard, external processing of the signals can be easily performed.

2 Interfacing with the Pmod

The PmodDIP communicates with the host board via the GPIO protocol. As this is a pass-through module, all signals that are applied to each of the lanes will not be modified in any way.



2.1 Pinout Description Table

| Pmod Header Pin | DIP Header | DIP Pin |
|-----------------|------------|---------|
| 1 | J2 | 1 |
| 2 | J2 | 2 |
| 3 | J2 | 3 |
| 4 | J2 | 4 |
| 5 | J2 | 5 |
| 6 | J2 | 6 |
| 7 | J3 | 1 |
| 8 | J3 | 2 |
| 9 | J3 | 3 |
| 10 | J3 | 4 |
| 11 | J3 | 5 |
| 12 | J3 | 6 |

Any external power applied to the PmodDIP must be within the limits that your system board and attached Pmod can handle.

3 Physical Dimensions

The pins on the pin header are spaced 100 mil apart. The PCB is 0.7 inches long and 0.5 inches wide.