



The new generation of DUSPOL® voltage testers safe voltage testing up to 1000 V

The international standard for voltage testers IEC/EN 61243-3 (DIN VDE 0682-401):2011 increases safety for work under voltage

Your work as an expert requires safe testing. Therefore, you should not make any compromises concerning safety! Voltage testers which are used on electrical systems of up to 1000 V have to comply with the standard IEC/EN 61243-3 (DIN VDE 0682-401):2011. The standard creates uniform testing and safety criteria on an international level and remarkably which concentrates on user safety.

The new generation of DUSPOL® voltage testers exceeds the demands of the standards concerning both the protection category for housings (IP 65) and overvoltage protection (CAT IV 600 V). The nominal voltage range has been increased to a minimum of 1000 V AC/DC in order to ensure safe testing of increased system voltages of industrial applications, photovoltaic systems and wind power plants as well as of hybrid automotive engineering.



CAT IV 600 V

DUSPOL® analog

CAT IV 600 V

DUSPOL® expert

CAT IV 600 V

DUSPOL® digital



Stand-by case
010911
(see page 18)

All DUSPOL® voltage testers are equipped with a direct display system without loading the test point. In case of need, a load circuit can be connected via a push-button which suppresses inductive and capacitive reactive voltages. Thus, it is possible to clearly distinguish between high-energy and low-energy electric circuits.

A vibrating motor can be activated additionally. The vibrating power of this motor increases proportionally to the applied voltage. This is an additional indication of voltage being applied.

The DUSPOL® voltage testers underlines once again the BENNING expertise in the field of testing, measuring and safety technology. With a DUSPOL® voltage tester you acquire an innovative product which has been tested and approved by the independent VDE Test and Certification Institute.

DUSPOL® voltage testers The original!

Product safety at the highest level:

- safe voltage testing up to 1000 V AC/DC
- direct display without actuating a push-button (high-impedance testing)
- load connection via push-button (low-impedance testing)
- battery-independent voltage indication from 50 V AC/DC on
- vibration alert in the test handle
- robust round housing with rubberized gripping surface for outdoor use (protection category IP 65)
- tested and approved in compliance with the current DIN EN 61243-3 (VDE 0682-401):2011 standard

DUSPOL® voltage testers – the testers with the VDE mark of conformity safe, reliable and powerful

The new generation of DUSPOL® voltage testers

- safe voltage testing up to 1000 V AC/DC
- load connection with vibration alert
- intentional tripping of a 30 mA RCD
- phase sequence test in a three-phase mains
- single-pole external conductor test (phase)

Additionally for DUSPOL® expert, DUSPOL® digital:

- acoustic continuity test with loud test buzzer and visual indication by means of yellow LED
- measuring point illumination by means of white high-power LED
- phase sequence test by means of green LED (left/right)
- detector for non-contact localization of cable breaks on exposed and live lines

Additionally for DUSPOL® digital:

- voltage testing up to 1000 V AC TRUE RMS/1200 V DC
- TRUE RMS measuring method
- low-volt range: 1.0 V to 11.9 V
- frequency indication up to 1000 Hz
- resistance measurement up to 300 kΩ
- conducting-state voltage measurement of diodes
- automatic LC display illumination by means of a light sensor



Voltage and Continuity Tester

	DUSPOL® analog	DUSPOL® expert	DUSPOL® digital	PROFIPOL®
indication	plunger system (illuminated)/LED	LED	LED/LCD (illuminated)	LED
indication steps	12 – 1000 V AC/DC	12 – 1000 V AC/DC	1.0 – 1000 V AC/1200 V DC	6 – 400 V AC/DC
frequency range	–	–	1 – 1000 Hz	–
acoustic and visual continuity test	–	buzzer + yellow LED 0 – 100 kΩ	buzzer + yellow LED 0 – 100 kΩ	–
diode test	–	conducting-state/ non-conducting direction	0.3 – 2.0 V	–
resistance measuring range	–	–	0.1 kΩ – 300 kΩ	–
phase-sequence test	LCD (“R” symbol)	green LEDs (right/left)	green LEDs (right/left)	–
single-pole outer conductor test	LCD (“R” symbol)	red “lightning” LED	red “lightning” LED	–
polarity test	LED (+/-)	LED (+/-)	LCD (+/-)	LED (+/-)
cable break detector	–	yellow LED (flashing)	yellow LED (flashing)	–
load connection via push button	I _s = 600 mA (1000 V) 30 mA RCD trip	I _s = 550 mA (1000 V) 30 mA RCD trip	I _s = 550 mA (1000 V) 30 mA RCD trip	–
vibrating alarm	yes	yes	yes	–
measuring point illumination	–	white LED	white LED	–
protection class	IP 65	IP 65	IP 65	IP 65
item no.	050261	050262	050263	020022

