

Product datasheet

Specifications



Easy UPS 3S 20 kVA 400 V 3:1 UPS for internal batteries

Local distributor code: 422503619 E3SUPS20K3IB

Overview

Presentation High-efficiency 3-phase UPS that features advanced product features, competitive specifications, and robust electrical design, making business continuity easy in the data center or electrical room. This is an exceptionally easy to install, operate, maintain, and service 20 kVA UPS, ideal for small and medium businesses. Includes dust filter and conformance-coated boards for harsh environments. This UPS is for internal batteries, but is supplied without batteries, so you can easily customize the battery runtime. For battery runtime details, see the runtime charts published under the Documents tab.

Lead time Usually Ships within 6 Weeks

Main

Main Input Voltage 400 V 3 phases

Other Input Voltage 380 V
415 V

Main Output Voltage 230 V

Other Output Voltage 220 V
240 V

Rated power in W 20 kW

Rated power in VA 20 kVA

Provided equipment Dust filter
Installation guide

Batteries & Runtime

Battery type VRLA

Battery voltage 240 V

Maximum short-circuit current 10 kA

Number of battery filled slots 0

Number of battery free slots 3

Max current discharge 54 A

Discharge battery voltage +/- 198 V DC

Physical

Colour White (RAL 9003)

Height 140 cm

Width 38 cm

Depth 90.7 cm

Net weight	150 kg
USB compatible	Yes

Input

Maximum input current	37 A
Input harmonic distortion	Less than 5 % for full load
Input Power Factor at Full Load	0.99
Input voltage limits	304...477 V
Input protection type	Circuit breaker and fuse
Network frequency	45...65 Hz

Output

Maximum configurable power in VA	20 kVA
Maximum configurable power in W	20 kW
Output frequency	50 Hz sync to mains 60 Hz sync to mains
Harmonic distortion	Less than 3 %
Output harmonic distortion	< 5.5% at 100% non-linear load
Output overload operation	10 minutes at 125% and 60 seconds at 150%
Output voltage tolerance	+/- 1.5 %
UPS type	Double conversion online
Crest factor	3 : 1

Conformance

Product certifications	CE EAC RCM
------------------------	------------------

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3281 ft
Ambient air temperature for storage	-25...55 °C
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0.00...15240.00 m
Acoustic level	60 dBA
Heat dissipation	870 Btu/h
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	164 cm
Package 1 Width	101.4 cm

Package 1 Length	56.3 cm
Package 1 Weight	158 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Recommended replacement(s)