

### Monitoring relays - ENYA series Voltage monitoring in 3- & 1-phase mains in accordance with VDE 0108-100 and VDE 0100-718 Undervoltage monitoring Supply voltage = measured voltage 2 change over contacts Width 35 mm Installation design



## **Technical data**

#### 1. Functions

Undervoltage monitoring in 3- & 1-phase mains in accordance with VDE 0108-100 and VDE 0100-718 (each phase against the neutral wire) with fixed adjustable threshold and fixed adjustable hysteresis.

#### 2. Time ranges

Adjustment range fixed, approx. 200ms

### Tripping delay: 3. Indicatiors

Type E3YF400V02 0.85: Green LED ON/OFF: Yellow LED ON/OFF:

indication of supply voltage indication of relay output Type E3YF400VT02 0.85:

Green LED L1 ON/OFF: indication of supply voltage L1-N Green LED L2 ON/OFF: indication of supply voltage L2-N Green LED L3 ON/OFF: indication of supply voltage L3-N Yellow LED ON/OFF: indication of relay output

#### 4. Mechanical design

Self-extinguishing plastic housing, IP rating IP40 Mounted on DIN-rail TS 35 according to EN 60715 Mounting position: any Shockproof terminal connection according to VBG 4 (PZ1 required), IP rating IP20 Tightening torque: max. 1Nm Terminal capacity:

1 x 0.5 to 2.5mm<sup>2</sup> with/without multicore cable end

- 1 x 4mm<sup>2</sup> without multicore cable end
- 2 x 0.5 to 1.5mm<sup>2</sup> with/without multicore cable end
- 2 x 2.5mm<sup>2</sup> flexible without multicore cable end

#### 5. Input circuit

Supply voltage: Terminals: Rated voltage U<sub>N</sub>:

Tolerance: Rated consumption: Rated frequency: Duty cycle: Reset time: Hold-up time: Drop out voltage:

Overvoltage category: Rated surge voltage:

(= measured voltage) N-L1-L2-L3 see table ordering information or printing on the unit -30% to +30% of U<sub>N</sub> 11VA (1,2W) a.c. 48 to 63Hz 100% 500ms determined by undervoltage detection

(see measured circuit) III (in accordance with IEC 60664-1) 6kV

#### 6. Output circuit

2 potential free change over contacts Rated voltage: Switching capacity: Fusing: Mechanical life: Electrical life:

Switching frequency:

Overvoltage category: Rated surge voltage:

### 7. Measuring circuit

Measuring variable: Measuring input: Terminals: Overload capacity:

Input resistance: Switching threshold U.: Hysteresis H: Overvoltage category: Rated surge voltage:

### 8. Accuracy

Base accuracy: Adjustment accuracy: Repetition accuracy: Voltage influence: Temperature influence:

### 9. Ambient conditions

Ambient temperature: Storage temperature: Transport temperature: Relative humidity:

Pollution degree:

10. Weight Single packing: 109g

250V a.c. 1250VA (5A / 250V) 5A fast acting 20 x 10<sup>6</sup> operations 2 x 10<sup>5</sup> operations at 1000VA resistive load max. 6/min at 1000VA resistive load (in accordance with IEC 60947-5-1) III (in accordance with IEC 60664-1) 6kV

a.c. sinus, 48 to 63Hz (= supply voltage) N-L1-L2-L3 determined by tolerance specified for supply voltage

fixed 195,5V approx. 5% III (in accordance with IEC 60664-1) 6kV

≤5% (of nominal value)

≤2% ≤0.05% /°C

-25 to +55°C -25 to +70°C -25 to +70°C 15% to 85% (in accordance with IEC 60721-3-3 class 3K3) 2 (in accordance with IEC 60664-1)

www.tele-online.com

# Functions


Undervoltage monitoring for 3-phase a.c. mains with fixed adjustable switching threshold and fixed adjustable hysteresis. All measuring inputs (L1, L2 and L3) must be connected to phase voltage. If single or 2-phase monitoring is required, unused input terminals (L) must be connected to mains voltage to have proper L-N voltage on the terminals L1, L2 and L3. A phase failure can not be detected, if the reverse voltage coming from the load exceeds the threshold  $U_{\rm s}$ .

#### Test function (optional)


The test function enables a manually disconnection of the output relay.

#### Undervoltage monitoring


The output relay R switches into on-position (yellow LED illuminated), when the measuring voltage of all connected phases exeeds the fixed threshold by more than the fixed hysteresis. When the voltage of one of the connected phases falls below the fixed threshold, the output relay R switches into off-position again (yellow LED not illuminated).




# Connections




## Connections



## Dimensions





# **Ordering information**

Types	Rated voltage U <sub>N</sub>	Switching threshold U <sub>s</sub>	Options	LEDs	Part No.
E3YF400V02 0.85	3(N)~400/230V in accordance with VDE 0108	fixed 195,5V (L-N)	-	U, Rel.	1341401
E3YF400VT02 0.85	3(N)~400/230V in accordance with VDE0 108	fixed 195,5V (L-N)	Test function	L1, L2, L3, Rel.	1341402



