IoT Flow Sensors E8FC

Detect Signs of Abnormalities in Cooling Water by Simultaneous Measurement of "Flow Rate + Temperature"

- Multi-sensing of "Flow rate + temperature" for preventing a sudden stops or manufacturing defects.
- Various lineup of replacement adapters to enable easy replacement of your current pressure gauges and flow meters.
- Analog current output function in addition to the IO-Link communications function that can perform self-diagnosis of abnormalities in the sensor itself.



Refer to Safety Precautions on page 19.





For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Sensors [Refer to Dimensions on page 21.]

Appearance	Applicable fluid	Control output	Communication method	IO-Link baud rate	Model
	PNP Liquid	IO-Link	COM2 (38.4 kbps)	E8FC-25D	
•		FINE	Analog	COM3 (230.4 kbps)	E8FC-25T
		Analog		E8FC-25	

Note: Please contact your OMRON sales representative regarding the IO-Link setup file (IODD file).


^{*} The applicable fluid is a liquid that does not erode the wetted part materials (for example, water or a fluid whose conductivity is equivalent to that of water).

Adapters [Refer to Dimensions on page 21.]

It must be selected from the adapters below.

	Applicable	diameter *			
Appearance	Nominal diameter A	Nominal diameter B	Thread type	Materials	Model
	10 A	3/8"	R (taper thread)		E8FC-YA-R10A
	10 A	3/8	NPT (taper thread)		E8FC-YA-N10A
	1F A	1/0"	R (taper thread)		E8FC-YA-R15A
	15 A	1/2"	NPT (taper thread)	0110004	E8FC-YA-N15A
	00.4	0/4"	R (taper thread)	- SUS304	E8FC-YA-R20A
	20 A	3/4"	NPT (taper thread)		E8FC-YA-N20A
	05 A	4.7	R (taper thread)		E8FC-YA-R25A
	25 A	1"	NPT (taper thread)		E8FC-YA-N25A

^{*}The applicable diameter is the size of the part shown below at the piping side.



Cables (Sensor I/O Connectors)

A Cable is not provided with the Sensor. It must be ordered separately.

Туре	Appearance	Cable	Model
	Straight	2 m	XS5F-D421-D80-F
Socket on one		5 m	XS5F-D421-G80-F
cable end	L-shaped	2 m	XS5F-D422-D80-F
	W	5 m	XS5F-D422-G80-F
	Straight/straight	2 m	XS5W-D421-D81-F
Socket and plug on cable ends *		5 m	XS5W-D421-G81-F
	L-shaped/L-shaped	2 m	XS5W-D422-D81-F
		5 m	XS5W-D422-G81-F

Note: Refer to *Sensor I/O Connectors/Sensor Controllers* on OMRON website for details. * Straight type/L-shape type combinations are also available.

O-ring (for replacement) [Refer to Dimensions on page 22.]

Appearance	Туре	Model
0	For E8FC-25□	E8FC-YL-1

Ratings and Specifications

Sensors


	PNP (COM2)	E8FC-25D				
Model	PNP (COM3)	3) E8FC-25T				
	` ,	E8FC-25				
Applicable	Nominal diameter B	3/8"	1/2"	3/4"	1"	
diameter	Nominal diameter A	10 A	15 A	20 A	25 A	
Applicable fluid			corrode the material is equivalent to that	of the wetted part (for ext of water).	cample, water or a fluid	
Permissible pressure *1		10 MPa				
	Detect flow rate vance	0.6 to 14 l/min	1 to 30 l/min	1.5 to 60 l/min	2 to 100 l/min	
	Rated flow rate range	Inner diameter setting (10 A, 15 A, 20 A, 25 A)				
	Display range	0 to 16 l/min	0 to 33 l/min	0 to 66 l/min	0 to 110 l/min	
	Zero cutting flow rate *3	0.6 l/min	1 l/min	1.5 l/min	2 l/min	
	Display resolution (I/min)	0.1/1 (Selectable)				
Flow rate	Flow rate monitoring response time	Control output: 1.0, 2.5, 5, 10, 30, 60 s				
monitoring *2	Flow rate monitoring precision	± (7.0% + 2.0% F.5	S.) or less			
	Flow rate repeatability / F.S. (prescribed for each response time)	1 s: ±3.5%, 2.5 s: ±2.5%, 5 s: ±1.6%, 10 s: ±1%, 30 s: ±0.8%, 60 s: ±0.6%				
	Ambient temperature characteristics *4	±1.0% F.S./10°C				
	Hysteresis	Variable				
T	Temperature monitoring rated range	0 to 85°C				
Temperature monitoring *5	Temperature monitoring precision	±2.5°C				
	Temperature repeatability	±0.5°C				
Control output	Standard mode	Judge if the measu	red value is the thre	shold value or more (or l	ess).	
judgment (selectable)	Window mode	Judge if the measured value is within the upper and lower limits.				
Display method		Numerical value indication: 4-digit 7-segment white LED with inverting function Status indicators: The content of indication is selectable from green, orange, red and OFF. Output indicator: OUT1 operation (orange), OUT2 operation (orange) Unit indicator: //min (White), % (White), °C (White), ST (White) Communication indicator: Lighting when communications are in progress (green)				
Delay setting		1 to 9999 ms (Select a function from invalid, ON delay, OFF delay, and one-shot.)				
Connection method	od	M12, 4-pole connector type				
Output ch1 (selectable)	Control output	Flow rate control output (N.O./N.C.) E8FC-25D/-25T: PNP E8FC-25: NPN 30 VDC or less, Class 2, 100 mA max., residual voltage 1 V or less			ess	
	Pulse output	1/ 10/ 100/1000 I				
	Control output	Flow rate control output (N.O./N.C.) / temperature control output (N.O./N.C.) E8FC-25D/-25T: PNP E8FC-25: NPN 30 VDC or less, Class 2, 100 mA max. residual voltage 1 V or less			,	
Output ch2 (selectable)	Analog current output *7	Flow rate analog output /temperature analog output Current output 4 to 20 mA (maximum load resistance 350Ω or less) (Display value \pm 2% of F.S.)			ess)	
	Pulse output	1/ 10/ 100/1000 I				
	External input	Smart tuning, One-point tuning, short-circuit current 1.5 mA or less, input time 20 ms or more				

PNP (COM		E8FC-25D		
Model	PNP (COM3)	E8FC-25T		
	NPN	E8FC-25		
	IO-Link specification	Ver 1.1		
	Baud rate	E8FC-25D: COM2 (38.4kbps) E8FC-25T: COM3 (230.4Kbps)		
IO-Link	Data length	PD Size: 6 byte OD Size: 1 byte (M-sequence type: TYPE_2_V)		
	Minimum cycle time	E8FC-25D (COM2): 3.2 ms E8FC-25T(COM3): 2.0 ms		
	Power supply voltage	15 to 30 VDC (including 10% ripple (p-p)), Class 2		
Power supply	Power consumption	2,880 mW or less (When power supply voltage is 30 V, current consumption must be 96 mA or less. When power supply voltage is 15 V, current consumption must be 192 mA or less.)		
Protection circui	t	Power supply reverse connection protection, output short-circuit protection, and output reverse connection protection		
	Ambient temperature range	-20 to 80°C in operation and storage, respectively (no condensation)		
	Applicable fluid temperature	0 to 85°C (no icing on the pipe surface)		
	Ambient humidity range	35 to 85%RH in operation and storage, respectively (no condensation)		
	Withstand voltage	500 VAC 50/60 Hz 1min		
Environment resistance	Vibration resistance (destruction)	10 to 2000 Hz, double amplitude 1.5 mm, 2 hours in X/Y/Z direction each		
	Shock resistance (destruction)	500 m/s², three times in X/Y/Z direction each		
	Protective structure	IP67		
	Pollution degree	3		
	Altitude	2,000 m or less		
	Installation place	Indoor		
Materials Wetted part Other than wetted part		Detecting unit: SUS304L, O-ring: FKM		
		Head: PPSU, display unit: PES, button: PBT, chassis: SUS304L, nut: SUS304		
Weight		Approx. 190 g		
Accessories		Ferrite core x 1 (TDK's Model ZCAT1 730-0730A) User's manual (Japanese, English, and Chinese), one each Compliance sheet Index list		

- *1. Even instantaneous pressure fluctuation such as water hammer must be within the permissible pressure.
- *2. The flow rate precision is defined based on the values measured in Omron's pre-shipment adjustment facility using water at the ordinary temperature (approx. 23°C).
 - In the ordinary temperature environment (approx. 23°C), install the product with the long side of the chassis holding unit toward the upstream of the pipe.
 - The measured value might vary due to fluid pulsation or pipe clogging.
- *3. Cutting to zero is the function outputting the flow rate less than the minimum rated flow rate as zero.
- *4. The ambient temperature characteristics are defined based on the values measured in the following environment using water at the ordinary temperature (approx. 23°C) flowing at 30 l/min.
 - In ordinary temperature environment (approx. 23°C) / pipe diameter 20A / straight pipe length 200 mm or more / recommended joint (KITZ's PTZ-20A) / dedicated adapter (E8FC-YA-R20A) / Install the product with the long side of the chassis holding unit toward the upstream of the pipe.
- *5. The temperature precision is defined based on the values measured in the following environment using water.
 - In ordinary temperature environment (approx. 23°C) / pipe diameter 20A / straight pipe length 200 mm or more / recommended joint (KITZ's PTZ-20A) / dedicated adapter (E8FC-YA-R20A) / Install the product with the long side of the chassis holding unit toward the upstream of the pipe.
- ***6.** If the pipe temperature exceeds 70°C, do not contact any cables with the pipe.
- *7. Do not connect analog current output with the master unit of IO-Link. Otherwise, the unit might fail.


I/O Circuit Diagrams

PNP output




*Pin 2 input/output can be switched with either the operation buttons or the IO-Link communication command "Pin 2 switching mode selection".

NPN output



^{*}Pin 2 input/output can be switched with the operation buttons.

Connector Pin Arrangement



Applicable connector code: XS5F / XS5W series Applicable IO-Link master unit: NX/GX series

Pin No.	E8FC	E8FC-25	
	Standard I/O mode	IO-Link mode	
(1)	+V	+V	+V
(2)	EXTIN/Analog/OUT2 *	Analog/OUT2 *	EXTIN/Analog/OUT2 *
(3)	0 V	0 V	0 V
(4)	C/Q	C/Q	Q

Q: Control output
C: IO-Link
— communications

EXTIN: External input


^{*} Pin 2 input/output can be switched with either the operation buttons or the IO-Link communication command, "Pin 2 switching mode selection".

E8FC

Timing Charts

The PNP output is described below by using the flow rate control output of OUT1 as an example. The activity is the same even when temperature control output is selected in OUT2.

PNP output




^{*1.} The N.O./N.C. setting can be changed by the operation buttons or IO-Link communications.

^{*2.} The timer function can be set individually for OUT1 and OUT2 by the operation buttons or IO-Link communications. (Selection of ON delay, OFF delay, or one-shot function, and selection of a timer time from 1 to 9999 ms) The delay timing of each function is same as the NPN output. Refer to the next page.


^{*3.} Factory default

NPN output




*1. The N.O/N.C setting can be changed by the operation buttons.

*2. The timer function can be set individually for OUT1 and OUT2 by the operation buttons. (Selection of ON delay, OFF delay, or one-shot function, and selection of a timer time from 1 to 9999 ms)



*3. Factory default

Nomenclature



Safety Precautions

Be sure to read the precautions for all models in the website at: http://www.ia.omron.com/.

Warning Indications



Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally, there may be significant property damage.



Indicates a potentially hazardous situation which, if not avoided, may result in minor or moderate injury or in property damage.

Precautions for Safe Use

Supplementary comments on what to do or avoid doing, to use the product safely.

Precaution for Correct Use

Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.

Meaning of Product Safety Symbols



General Prohibition

Indicates the instructions of unspecified prohibited action.



General caution

Indicates unspecified general alert.



Caution, explosion

Indicates the possibility of explosion under specific conditions.



Caution, high temperature

Indicates the possibility of injuries by high temperature under specific conditions.



Caution, fire

Indicates the possibility of fires under specific conditions.

⚠ WARNING

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purpose.



The specification of this product is not for beverage, food, or medical chemicals.

Do not use this product for the device contacting beverage, food, or medical chemicals.



Do not use the product with voltage in excess of the rated voltage.

Excess voltage may result in malfunction or fire.



This product is not assumed to be used in explosion-proof areas.

Do not use the product in explosion proof areas.



Never use the product with an AC power supply. Otherwise, explosion may result.



The product might fail or be destroyed.

Do not impress any pressure exceeding the rated value even instantaneously.



The product might fail or be damaged.

Do not stand on the sensor, or add excessive load.



The fluid in the pipe might spout out. Tighten the prescribed O-ring to the pipe.



Caution

The product might fail or be damaged. Piping, wiring, maintenance, and checkup must be done by operators with expertise.



The product might be damaged or fire. Do not short-circuit load.



The product might be damaged or fire.

Be careful with polarity of the power supply to avoid

Be careful with polarity of the power supply to avoid incorrect wiring.



The user might get burned.

The sensor surface temperature rises depending on the operating condition such as ambient temperature, power supply voltage, or fluid temperature. Be careful when operating or cleaning the product.



Precautions for Safe Use

The following items are necessary for ensuring safety, so be sure to observe them.

- Do not use the product in the following installation areas.
 - (1) Locations subject to direct sunlight
 - (2) Locations subject to condensation due to high humidity
 - (3) Locations subject to corrosive gas
 - (4) Locations subject to vibration or mechanical shocks exceeding the rated values
 - (5) Locations subject to exposure to water, oil, chemicals
 - (6) Locations subject to stream
 - (7) Locations subjected to strong magnetic field or electric field
- Do not use in an environment exposed to an inflammable/ explosive gas
- Do not use in an ambient atmosphere or environment exceeding the rating.
- Although the product is classified into IP67, do not use it in water, under the rain, or outdoor.
- Do not use the product for any inflammable, explosive, or corrosive fluids.
- Do not froze or solidify the fluid. Otherwise, the product might fail or be damaged.
- Provide a relief valve to prevent the circuit from liquid sealing.
- The surface temperature of the sensing part may increase. Use caution while operating and cleaning the product.
- Make sure safety before installing/replacing the sensor, for example, stop the machine or depressurize the fluid.
- In order to ensure safety of user operations and maintenance, install the product apart from high-pressure equipment or power equipment.
- When revolving the product, support the chassis holding part with a spanner.
- Wire this product separately from high-pressure wire or power wire. If wiring together with such wire or in the same duct, this product might receive induction, which might cause malfunctioning

or damages.


- · Be sure to turn OFF the power before wiring.
- . Do not wire with a wet hand.
- Use this product under the rated or smaller load. Otherwise, the product might be damaged or catch fire.
- · Connect load correctly.
- If the load and sensor use separate power supplies, turn ON the sensor's power first.
- Process unwired terminals so that they do not contact other wire or equipment.
- Do not use the product with the main unit damaged.
- Be careful with the sharp screw parts.
- · Do not pull connected cables hard.
- Do not use organic solvents such as thinner or alcohol for cleaning because they deteriorate the degree of protection and indication performance.
- Do not try to disassemble, repair, or alter the main unit.
- · If disposing this product, handle it as industrial waste.
- This product is certified by the UL standard based on the assumption that Class 2 circuits are used. Operate this product using Class 2 power supply in the United States or Canada.
- Use cables of Omron model XS5F-D4 series or model XS5W-D4 series.
- The — mark shown on the sensor nameplate means direct current.
- Electromagnetic environment: Industrial electromagnetic environment (EN 61326-1 Table2)


Precaution for Correct Use

- Do not use this product as a measuring apparatus for commercial transactions.
- Do not use this product for any fluids containing impurities.
- If the fluid is non-conductive and the pipe is made of resin, ground the chassis.
- Use the product in the condition that the fluid temperature is higher than the ambient temperature. For preventing condensation, use the product as dehumidifying by air conditioning and 30 cm or more apart from cold pipes.
- Do not add excessive impart such as falling or collision.
- Do not touch the detecting unit with bare hands.
- Apply grease to the thread parts to prevent them from getting hard to remove due to seizure.
- · Fasten by the prescribed torque.
- When using a cable of which diameter is different from that of the recommended cable, prepare a ferrite core suitable for the cable diameter separately.
- If using the product in IO-Link mode, keep the wiring length between the master unit and sensor 20 m or less.
- Just after the power is turned ON, it might take long for the measured value to get stable according to the operating environment.
- Do not connect with the IO-Link master unit in analog output mode.
 This product might be damaged depending on the specification of the IO-Link master.
- Do not push the button with something sharp such as a screwdriver because doing so might damage the button.
- If using the product in an environment subject to sharp temperature variation, evaluate the product in the environment in advance.
- When implementing maintenance, use a soft brush or waste cloth so as not to damage the detecting unit or O-ring.
- When replacing the O-ring, prevent dust/dirt from being mixed into the O-ring.
- Use the product in an environment at altitudes less than 2,000 m.
- Use the product in an environment of pollution degree 3.

Piping Method

- Use the adapter according to the connection pipe diameter of the piping.
- Install the sensor such that its tip is in contact with the fluid.
- In the case of horizontal piping, it is recommended to install the sensor from the side.
- In the case of vertical piping, it is recommended to install the sensor such that the flow is from the bottom to the top.
- When revolving the product, support the chassis holding part with a spanner.






Sensors

IoT Flow Sensor E8FC-25□






Adapters

E8FC-YA-R10A E8FC-YA-N10A






*The specification for each model is shown in the table below.

Model	E8FC-YA-R10A E8FC-YA-N10A	
Applicable diameter	10 A	
Threaded	R3/8	NPT3/8

E8FC-YA-R15A E8FC-YA-N15A






*The specification for each model is shown in the table below.

Model	E8FC-YA-R15A E8FC-YA-N1	
Applicable diameter	15 A	
Threaded	R1/2	NPT1/2

E8FC-YA-R20A E8FC-YA-N20A








 $*$ The specification for each model is shown in the table below.

Model	E8FC-YA-R20A E8FC-YA-N20A	
Applicable diameter	20	Α
Threaded	R3/4	NPT3/4

E8FC-YA-R25A E8FC-YA-N25A








* The specification for each model is shown in the table below.

Delow.		
Model	E8FC-YA-R25A	E8FC-YA-N25A
Applicable diameter	25	A
Threaded	R1	NPT1

E8FC

O-ring E8FC-YL-1





Cables

Sensor I/O Connectors (M12, Socket on one cable end)

Straight XS5F-D421-D80-F XS5F-D421-G80-F

40.7 L (cable length)
40.7


M12×1

30


50

Sensor I/O Connectors (M12, Socket and plug on cable ends) Straight/straight

Straight/straight XS5W-D421-D81-F XS5W-D421-G81-F



L-shaped XS5F-D422-D80-F XS5F-D422-G80-F



L-shaped/L-shaped XS5W-D422-D81-F XS5W-D422-G81-F

