



round cylinder DSNU-S-25-25-P-A

Part number: 5228230

★ Core product range

FESTO



Data sheet

Feature	Value
Stroke	25 mm
Piston diameter	25 mm
Piston rod thread	M8
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Design structure	Piston Piston rod Cylinder barrel
Position detection	For proximity sensor
Operating pressure	0.6 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	-20 ... 80 °C
Theoretical force at 6 bar, return stroke	247.4 N
Theoretical force at 6 bar, advance stroke	294.5 N
Moving mass with 0 mm stroke	71 g
Additional weight per 10 mm stroke	11 g
Basic weight for 0 mm stroke	238 g
Additional mass factor per 10 mm of stroke	6 g
Mounting type	with accessories
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Material cover	Wrought Aluminium alloy
Material seals	TPE-U(PU)
Material piston rod	High alloy steel, non-corrosive
Material cylinder barrel	High alloy steel, non-corrosive