


**Diameter: 20.0 mm (0.78")**  
**Height: 3.20 mm (0.125")**


### Specifications

<b>Classifications:</b>	Lithium
<b>Chemical System</b>	Manganese Dioxide Li/Organic Electrolyte
<b>Designation:</b>	ANSI CR2032, IEC 5004LC
<b>Nominal Voltage:</b>	3V
<b>Storage Temp:</b>	+5°C to +30°C
<b>Operating Temp:</b>	-20°C to +60°C
<b>Typical Weight:</b>	3.0 gm
<b>Typical Volume:</b>	0.63 cm <sup>3</sup> (0.04 in <sup>3</sup> )
<b>Typical Li Content:</b>	0.07g
<b>Transportation:</b>	For complete details, please see the reference: Special Provision A45 of the International Air Transport Association Dangerous Goods Regulations
Global (except US)	
United States:	49 CFR 173.185

Relative Capacity vs. Discharge



Constant Temperature Discharge @ 15 kΩ



\* Nominal capacity indicates duration until the voltage drops down to 2.0V when discharged at a nominal discharge current at 20°C.  
 \*\* When using these batteries at temperatures outside the range of -20 to +60°C, please consult Duracell in advance for conditions of use.  
 \*\*\* Dimensions and weight are for the battery itself, but may vary depending on the shape of terminals or other factors.

**DURACELL®**  
 BATTERIES

Berkshire Corporate Park  
 Bethel, CT 06801 U.S.A  
 Telephone: Toll-free 1-800-544-5454  
 Internet: [www.duracell.com](http://www.duracell.com)

\*Delivered capacity is dependent on the applied load, intermittent changes, operating temperature and cut off voltage. Please refer to the charts and discharge data shown for examples of energy/service life that the battery will provide for various conditions.

Information and contents in this data sheet are for reference purposes only. They do not constitute any warranty and representation is subject to change without notice. For the most current information and further details, please contact Duracell.