

EE741

Modular, compact, inline flow meter for compressed air and gases

The EE741 inline flow meter is dedicated for accurate metering and monitoring of compressed air and technical gases. With three different gauge mounting blocks, one and the same transmitter unit can be installed on DN15, DN20 and DN25 pipes.

The thermal measuring principle and the well-proven E+E hot film sensor element lead to best long-term stability and fast response time. Outstanding measuring accuracy, even in the lower measuring range is achieved by an application-specific multi-point factory adjustment, which is performed at 7 bar (102 psi). This allows reliable leak detection and corresponding energy savings.

The construction of the EE741 is optimized for easy installation and maintenance.



The EE741 is user configurable and can be easily adapted to any measuring task. The configuration can be set either using the optional display and push buttons or with the free product configuration software EE-PCS.

Typical applications _

- Compressed air consumption measurement
- Flow measurement of technical gases (O₂, N₂, Ar, CO₂, He)
- Nitrogen generators
- Leak detection

Features

Transmitter

- » Can be used for three different pipe diameters
- » Installation and removal without disassembling the pipework facilitates regular calibration
- » Application-specific adjustment under pressure for best accuracy

Display (optional)

- » Shows instantaneous values and overall consumption
- » Intuitive device setup with push
- » Can be rotated in 90° increments

Sensor head and thermal flow sensor

- » Robust design in stainless steel
- » Very fast response time
- » Wide measuring range
- » Long-term stable and accurate
- » Negligible pressure drop
- » Highly insensitive to contamination
- » No additional pressure and temperature compensation required



- » User configurable via display or software
- » Analogue 0-20 / 4-20 mA
- » Pulse output


Gauge mounting block

- » Precise and reproducible inline installation of the transmitter for best accuracy
- » Aluminum or stainless steel
- » Can be operated with sealing plug also without transmitter

- » 2 switch outputs
- » Modbus RTU
- » M-Bus



- » Standard volume flow
- » Mass flow
- » Standard flow
- » Temperature
- » Integrated consumption meter (totalisator) for cost-effective consumption analysis without additional datalogger




v1.0 / Modification rights reserved **EE741**

Modular design _

With the DN15, DN20 and DN25 gauge mounting blocks, one and the same transmitter unit can be installed on all three pipe diameters. The pipe diameter can easily be changed via display menu or with the EE-PCS product configuration software.

Once the gauge mounting block is built into the pipeline, the transmitter can be installed and removed without disassembling the pipework. As a result, the EE741 is also ideal for temporary measurements or even mobile use. The sealing plug included in the scope of supply enable the normal operation of the compressed air system when the transmitter is removed.



Technical data _

Meas	sured values				
	Flow				
	Measurands		m³/h, m³/min, l/min, l/s, kg/h, k	g/min, m/s, SCFM, ft/min, °C, °F	
	Standard conditions (factory setting)		1013.25 mbar (14.7 psi), 0 °C (32 °F) (configurable)		
	Measuring range	e ¹⁾ in air	DN15: 0.276.3 Nm ³ /h (0.12	244.88 SCFM)	
			DN20: 0.4135.6 Nm ³ /h (0.24	479.77 SCFM)	
			DN25: 0.6212 Nm ³ /h (0.36	5124.71 SCFM)	
	Accuracy ²⁾ in air at	7 bar (102 psi) (abs) and 23 °C (73 °F)	± (3 % of measured value + 0.	.3 % of full scale)	
	Temperature coe			ue / °C deviating from 23°C (73°F)	
	Pressure coeffici	ent ³⁾		e / bar deviating from 7 bar (102 psi)	
	Response time t ₉₀ Measuring rate		< 2 sec. 0.1 sec.		
	Temperature				
	Measuring range	2	-2060 °C (-4140 °F)		
	Accuracy at 20 °C (68 °F) and flow >0.5 Nm/s	± 0.7 °C (1.26 °F)		
Outp					
	Analogue output (scalable)		0 - 20 mA / 4 - 20 mA	R₁<500 Ohm	
			DC PNP, max. 100 mA, V _{drop} <	2.5 V	
			Configurable: N/C or N/O, hysteresis, window		
			Modbus RTU or M-BUS (Mete	r-Bus)	
	Configuration into	erface	USB	<u> </u>	
Gene	•		-2060 °C (-4140 °F) ± 0.7 °C (1.26 °F) 0 - 20 mA / 4 - 20 mA R _L <500 Ohm DC PNP, max. 100 mA, V _{drop} <2.5 V Configurable: N/C or N/O, hysteresis, window Consumption meter, pulse length 0.022 sec. Modbus RTU or M-BUS (Meter-Bus) USB 18 - 30 V DC 150 mA (with display) 100 mA (without display) 16 bar / PN16 lay -1050 °C (14122 °F) lisplay -2060 °C (-4140 °F)		
	Supply voltage		18 - 30 V DC		
	Current consumption (max.)		150 mA (with display)		
			100 mA (without display)		
	Operating pressu	ure (max.)	16 bar / PN16		
	Ambient temperature with display without display Medium and storage temperature Humidity Medium Electrical connection Electromagnetic compatibility		-1050 °C (14122 °F)		
			-2060 °C (-4140 °F)		
			-2060 °C (-4140 °F)		
			0100 % RH, non-condensing	g	
			Compressed air, nitrogen, oxy		
			M12x1 4 pol. plug		
			EN61326-1	EN61326-2-3	
			Industrial environment	<i>CE</i>	
	Material	Enclosure	Polycarbonate		
		Probe tube	Stainless steel 1.4404		
		Probe head / sensor	Stainless steel 1.4404 / glass		
		Gauge mounting block	Aluminium anodized or stainle	ss steel 1.4404	

¹⁾ Factory setting of the output see manual.

Enclosure protection class

IP65

EE741 v1.0 / Modification rights reserved 175

²⁾ The tolerance specifications include the uncertainty of the factory calibration with a coverage factor k=2 (2 x standard deviation). The tolerance was calculated in accordance with EA-4/02 following the GUM (Guide to the Expression of Uncertainty in Measurement).

³⁾ The flow meter is factory adjusted at 7 bar (abs). At operating pressure other than 7 bar (abs), the error can be corrected by entering the actual system pressure via display menu or with EE-PCS configuration software.



Display (optional) _

The state-of-the-art LCD shows the current measured values and the overall consumption. The user specific device setup can be easily performed with the push buttons and intuitive menu guidance.

The display can be rotated in 90° increments with a push button for convenient orientation in any mounting position of the flow meter.

The EE741 without display can be configured by the user via USB interface with the free EE-PCS product configuration software.





Thread R_p or NPT

1/2"

3/4"

Dimensions (mm/inch)





Connection diagram.



M12 plug on device

Analogue/switch/ pulse output

1...V+

2...Output 1

3...GND

4...Output 2

Modbus RTU

1...V+

2...RS485 A (=D+)

3...GND

4...RS485 B (=D-)

M-Bus / Meter-bus

1...V+

2...M-Bus 3...GND

4...M-Bus

The output signal is freely selectable and scalable by the user:

Output 1: Analogue [mA] or switch

Output 2: Pulse or switch

Accessories

- Inlet and outlet path BSP thread, stainless steel, for mounting block $\,$ DN15 $\,$

DN15 HA070215 DN20 HA070220 DN25 HA070225

Scope of supply _

EE741

- · EE741 according to ordering guide
- 1 x Allen key
- · 1 x USB cable
- · Operating instructions
- Inspection certificate according to DIN EN10204 3.1

Gauge mounting block:

Gauge mounting block incl. mounted sealing plug

176 v1.0 / Modification rights reserved EE741

Ordering information

A complete flow meter consists of a transmitter (Item 1) and a gauge mounting block (Item 2).

Ite	m 1 - Transmitter			EE741-	EE741-
	Output	Analogue/switch/pulse	output	A6	
ø		RS485 Modbus RTU			J3P1
Hardware		M-Bus			J5P4
	Display	No display		No code	No code
		With display		D2	D2
	Accessories for electrical connection			No code	No code
	D	M12x1 straight socket	, can be assembled	AC2	AC2
	Pipe diameter (user selectable)	DN15		DN15	DN15
		DN20 DN25		DN20 DN25	DN20 DN25
	Output 1	Analogue output	4-20 mA	No code	DNZ5
	Output 1	Analogue output	0-20 mA	GA5	
		Switch output	0-20 IIIA	GA9	
	Outroot 0		(Only with Manager and a start 2 - Consumption)		
	Output 2	Pulse output Switch output	(Only with Measurand output 2 = Consumption)	No code GB9	
	Measurand output 1	Standard volume flow	V/a [Nm3/h]	No code	
	weasurand output 1	Standard volume now	V ₀ [Nm³/min]	MA84	
			V ([l/min]	MA85	
			V 0 [I/s]	MA86	
			V ₀ [SCFM]	MA87	
		Mass flow	m' [kg/h]	MA80	
		Wass now	m' [kg/min]	MA81	
_		Standard flow	v ₀ [Nm/s]	MA22	
Ę			v ₀ [SFPM]	MA23	
<u> </u>		Temperature	T [°C]	MA1	
<u></u>		·	T [°F]	MA2	
Software configuration	Measurand output 2	Consumption	Q ₀ [Nm ³] (Only for output 2 = Pulse output)	No code	
ပ		Standard volume flow	V ₀ [Nm ³ /h]	MB83	
/ar			V'₀ [Nm³/min]	MB84	
₹			V'₀ [l/min]	MB85	
လွ			V' ₀ [l/s]	MB86	
			V'₀ [SCFM]	MB87	
		Mass flow	m' [kg/h]	MB80	
			m' [kg/min]	MB81	
		Standard flow	v ₀ [Nm/s]	MB22	
		-	v ₀ [SFPM]	MB23	
		Temperature	T [°C]	MB1	
			T [°F]	MB2	
	Unit for process parameters	SI units [mbar, °C]		No code	No code
		US units [psi, °F]		U2	U2
	Medium	Air		No code	No code
		Nitrogen		FU2	FU2
		CO ₂		FU3	FU3
		Oxygen 1)		FU4	FU4
		Helium		FU6	FU6
		Argon		FU7	FU7

em 2 - Gauge mounting block		BSP-thread	NPT-thread
Aluminum gauge mounting block	DN15	HA079015	HA179015
	DN20	HA079020	HA179020
	DN25	HA079025	HA179025
Stainless steel gauge mounting block	DN15	HA078015	HA178015
	DN20	HA078020	HA178020
	DN25	HA078025	HA178025
Stainless steel gauge mounting block	DN15	HA081015	HA181015
for oxygen 1)	DN20	HA081020	HA181020
	DN25	HA081025	HA181025

¹⁾ The parts of the transmitter/mounting block in contact with the medium are oil and grease-free.

Order Example

Item 1 - Transmitter EE741-A6D2DN15

Output: Analogue/switch/pulse output Display: With display

Display: With display: Accessories for electrical connection: None Pipe diameter (user selectable): DN15

Unit for process parameters: SI units [mbar, °C]

Medium:

Item 2 - Gauge mounting block

HA079015

Aluminium gauge mounting block DN15

EE741 v1.0 / Modification rights reserved 177