
Energy Management Energy Analyzer Type EM111

CARLO GAVAZZI



- · Single phase energy analyzer
- Class 1 (kWh) according to EN62053-21
- Class B (kWh) according to EN50470-3
- Accuracy ±0.5% RDG (current/voltage)
- Direct current measurement up to 45AAC
- · Backlit LCD display with integrated touch key-pad
- Energy readout on display: 7 digit
- · Variable readout on display: 4 digit
- Energy measurement: kWh and kvarh (imported/ exported); kWh+ by 2 tariffs
- System variables, kW, kvar, V, A, PF, Hz, kWdmd, kWdmd peak
- Self power supply
- Dimensions: 1-DIN module
- Protection degree (front): IP51
- Pulse output (optional, by open collector PNP)
- RS485 Modbus port (optional)
- M-bus port (optional)
- Digital input (for tariff management)
- Easy connection or wrong current direction detection
- Certified according to MID Directive (option PF only): see "how to order" below

Product description

Single-phase energy analyzer with backlit LCD display with integrated touch keypad. Particularly indicated for active energy metering and for cost allocation in

applications up to 45 A (direct connection), with dual tariff management availability. It can measure imported and exported energy or be programmed to consider only

the imported one. Housing for DIN-rail mounting, with IP51 front degree protection. The meter is optionally provided with pulse output proportional to the active energy being

measured, RS485 Modbus port or M-bus port.

Certified according to MID Directive, Annex "B" + Annex "D" or Annex "B" + Annex "F" for legal metrology relevant to active electrical energy meters (see Annex MI-003 of MID). Can be used for fiscal (legal) metrology.

Type Selection

Range code		System		Power supply		Output	
AV8:	230VLN AC - 5(45)A (Direct connection) 120VLN AC - 5(45)A	1:	1-phase 2-wire	X:	Self power supply -30% +20% of the rated measuring input	O1: S1: M1:	pulse output RS485 Modbus port M-bus port
	(Direct connection)				voltage, 45 to 65Hz	IVI I .	M-Dus port

Option

PF: Certified according to MID Directive, Annex"B" + Annex "D" for legal metrology relevant to active electrical energy meters (see Annex MI-003 of MID). Can be used for fiscal(legal) metrology.

Measurement

B: Only the total positive energy meter is certified according to MID. Negative energy is not measured.

STANDARD

Not certified according to MID Directive. Cannot be used for fiscal (legal) metrology.

Type Selection

X:

none

Rang	e code	Syst	em	Pow	er supply	Outp	ut
AV8:	(Direct connection)	1:	1-phase 2-wire	X:	Self power supply -30% +20% of the rated measuring input voltage, 45 to 65Hz	O1: S1: M1:	pulse output RS485 Modbus port M-bus port
Optio	on						

Input specifications

Rated Inputs			digit
Current type	1-phase loads, direct	Touch key	2 (Enter and UP).
,.	connection	Max. and Min. indication	Max. 999 999.9
Current range	5(45)A		Min. 0.0
Nominal voltage	230VLN AC (AV8 option),	Memory energy storage	
3	120 VLN (AV7 option)	Energy	10^10 cycles. Energy value
Accuracy	, ,	0,	is saved every time the less
(@25°C ±5°C, R.H. ≤60%,			significant digit increases.
45 to 65 Hz)		Programming parameters	10^10 cycles. When a
AV7	Imin=0.25A; Ib: 5A, Imax:	3 1 3 1 1 1 1 1	parameter is modified, only
	45A; Un: 120VLN -30%		the relevant memory cell is
	+30%		overwritten
AV8	Imin=0.25A; Ib: 5A, Imax:	LEDs	Flashing red light pulses
7.00	45A; Un: 230VLN -30%	2250	according to EN50470-3,
	+20%		EN62052-11, 1000 imp./
Energies	12070		kWh (min. period: 90ms)
Active energy	Class 1 according to		Fix orange light: wrong
Active chergy	EN62053-21, and MID		current direction (only with
	Annex MI-003 Class B		"B" measurement selection)
	(Class B (kWh) according		B measurement selection)
	to EN50470-3)	Current overloads	
Reactive energy	Class 2 according to	Continuous	45A, @ 50Hz
Reactive energy	EN62053-23	For 10ms	1350 A
Start-up current:	20mA (AV7, AV8),	Voltage Overloads	
Start-up current.	-20mA (AV7, AV8),	Continuous	1.2 Un
	of negative current	For 500ms	2 Un
	Self-consumption is not	Input impedance	
	measured.	Voltage input 230VL-N	1.2 Mohm
Start up voltage		Voltage input 120VL-N	1.2 Mohm
Start-up voltage	84VLN (AV7), 161VLN	Current inputs: 5(45) A	< 0.5 VA
Resolution	(AV8) Display/serial		
Resolution	communication		
Current	0.1/0.001 A		
	0.1/0.001 A 0.1/0.1 V		
Voltage Power	0.1/0.1 V 0.01 kW or kVar/ 0.1 W or		
Power			
Fraguenov	var		
Frequency PF	0.1 Hz/0.1Hz		
	0.01/0.001		
Energies (positive)	0.01 kWh or kvarh / 0.1		
	kWh or kvarh		
Energies (negative)	0.01 kWh or kvarh / 0.1		
Energy additional errors	kWh or kvarh		
-	According to EN62052 24		
Influence quantities Temperature drift	According to EN62053-21 ≤200ppm/°C		
Sampling rate			
Sampling rate	4096 samples/s @ 50Hz		
	4096 samples/s @ 60Hz		
Display and touch key-pad			
Type	Backlit LCD, 7-digit, h 6		
	mm		
Read-out	Energy: 8 digit. Variables: 4		

Digital input specifications

Digital inputs

Function

Number of inputs Contact measurement voltage Input impedance Contact resistance Free of voltage contact Tariff management (switch between t1-t2)

1 5 V 1kohm

1kohm, close contact 100kohm, open contact Overload

In case a voltage is erroneously applied to the digital input, the input is not damaged up to 30 VAC/DC.

Output specifications

RS485 serial port RS485 by screw connection. For communication **Function** of measured data, programming parameters Protocol ModBus RTU (slave function) Baud rate 9.6, 19.2, 38.4, 57.6, 115.2 kbaud, even or no parity, Address 1 to 247 (default: 01) 1/8 unit load. Maximum 247 Driver input capability transceivers on the same bus. Data refresh time 1sec 50 words available in 1 Read command read command Rx/Tx indication Rx segment on display is shown when a valid

x indication

Rx segment on display is shown when a valid Modbus command is sent to that specific meter

Tx segment on display is shown when a valid Modbus reply is sent back to the master

M-bus port M-bus by screw connection.

Function For communication of measured data
Protocol M-bus according to EN13757-1

Baud rate 0.3, 2.4, 9.6 kbaud

Meters in the M-bus network 250
Primary address Selectable

Secondary address
Univocally defined in each unit

9999

Identification number range fro

unit from 5000 0000 to 6999

Other

Available functions: wild card, header, initialisation SND_NKE, and req_udr management. Management of primary address modification via M-bus and reset of partial energy via M-bus available. VIF, VIFE, DIF and DIFE: see protocol

Static output

Purpose For pulse output

proportional to the active energy (kWh)

Pulse rate Selectable in multiple of

100

Max 1000 or 3000 kWh according to pulse ON

duration

Pulse ON duration Selectable: 30ms or 100 ms according to EN62052-

31

Output type Open collector PNP Load V_{ON} 2.5 VAC/DC max. 100mA

ON 2.5 VAC/DC max. 100mA

V_{OFF} 260 VAC max.

General specifications

Operating temperature	-25 to +65 °C, indoor, (R.H. from 0 to 90% non-	Standard compliance Safety	EN62052-11
	condensing @ 40°C)	Metrology	EN62053-21, EN50470-3
Storage temperature	-30°C to +80°C (R.H. <	Approvals	CE, MID (PF option only)
	90% noncondensing @	Connections	
	40°C)	Cable cross-section area	Measuring inputs: max. 6
Overvoltage category	Cat. III		mm² with/without metallic
Insulation (for 1 minute)	4000 VAC RMS between measuring inputs and digital/serial output (see table) 4000 VAC RMS	Other terminals	cable ferrule; Max. screw tightening torque: 1.1 Nm 1.5 mm², Min./Max. screws tightening torque: 0.4 Nm
Dielectric strength	4000 VAC RMS for 1 minute	Housing Dimensions (WxDxH) Material	17,5 x 63 x 91,5 mm Noryl, self-extinguishing:
EMC	According to EN62052-11		UL 94 V-0
Electrostatic discharges	15kV air discharge;	Sealing covers	Included
Immunity to irradiated		Mounting	DIN-rail
electromagnetic fields	Test with current: 10V/m from 80 to 2000MHz;	Protection degree	
	Test without any current:	Front	IP51
	30V/m from 80 to	Screw terminals (cable inputs)	IP20
	2000MHz;	Weight	Approx. 80 g (packing
Burst	On current and voltage measuring inputs circuit: 4kV		included)
Immunity to conducted			
disturbances	10V/m from 150KHz to 80MHz		
Surge	On current and voltage measuring inputs circuit: 4kV;		
Radio frequency	According to CISPR 22		

Power supply specifications

0.16		D	4.004 < 0) (A
Self power supply		Power consumption	≤ 1.0W, ≤ 8VA
AV8	230VAC VL-N, -30% +20%		
	50/60Hz		
AV7	120VAC VL-N, -30% +30%		
	50/60Hz		

Insulation (for 1 minute) between inputs and outputs


	Measuring input	Digital or serial output	Digital input
Measuring input	-	4 kV	4 kV
Digital or serial output	4 kV	-	-
Digital input	4 kV	-	-

MID "Annex MI-003" compliance (PF option only)


Accuracy	0.9 Un ≤ U ≤ 1.1 Un; 0.98 fn ≤ f ≤ 1.02 fn; fn: 50 Hz; cosφ: 0.5 inductive to 0.8 capacitive. Class B Considering listed lb or In values
Operating temperature	-25 to +55°C (13°F to 131°F) (R.H. from 0 to 90% non-condensing @ 40°C)
EMC compliance	E2
Mechanical compliance	M2

Accuracy (according to EN50470-3 and EN62053-23)

kWh, PF=accuracy (RDG) depending on the current



kvarh, accuracy (RDG) depending on the current



Display pages

No	Variable	"Full" mode	"Easy" mode	Note
0	kWh+ (imported)	Х	Х	In PF version (MID) this is the only certified energy meter. In X version with Measurement menu set to "A", this is considering the total energy without considering the current direction.
1	kWh- (exported)	Х	Χ	In PFB version and in X version with Measurement menu set to "B"
2	kW	Х	Х	
3	V	X	Х	
4	A	X	Х	
5	PF	X		
6	Hz	X		
7	kvarh+ (imported)	X		In X version with Measurement menu set to "A", this is considering the total positive reactive energy without considering the current direction.
8	kvarh- (exported)	Х		In PFB version and in X version with Measurement menu set to "B"
9	kvar	Х		
10	kW dmd	X		
11	kW dmd peak	Х		
12	kWh (t1)	Х	Х	Only relevant to kWh+, with Tariff menu set to ON
13	kWh (t2)	Х	Х	Only relevant to kWh+, with Tariff menu set to ON

X= available

List of available menus

Menu name and desc	ription	Range	Default setting
PASS	Password request	From 0000 to 9999	0000
nPASS	New password	From 0000 to 9999	0000
Measure Measurement type (A=easy connection; B=bidirectional, imported and exported energy). Not available in PFA and PFB versions (MID)		A; b	A
P int	Integration time for Wdmd calculation	1 to 30 min	1
Mode	Selection of complete or simplified set of variables on display	Full or Easy	Full
Tariff	Tariff enabling	Yes/No	No
PULSE (O1 option)	Selection of pulse ON duration	30 or 100 ms	30
	Selection of the pulse rate	100 to 1000 (if duration is 100ms) or to 3000 (if 30 ms)	100
Address (S1 option)	Modbus serial address	1 to 247	01
Baud (S1)	Modbus baud rate	9.6; 19.2; 38.4; 57.6, 115.2 kbps	9.6
Parity (S1)	Modbus parity	No/even	No
Prl Add (M1 option)	M-bus primary address	1 to 250	1
Baud (M1) M-bus baud rate		0.3; 2.4; 9.6 kbps	2.4
RESEt Allow the reset of tariff meters and W dmd peak and of the kWh/kvarh partial meter available only via serial communication		Yes/No	No
End	Exit to measuring mode		

Note: after the confirmation of a new parameter value, the value is stored in the memory without the need to exit the programming mode.


Additional available information on the display (*)


Туре	Description	Note
Info page 1	YEAr (2013)	Year of production
Info page 2	SErIAL (dddnnnA)	Serial number (ddd= day of the year; nnn=progressive number; A= production line, internal use only)
Info page 3	rEV (A.01)	Firmware revision
Info page 4	MEASurE	Measurement type
Info page 5	P int	Integration time for Wdmd calculation
Info page 6	ModE	Set of variables on display
Info page 7	tArIFF	Tariff enabling
Info page 8 (O1)	PULSE	Pulse ON duration
		Pulse rate
Info page 8 (S1)	AddrESS	Modbus serial address
Info page 9 (S1)	bAud	Modbus baud rate
Info page 10 (S1)	PArItY	Modbus parity
Info page 8 (M1)	Prl Add	M-bus primary address
Info page 9 (M1)	bAud	M-bus baud rate


^(*) can be reached by pressing simultaneously the 2 touch keys


Wiring diagrams













use a signal repeater. Maximum 247 transceivers on the same bus.



Front panel description



1. Display

Backlit LCD display with touch key-pad.

Upper part: enter Lower part: UP

Scroll in up direction: UP Scroll in down direction: DOWN

2. LED

LED proportional to kWh reading

3. Serial number and MID data

Area reserved to serial number and MID-relevant data in PF versions

Dimensions (mm)

