ED-004 Ethernet to Digital I/O +RS232

4 Digital I/O Lines with RS232 Serial Port


brainboxes

www.brainboxes.com

- 4 Digital Ports independently can be In or Out
- 1 RS232 Serial Port
- 1 Ethernet Port
- User friendly software interface Simple web based configuration, monitoring and control
- Software APIs for VB, C# and more








GLOBAL

ED-004

brainboxes www.brainboxes.com

Ethernet to Digital I/O +RS232

| Integrate with popular software packages or use with our free APIs | Ethernet Port | Easy Wire F | Removable screw terminal blocks |
|--|---|--|---|
| LED status ligh | its | | Wide Range Input Power: +5VDC to +30VDC |
| Wall mount holes compatible with MK-048 DIN mount clips | ETHERNET | FY - RK - RT - | IP30 Non-conducting polyamide case |
| View from webpage - no software required | REMOTE I/O RS232 PORT | DIGITAL I/O | -10°C to +60°C/+14°F to +140°F temperature range |
| | 70 TO 00 TO | 1 6 103 1 6 102 1 6 102 1 6 100 1 6 100 1 6 100 | Supports Modbus TCP or ASCII commands |
| | RS232 Serial Port | 4 Digital I/O | Lines |
| Connectors | | | |
| Screw Terminals | 3 way x 0.2inch/5.08 | mm and 10 way | x 0.2inch/5.08mm pitch |
| | 0.150 inch, 3.81mm, 20 pins, 12+8 screw terminals, #26 - #16 AWG, 0.14mm ² -1.3mm ² | | |
| Power Supply | | | |
| Power Supply input | Unregulated +5V to + | 30Volts DC, reve | rse polarity protection |
| Isolation | 1500VRMS Magnetic i | isolation from Eth | nernet |
| Environmental | | | |
| Operating Temperature | -10°C to +60°C / +14 | °F to +140°F | |
| Storage Temperature | -10°C to +70°C / +14 | °F to +158°F | |
| Ambient Relative Humidity | 5 to 95% (non-conden | ising) | |
| Magjack LED Information | | | |
| | 5 | nnection establis | hed |
| | Flashing Green Da | ta communicatio | n |
| Speed LED | Green 10 | 0Base-Tx | |
| | Unlit 10 | Base-T | |
| Ethernet | | | |
| Ethernet Port | RJ45 jack, 10/100Mh: | z autosensing, cr | ossover auto sensing (Auto MDIX) |
| Protection | 1,500 Volts magnetic | | • |
| Housing | IP-30 rated non-condu | ucting polyamide | case |



Terminal Block Pin Outs

| PIN | FUNCTION |
|-----|----------|
| 1 | TxD |
| 2 | RxD |
| 3 | RTS |
| 4 | CTS |
| 5 | GND |
| 6 | DIO 3 |
| 7 | DIO 2 |
| 8 | DIO 1 |
| 9 | DIO 0 |
| 10 | GND |

Ethernet Port Pin Outs

| PIN | FUNCTION |
|-----|-----------|
| 1 | RD+ / TD+ |
| 2 | RD- / TD- |
| 3 | TD+ / RD+ |
| 4 | NC |
| 5 | NC |
| 6 | TD- / RD- |
| 7 | NC |
| 8 | NC |

| Power 7 | Ferminal | Pin | Outs |
|---------|----------|-----|------|
| | | | |

| PIN | FUNCTION | |
|-----|------------------|--|
| 1 | +V | |
| 2 | -V | |
| 3 | Functional Earth | |

Lifetime Warranty and Support:

We can help with every aspect of your project, from getting you up and running to custom application.

ED-004

Ethernet to Digital I/O +RS232

| Digital Channels - 4 Ports individually selectable as Inputs or Outputs | | |
|---|---|--|
| Inputs | | |
| NPN/PNP | Individually jumper selectable pull up for NPN, active low, type sensors and pull down for PNP, active high, type sensors | |
| Logic Level 0: | 0V to +1V | |
| Logic Level 1: | +2V to +30V | |
| Latched Inputs: | Triggered by user programmable positive or negative edges, stays true until acknowledged | |
| Counter Inputs: | User programmable- counts positive or negative transitions 0-65335 | |
| Outputs | | |
| Maximum output current | Sinks up to 0.85 Amp per pin, 30V max load Max combined load 3.4 Amps per ED device | |
| Characteristic: | Open drain output, protected MosFET intelligent short circuit protection up to 36V Over temperature shutdown :175°C typical 150°C min | |
| Maximum output load Voltage | 30V | |
| ESD Production | 16kV | |
| Quick-Stop function | When a user programmable input transitions to a preconfigured high or low state then all outputs go to a user programmable known good state | |
| Serial Port - RS232 | | |
| Baud Rate | From 110 - 1 MegaBaud - Any custom Baud rate accepted | |
| Data Bits | 5,6,7 or 8 | |
| Parity | Odd, Even, None, Mark or Space | |
| Stop Bits | 1 or 2 | |
| Flow Control | RTS/CTS, XON/XOFF | |
| Tx/Rx Modes | Point to Point | |
| Power Supply | | |
| Power Supply input | Unregulated +5V to +30Volts DC, reverse polarity protection | |
| Isolation | 1500VRMS Magnetic isolation from Ethernet | |
| Power Consumption | 2.5 Watts Max : 220 mAmps@+5VDC/36mAmps@+30VDC | |

Software

orainboxes

www.brainboxes.com

OS CompatibilityBrainboxes' software provides a TCP or Serial COM port interface. All
software versions and updates available to download from our website.MicrosoftLegacy COM port drivers for Microsoft OS up to latest Windows 11

Other

TCP and web browser interface for other OSs & Linux, e.g. Android, Raspberry Pi



| Boost.IO Manager | Lets you find, install and upgrade devices |
|----------------------------|---|
| Industry Standard Packages | The COM port based driver means devices are compatible with popular packages such as: LabView, MATLAB, Agilent VEE. So you can continue to get value from your existing development and process control system. |
| Software Platforms | APIs and sample program code for: Microsoft .NET, C#, Visual Basic, C++, JavaScript, PHP, Java, Objective-C, Python and more - www.brainboxes.com |



Modbus

Device works as a Modbus TCP server. Modbus TCP can be used on the input and output lines.

| | Modbus access type | Supported Modbus function codes | Logical address | 984 style address | IEC 61131 address |
|--------------------------|-----------------------|---------------------------------|-----------------|-------------------|----------------------|
| Read DI counter values | Holding register | 3 | 0x0000 | 40001 | %MW0 |
| Clear DI counters | Coil | 5, 15 | 0x0200 | 00513 | %M512 |
| Set/read digital outputs | Coil | 1, 5, 15 | 0x0000 | 00001 | %M0 |

ASCII

The ED device's webpage has an interactive ASCII console where any command can be entered and it is immediately executed showing the device's response.

| \$01M | read the name of device address 01 |
|-----------|---|
| !01ED-588 | device 01 replies that its name is ED-588 |
| \$01F | read firmware version number of device address 01 |
| !012.54 | firmware version of device 01 is 2.54 |

Full command tables can be found in the device manual









_ .

UK +44 (0)151 220 2500 // USA +1 855 958 2502 www.brainboxes.com // sales@brainboxes.com

| ED-004 | Ethernet to Digital I/O +RS232 | | |
|------------------------|---|--|--|
| Packaging Information | | | |
| Packaging | Microsoft signed drivers & utilities, Quick Start Guide, Device | | |
| Packaged Weight | 0.222 kg, 7.83 ounces | | |
| Packaged Dims | 160x135x49 mm, 6.3x5.3x1.9 inches | | |
| GTIN Universal Code | 837324009859 | | |
| Approvals | | | |
| Industry Approvals | Microsoft Certified Gold Partner, WEEE, RoHS, AEO (C-TPAT), CE, UKCA | | |
| Product Support | | | |
| Warranty | Lifetime - online registration required | | |
| Support | Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team | | |
| Additional Information | | | |
| OEM option | Available for bulk buy OEM | | |
| Made In | Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards 'Manufacturer of the Year' | | |
| Customisable | Brainboxes operate a 'Perfect Fit Custom Design' policy for volume users. More info:sales@brainboxes.com | | |



PW-600 Power supply with connectors for UK, USA, EU and AUS mains socket. 'Tails' are suitable for connecting to screw terminal blocks.



MK-048 DIN Rail Mounting Kit Enables device to be clipped onto a DIN rail.

