

UK +44 (0)151 220 2500 // USA +1 855 958 2502 www.brainboxes.com // sales@brainboxes.com

ED-593 Ethernet to 8x Thermocouple


8 Channel Thermocouple Input

- \cdot $\,$ Factory floor process control and automation
- 8 Channel Differential Thermocouple Inputs
- Measurement Range: -265°C to +1820°C / -445°F to 3308°F
- 1 Ethernet Port
- -40°C to +80°C/-40°F to +176°F product operating temp. range
- Covers most standard thermocouple types
- Software APIs for VB, C# and more










Wide range input power: +5VDC to +30VDC

Connectors		
Screw Terminals	3.5mm pitch	
Wire Thickness	#22 - #14, 0.5mm ² -2.5mm ²	
Environmental		
Operating Temperature	-40°C to +80°C /	′ -40°F to +176°F
Storage Temperature	-40°C to +85°C / -40°F to +185°F	
Ambient Relative Humidity	5 to 95% (non-condensing)	
Magjack LED Information		
Link/Activity LED	Solid green	Connection established
	Flashing Green	Data communication
Speed LED	Green	100Base-Tx
	Unlit	10Base-T
Ethernet		
Ethernet Port	RJ45 jack, 10/100Mhz autosensing, crossover auto sensing (Auto MDIX)	
Protection	1,500 Volts Magnetic Isolation On Port	
Housing	IP-20 rated non-conducting polyamide case	



Terminal Block Pin Outs

Terminal Block	Pin 1	Pin 2	Pin 3	Pin 4	Pin 5
Yellow	AGND	TC 0-	TC 0+	TC 1-	TC 1+
Orange	AGND	TC 2-	TC 2+	TC 3-	TC 3+
Grey	GND	RS-485 D-	RS-485 D+	RS-485 D+	RS-485 D-
Green	AGND	TC 4-	TC 4+	TC 5-	TC 5+
Blue	AGND	TC 6-	TC 6+	TC 7-	TC 7+
Black	-V	+VA	+VB	-V	Func GND
	Pow	er Input +	5V to +30V D	C	

Ethernet Port Pin Outs

PIN	FUNCTION
1	RD+ / TD+
2	RD- / TD-
3	TD+ / RD+
4	NC
5	NC
6	TD- / RD-
7	NC
8	NC

Lifetime Warranty and Support:

We can help with every aspect of your project, from getting you up and running to custom application.

UK +44 (0)151 220 2500 // USA +1 855 958 2502 www.brainboxes.com // sales@brainboxes.com

ED-593

Ethernet to 8x Thermocouple

Thermocouple Channels - 8 Inputs

brainboxes

www.brainboxes.com

Inputs	
IO Protocols	DCON ASCII over TCP or COM Port; Modbus TCP
Description	8 thermocouple sensor inputs - individually configurable for thermocouple type
Isolation	Yes Analogue inputs power, network and RS-485 ports are all isolated from each other Analogue input channels are not isolated from each other
Thermocouple types	Type J, K, T, E, R, S, B and N
Measurement range	-265°C to +1820°C/-445°F to 3308°F/8K to 2093K, depending on thermo- couple type
Input Resolution	16 bit resolution
Measurement Accuracy	0.16% of primary range
Measurement rate	Open-Wire Detection disabled - 6 measurements per second, divided between all enabled inputs Open-Wire Detection enabled - 4 measurements per second, divided between all enabled inputs
Low Noise	CMRR > 120dB
Rejects Mains Hum	NMRR > 75dB at 50Hz and 60Hz

Serial Expansion Port - RS485

Half Duplex RS485 port allows connection and control of industry standard NuDAM, eDAM and ADAM modules using ASCII protocols.

Power Supply	
Power Supply input	Unregulated +5VDC to +30VDC, reverse polarity protection
Isolation	1500VRMS Magnetic isolation from Ethernet
Power Consumption	2.5 Watts Max : 500 mAmps@+5VDC/83 mAmps@+30VDC



Software

brainboxes

www.brainboxes.com

OS Compatibility	Brainboxes' software provides a TCP or Serial COM port interface. All software versions and updates available to download from our website.
Microsoft	Windows 8, Windows 8.1, Windows 10, Windows 11 Windows Server 2016, 2019, 2022
Other	TCP and web browser interface for other OSs & Linux, e.g. Android, Raspberry Pi Image: Comparible Comparible Image: Comparible Comparible Image: Comparible Comparible
Boost.IO Manager	Lets you find, install and upgrade devices
Industry Standard Packages	The COM port based driver means devices are compatible with popular packages such as: LabView, MATLAB, Agilent VEE. So you can continue to get value from your existing development and process control system.
Software Platforms	APIs and sample program code for: Microsoft .NET, C#, Visual Basic, C++, JavaScript, PHP, Java, Objective-C, Python and more - www.brainboxes.com
	Matlas



Modbus MODBUS Support coming soon...

ASCII

The ED device's webpage has an interactive ASCII console where any command can be entered and it is immediately executed showing the device's response.

\$01M	read the name of device address 01
!01ED-588	device 01 replies that its name is ED-588
\$01F	read firmware version number of device address 01
!012.54	firmware version of device 01 is 2.54

Full command tables can be found in the device manual:



www.brainboxes.com/ED-593



UK +44 (0)151 220 2500 // USA +1 855 958 2502 www.brainboxes.com // sales@brainboxes.com

ED-593

Ethernet to 8x Thermocouple

Packaging Information Packaging N	
Packaging M	
ruckugnig	Aicrosoft signed drivers & utilities, Quick Start Guide, Device
Packaged Weight 0	0.192 kg, 6.77 ounces
Packaged Dims 1	60x135x49 mm, 6.3x5.3x1.9 inches
GTIN Universal Code 8	337324004007
Approvals	
	METLABS E112324 complies with UL62368-1, CSA C22.2, No. 62368-1 Microsoft Certified Gold Partner, WEEE, RoHS, AEO (C-TPAT), UKCA, CE
Product Support	
Warranty L	ifetime - online registration required
	ifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team
Additional Information	
OEM option A	Available for bulk buy OEM
	Manufactured in the UK by Brainboxes Winner 2005 European Electronics ndustry Awards 'Manufacturer of the Year'
	Brainboxes operate a 'Perfect Fit Custom Design' policy for volume users. More info:sales@brainboxes.com



ED Range

Remote I/O products available in a range of formats and specifications

www.brainboxes.com



PW-600 Power supply with connectors for UK, USA, EU and AUS mains socket. 'Tails' are suitable for connecting to screw terminal blocks.



PW-650 Power supply with USB connector and pre-wired screw terminal block. Suitable for use with 5V USB ports.



MK-588 6 coloured PCB connectors. Individually numbered pins; 5 x 3.5mm pitch screw connections with tension sleeve.