

EE160

HVAC Humidity and Temperature Sensor

The EE160 is optimized for cost effective, accurate measurement of relative humidity (RH) and temperature (T) in building automation.

Reliable

Best long-term stability even in polluted or aggressive environment is ensured by the encapsulated measurement electronics inside the probe and E+E proprietary protection of the sensing element.

Versatile

The measured data is available on two voltage or current (2-wire) outputs, or on the RS485 interface with BACnet MS/TP or Modbus RTU protocol. Additionally, the EE160 features a passive T output.


Functional Design

EE160 is available for wall or duct mount. The IP65 / NEMA 4 enclosure minimizes installation costs and provides outstanding protection against contamination and condensation.

Comfortable Configuration and Adjustment

With an optional configuration adapter and the free EE-PCS Product Configuration Software, the user can set the RS485 interface parameters, the output scaling and perform one or two point adjustment for RH and T.

Features



Protective Sensor Coating

The E+E proprietary sensor coating is a hygroscopic layer applied to the HCT01 humidity sensing element. The coating substantially extends sensor life-time and ensures optimal measurement performance in corrosive environment (salts, off-shore applications). Additionally, it improves the long term stability in dusty, dirty or oily applications by preventing stray impedances caused by deposits on the active sensor surface or on the electrical connections.



Technical Data

leasurands Relative humidity						
Accuracy ¹⁾ at 20 °C	±2.5 % RH					
Temperature dependency, typ.	±0.03 % RH/°C					
Temperature						
Accuracy at 20 °C	±0.3 °C (±0.54 °F)					
Outputs						
Analogue output	0 - 10 V	0 < I _∟ < 1 mA	or			
(RH: 0100%; T: see ordering guide)	4 - 20 mA (2-wire	$R_{L} < 500 \text{ Ohr}$	n			
Digital interface	RS485 (EE160 = 1 unit load)					
Protocol	Modbus RTU or BACnet MS/TP					
Passive T-sensor	4-wire connection, see ordering guide					
General						
Sensing element	E+E HCT01 with E+E proprietary coating					
Power supply						
for 0 - 10 V / RS485	15 - 35 V DC or 24 V AC ±20 %					
for 4 - 20 mA	$10 \text{ V} + \text{R}_{\text{L}} \text{ x } 20 \text{ mA} < \text{U}_{\text{V}} < 35 \text{ V DC}$					
Current consumption, typ.		4 - 20 mA output	0 - 10 V output	RS485		
	24V DC supply	max. 40 mA	5 mA	5 mA		
	24V AC supply	-	13 mA _{rms}	15 mA _{rms}		
Connection	, -					
Housing material						
Protection class	IP65 / NEMA 4					
Cable gland	M16x1.5					
Electromagnetic compatibility	EN 61326-1					
	EN 61326-2-3					
Working range	g range -4060 °C (-40140 °F) / 1095 % RH -2060 °C (-4140 °F) / 1090 % RH, non-condensing					


¹⁾ Traceable to international standards, administrated by NIST, PTB, BEV,...

EE160 v2.4/ Modification rights reserved 55

The accuracy statement includes the uncertainty of the factory calibration with an enhancement factor k=2 (2-times standard deviation). The accuracy was calculated in accordance with EA-4/02 and with regard to GUM (Guide to the Expression of Uncertainty in Measurement).



Dimensions



Ordering Guide

				EE160-		
Hardware configuration	Model	RH + T	M1		M1	
		RH + T + T passive		M8		
	Туре	Wall mount		T1		
	туре	Duct mount		T2		
		0 - 10 V		A3		
	Output	4 - 20 mA	A	A6		
		RS485				
	T sensor passive ¹⁾	Pt100 DIN A		TP1		
		Pt1000 DIN A		TP3		
		NTC10k		TP5		
		Ni1000, TK6180		TP9		
	Filter	Membrane		no code		
Setup analgoue outputs	Relative humidity	RH, 0100 %RH	no c	no code		
	Temperature ²⁾	T [°C]	no c	no code		
	Temperature /	T [°F]	ME	MB2		
	Scale T low	-40		no code		
		Value	SBLV	SBL <i>Valu</i> e		
	Scale T high	60		no code		
		Value	SBHV	SBH <i>Valu</i> e		
Setup RS485	Protocol	Modbus RTU ³⁾			P1	
		BACnet MS/TP ⁴⁾			P3	
		9600			BD5	
		19200			BD6	
	Baud rate	38400			BD7	
		57600 ⁵⁾			BD8	
Se		76800 ⁵⁾			BD9	
	Units ²⁾ Metric (SI)				no code	
		Non-metric (US/GB)			U2	

- With Model M8 only / T sensor. Details see www.epluse.com/R-T_Characteristics.
 Can not be changed with EE-PCS.
- 3) Modbus map and configuration guide see user manual or Modbus application note at www.epluse.com/ee160.
- 4) Product Implementation Conformance Statement (PICS) available at www.epluse.com/ee160. 5) For BACnet MS/TP only.

Order Examples

EE160-M8T1A6TP1SBL-10SBH50 EE160-M1T2J3P1BD5U2 RH + T + T passive Model: Model: RH + T Wall mount Type: Type: Duct mount 4 - 20 mA Output: Output: RS485 Passive T Sensor: Pt100 DIN A Filter: Membrane Filter: Membrane Protocol: Modbus RTU Output RH: 0...100 %RH Baudrate: 9600 Output T: T [°C] Units: Non-metric -10 Scale T low: Scale T high: 50

Accessories (see data sheet "Accessories").

Product configuration software Power supply adapter Protection cap for 12 mm probe USB configuration adapter for EE160-M1TxJ3 (RS485) Product configuration adapter for EE160-MxTxAx (analogue output) EE-PCS (free download: www.epluse.com/EE160) V03 HA010783

HA011066 see datasheet EE-PCA

56 **EE160** v2.4 / Modification rights reserved