

Panasonic

ERJ2RKF****X Precision Thick Film Chip Resistors KIT

Order No : ERJ2RK-KIT

- | | | | |
|-----------------------|---------------------|-----------------------------|-------------|
| • Technology | Thick film | • Resistor Values | 122 |
| • Package Inch / Size | 0402 / 1005 | • Resistor Pieces per value | 200 |
| • Series | E24 + Jumper | • Operating Temperature | -55 to +155 |
| • Resistor Range | 10Ω to 1MΩ + Jumper | • Temperature Coefficient | ±100 ppm |
| • Tolerance | ±1 % | | |
| • Maximum Wattage | 0.1 W | | |
| • Maximum Voltage | 50 V | | |



Binder Dim. : 250x300x35 mm
Weight : 1300 g

KIT Content Listings

No	Manufacturer part number	Resistance
1	ERJ2GE0R00X	0 Ω
2	ERJ2RKF10R0X	10 Ω
3	ERJ2RKF11R0X	11 Ω
4	ERJ2RKF12R0X	12 Ω
5	ERJ2RKF13R0X	13 Ω
6	ERJ2RKF15R0X	15 Ω
7	ERJ2RKF16R0X	16 Ω
8	ERJ2RKF18R0X	18 Ω
9	ERJ2RKF20R0X	20 Ω
10	ERJ2RKF22R0X	22 Ω
11	ERJ2RKF24R0X	24 Ω
12	ERJ2RKF27R0X	27 Ω
13	ERJ2RKF30R0X	30 Ω
14	ERJ2RKF33R0X	33 Ω
15	ERJ2RKF36R0X	36 Ω
16	ERJ2RKF39R0X	39 Ω
17	ERJ2RKF43R0X	43 Ω
18	ERJ2RKF47R0X	47 Ω
19	ERJ2RKF51R0X	51 Ω
20	ERJ2RKF56R0X	56 Ω
21	ERJ2RKF62R0X	62 Ω
22	ERJ2RKF68R0X	68 Ω
23	ERJ2RKF75R0X	75 Ω
24	ERJ2RKF82R0X	82 Ω
25	ERJ2RKF91R0X	91 Ω
26	ERJ2RKF1000X	100 Ω
27	ERJ2RKF1100X	110 Ω
28	ERJ2RKF1200X	120 Ω
29	ERJ2RKF1300X	130 Ω
30	ERJ2RKF1500X	150 Ω
31	ERJ2RKF1600X	160 Ω
32	ERJ2RKF1800X	180 Ω
33	ERJ2RKF2000X	200 Ω
34	ERJ2RKF2200X	220 Ω
35	ERJ2RKF2400X	240 Ω
36	ERJ2RKF2700X	270 Ω
37	ERJ2RKF3000X	300 Ω
38	ERJ2RKF3300X	330 Ω
39	ERJ2RKF3600X	360 Ω
40	ERJ2RKF3900X	390 Ω
41	ERJ2RKF4300X	430 Ω
42	ERJ2RKF4700X	470 Ω
43	ERJ2RKF5100X	510 Ω
44	ERJ2RKF5600X	560 Ω
45	ERJ2RKF6200X	620 Ω
46	ERJ2RKF6800X	680 Ω
47	ERJ2RKF7500X	750 Ω
48	ERJ2RKF8200X	820 Ω
49	ERJ2RKF9100X	910 Ω
50	ERJ2RKF1001X	1 kΩ

No	Manufacturer part number	Resistance
51	ERJ2RKF1101X	1.1 kΩ
52	ERJ2RKF1201X	1.2 kΩ
53	ERJ2RKF1301X	1.3 kΩ
54	ERJ2RKF1501X	1.5 kΩ
55	ERJ2RKF1601X	1.6 kΩ
56	ERJ2RKF1801X	1.8 kΩ
57	ERJ2RKF2001X	2 kΩ
58	ERJ2RKF2201X	2.2 kΩ
59	ERJ2RKF2401X	2.4 kΩ
60	ERJ2RKF2701X	2.7 kΩ
61	ERJ2RKF3001X	3 kΩ
62	ERJ2RKF3301X	3.3 kΩ
63	ERJ2RKF3601X	3.6 kΩ
64	ERJ2RKF3901X	3.9 kΩ
65	ERJ2RKF4301X	4.3 kΩ
66	ERJ2RKF4701X	4.7 kΩ
67	ERJ2RKF5101X	5.1 kΩ
68	ERJ2RKF5601X	5.6 kΩ
69	ERJ2RKF6201X	6.2 kΩ
70	ERJ2RKF6801X	6.8 kΩ
71	ERJ2RKF7501X	7.5 kΩ
72	ERJ2RKF8201X	8.2 kΩ
73	ERJ2RKF9101X	9.1 kΩ
74	ERJ2RKF1002X	10 kΩ
75	ERJ2RKF1102X	11 kΩ
76	ERJ2RKF1202X	12 kΩ
77	ERJ2RKF1302X	13 kΩ
78	ERJ2RKF1502X	15 kΩ
79	ERJ2RKF1602X	16 kΩ
80	ERJ2RKF1802X	18 kΩ
81	ERJ2RKF2002X	20 kΩ
82	ERJ2RKF2202X	22 kΩ
83	ERJ2RKF2402X	24 kΩ
84	ERJ2RKF2702X	27 kΩ
85	ERJ2RKF3002X	30 kΩ
86	ERJ2RKF3302X	33 kΩ
87	ERJ2RKF3602X	36 kΩ
88	ERJ2RKF3902X	39 kΩ
89	ERJ2RKF4302X	43 kΩ
90	ERJ2RKF4702X	47 kΩ
91	ERJ2RKF5102X	51 kΩ
92	ERJ2RKF5602X	56 kΩ
93	ERJ2RKF6202X	62 kΩ
94	ERJ2RKF6802X	68 kΩ
95	ERJ2RKF7502X	75 kΩ
96	ERJ2RKF8202X	82 kΩ
97	ERJ2RKF9102X	91 kΩ
98	ERJ2RKF1003X	100 kΩ
99	ERJ2RKF1103X	110 kΩ
100	ERJ2RKF1203X	120 kΩ

No	Manufacturer part number	Resistance
101	ERJ2RKF1303X	130 kΩ
102	ERJ2RKF1503X	150 kΩ
103	ERJ2RKF1603X	160 kΩ
104	ERJ2RKF1803X	180 kΩ
105	ERJ2RKF2003X	200 kΩ
106	ERJ2RKF2203X	220 kΩ
107	ERJ2RKF2403X	240 kΩ
108	ERJ2RKF2703X	270 kΩ
109	ERJ2RKF3003X	300 kΩ
110	ERJ2RKF3303X	330 kΩ
111	ERJ2RKF3603X	360 kΩ
112	ERJ2RKF3903X	390 kΩ
113	ERJ2RKF4303X	430 kΩ
114	ERJ2RKF4703X	470 kΩ
115	ERJ2RKF5103X	510 kΩ
116	ERJ2RKF5603X	560 kΩ
117	ERJ2RKF6203X	620 kΩ
118	ERJ2RKF6803X	680 kΩ
119	ERJ2RKF7503X	750 kΩ
120	ERJ2RKF8203X	820 kΩ
121	ERJ2RKF9103X	910 kΩ
122	ERJ2RKF1004X	1 MΩ

Panasonic

ERJ3EK****V Precision Thick Film Chip Resistors KIT

Ordner No : ERJ3EK-KIT

- | | | | |
|-----------------------|---------------------|-----------------------------|-------------|
| • Technology | Thick film | • Resistor Values | 122 |
| • Package Inch / Size | 0603 / 1608 | • Resistor Pieces per value | 100 |
| • Series | E24 + Jumper | • Operating Temperature | -55 to +155 |
| • Resistor Range | 10Ω to 1MΩ + Jumper | • Temperature Coefficient | ±100 ppm |
| • Tolerance | ±1 % | | |
| • Maximum Wattage | 0.1 W | | |
| • Maximum Voltage | 75 V | | |



Binder Dim. : 250x300x35 mm
Weight. : 1300 g

KIT Content Listings

No	Manufacturer part number	Resistance
1	ERJ3GEY0R00V	0 Ω
2	ERJ3EKF10R0V	10 Ω
3	ERJ3EKF11R0V	11 Ω
4	ERJ3EKF12R0V	12 Ω
5	ERJ3EKF13R0V	13 Ω
6	ERJ3EKF15R0V	15 Ω
7	ERJ3EKF16R0V	16 Ω
8	ERJ3EKF18R0V	18 Ω
9	ERJ3EKF20R0V	20 Ω
10	ERJ3EKF22R0V	22 Ω
11	ERJ3EKF24R0V	24 Ω
12	ERJ3EKF27R0V	27 Ω
13	ERJ3EKF30R0V	30 Ω
14	ERJ3EKF33R0V	33 Ω
15	ERJ3EKF36R0V	36 Ω
16	ERJ3EKF39R0V	39 Ω
17	ERJ3EKF43R0V	43 Ω
18	ERJ3EKF47R0V	47 Ω
19	ERJ3EKF51R0V	51 Ω
20	ERJ3EKF56R0V	56 Ω
21	ERJ3EKF62R0V	62 Ω
22	ERJ3EKF68R0V	68 Ω
23	ERJ3EKF75R0V	75 Ω
24	ERJ3EKF82R0V	82 Ω
25	ERJ3EKF91R0V	91 Ω
26	ERJ3EKF1000V	100 Ω
27	ERJ3EKF1100V	110 Ω
28	ERJ3EKF1200V	120 Ω
29	ERJ3EKF1300V	130 Ω
30	ERJ3EKF1500V	150 Ω
31	ERJ3EKF1600V	160 Ω
32	ERJ3EKF1800V	180 Ω
33	ERJ3EKF2000V	200 Ω
34	ERJ3EKF2200V	220 Ω
35	ERJ3EKF2400V	240 Ω
36	ERJ3EKF2700V	270 Ω
37	ERJ3EKF3000V	300 Ω
38	ERJ3EKF3300V	330 Ω
39	ERJ3EKF3600V	360 Ω
40	ERJ3EKF3900V	390 Ω
41	ERJ3EKF4300V	430 Ω
42	ERJ3EKF4700V	470 Ω
43	ERJ3EKF5100V	510 Ω
44	ERJ3EKF5600V	560 Ω
45	ERJ3EKF6200V	620 Ω
46	ERJ3EKF6800V	680 Ω
47	ERJ3EKF7500V	750 Ω
48	ERJ3EKF8200V	820 Ω
49	ERJ3EKF9100V	910 Ω
50	ERJ3EKF1001V	1 kΩ

No	Manufacturer part number	Resistance
51	ERJ3EKF1101V	1.1 kΩ
52	ERJ3EKF1201V	1.2 kΩ
53	ERJ3EKF1301V	1.3 kΩ
54	ERJ3EKF1501V	1.5 kΩ
55	ERJ3EKF1601V	1.6 kΩ
56	ERJ3EKF1801V	1.8 kΩ
57	ERJ3EKF2001V	2 kΩ
58	ERJ3EKF2201V	2.2 kΩ
59	ERJ3EKF2401V	2.4 kΩ
60	ERJ3EKF2701V	2.7 kΩ
61	ERJ3EKF3001V	3 kΩ
62	ERJ3EKF3301V	3.3 kΩ
63	ERJ3EKF3601V	3.6 kΩ
64	ERJ3EKF3901V	3.9 kΩ
65	ERJ3EKF4301V	4.3 kΩ
66	ERJ3EKF4701V	4.7 kΩ
67	ERJ3EKF5101V	5.1 kΩ
68	ERJ3EKF5601V	5.6 kΩ
69	ERJ3EKF6201V	6.2 kΩ
70	ERJ3EKF6801V	6.8 kΩ
71	ERJ3EKF7501V	7.5 kΩ
72	ERJ3EKF8201V	8.2 kΩ
73	ERJ3EKF9101V	9.1 kΩ
74	ERJ3EKF1002V	10 kΩ
75	ERJ3EKF1102V	11 kΩ
76	ERJ3EKF1202V	12 kΩ
77	ERJ3EKF1302V	13 kΩ
78	ERJ3EKF1502V	15 kΩ
79	ERJ3EKF1602V	16 kΩ
80	ERJ3EKF1802V	18 kΩ
81	ERJ3EKF2002V	20 kΩ
82	ERJ3EKF2202V	22 kΩ
83	ERJ3EKF2402V	24 kΩ
84	ERJ3EKF2702V	27 kΩ
85	ERJ3EKF3002V	30 kΩ
86	ERJ3EKF3302V	33 kΩ
87	ERJ3EKF3602V	36 kΩ
88	ERJ3EKF3902V	39 kΩ
89	ERJ3EKF4302V	43 kΩ
90	ERJ3EKF4702V	47 kΩ
91	ERJ3EKF5102V	51 kΩ
92	ERJ3EKF5602V	56 kΩ
93	ERJ3EKF6202V	62 kΩ
94	ERJ3EKF6802V	68 kΩ
95	ERJ3EKF7502V	75 kΩ
96	ERJ3EKF8202V	82 kΩ
97	ERJ3EKF9102V	91 kΩ
98	ERJ3EKF1003V	100 kΩ
99	ERJ3EKF1103V	110 kΩ
100	ERJ3EKF1203V	120 kΩ

No	Manufacturer part number	Resistance
101	ERJ3EKF1303V	130 kΩ
102	ERJ3EKF1503V	150 kΩ
103	ERJ3EKF1603V	160 kΩ
104	ERJ3EKF1803V	180 kΩ
105	ERJ3EKF2003V	200 kΩ
106	ERJ3EKF2203V	220 kΩ
107	ERJ3EKF2403V	240 kΩ
108	ERJ3EKF2703V	270 kΩ
109	ERJ3EKF3003V	300 kΩ
110	ERJ3EKF3303V	330 kΩ
111	ERJ3EKF3603V	360 kΩ
112	ERJ3EKF3903V	390 kΩ
113	ERJ3EKF4303V	430 kΩ
114	ERJ3EKF4703V	470 kΩ
115	ERJ3EKF5103V	510 kΩ
116	ERJ3EKF5603V	560 kΩ
117	ERJ3EKF6203V	620 kΩ
118	ERJ3EKF6803V	680 kΩ
119	ERJ3EKF7503V	750 kΩ
120	ERJ3EKF8203V	820 kΩ
121	ERJ3EKF9103V	910 kΩ
122	ERJ3EKF1004V	1 MΩ

Panasonic

ERJ6ENF****V Precision Thick Film Chip Resistors KIT

Order No : ERJ6EN-KIT

- Technology Thick film
- Resistor Values 130
- Package Inch / Size 0805 / 2012
- Resistor Pieces per value 100
- Series E24 + Jumper
- Operating Temperature -55 to +155
- Resistor Range 10Ω to 2.2MΩ + Jumper
- Temperature Coefficient ±100 ppm
- Tolerance ±1 %
- Maximum Wattage 0.125 W
- Maximum Voltage 150 V



Binder Dim. : 250x300x35 mm
Weight : 1300 g

KIT Content Listings

No	Manufacturer part number	Resistance
1	ERJ6GEY0R00V	0 Ω
2	ERJ6ENF10ROV	10 Ω
3	ERJ6ENF11ROV	11 Ω
4	ERJ6ENF12ROV	12 Ω
5	ERJ6ENF13ROV	13 Ω
6	ERJ6ENF15ROV	15 Ω
7	ERJ6ENF16ROV	16 Ω
8	ERJ6ENF18ROV	18 Ω
9	ERJ6ENF20ROV	20 Ω
10	ERJ6ENF22ROV	22 Ω
11	ERJ6ENF24ROV	24 Ω
12	ERJ6ENF27ROV	27 Ω
13	ERJ6ENF30ROV	30 Ω
14	ERJ6ENF33ROV	33 Ω
15	ERJ6ENF36ROV	36 Ω
16	ERJ6ENF39ROV	39 Ω
17	ERJ6ENF43ROV	43 Ω
18	ERJ6ENF47ROV	47 Ω
19	ERJ6ENF51ROV	51 Ω
20	ERJ6ENF56ROV	56 Ω
21	ERJ6ENF62ROV	62 Ω
22	ERJ6ENF68ROV	68 Ω
23	ERJ6ENF75ROV	75 Ω
24	ERJ6ENF82ROV	82 Ω
25	ERJ6ENF91ROV	91 Ω
26	ERJ6ENF1000V	100 Ω
27	ERJ6ENF1100V	110 Ω
28	ERJ6ENF1200V	120 Ω
29	ERJ6ENF1300V	130 Ω
30	ERJ6ENF1500V	150 Ω
31	ERJ6ENF1600V	160 Ω
32	ERJ6ENF1800V	180 Ω
33	ERJ6ENF2000V	200 Ω
34	ERJ6ENF2200V	220 Ω
35	ERJ6ENF2400V	240 Ω
36	ERJ6ENF2700V	270 Ω
37	ERJ6ENF3000V	300 Ω
38	ERJ6ENF3300V	330 Ω
39	ERJ6ENF3600V	360 Ω
40	ERJ6ENF3900V	390 Ω
41	ERJ6ENF4300V	430 Ω
42	ERJ6ENF4700V	470 Ω
43	ERJ6ENF5100V	510 Ω
44	ERJ6ENF5600V	560 Ω
45	ERJ6ENF6200V	620 Ω
46	ERJ6ENF6800V	680 Ω
47	ERJ6ENF7500V	750 Ω
48	ERJ6ENF8200V	820 Ω
49	ERJ6ENF9100V	910 Ω
50	ERJ6ENF1001V	1 kΩ

No	Manufacturer part number	Resistance
51	ERJ6ENF1101V	1.1 kΩ
52	ERJ6ENF1201V	1.2 kΩ
53	ERJ6ENF1301V	1.3 kΩ
54	ERJ6ENF1501V	1.5 kΩ
55	ERJ6ENF1601V	1.6 kΩ
56	ERJ6ENF1801V	1.8 kΩ
57	ERJ6ENF2001V	2 kΩ
58	ERJ6ENF2201V	2.2 kΩ
59	ERJ6ENF2401V	2.4 kΩ
60	ERJ6ENF2701V	2.7 kΩ
61	ERJ6ENF3001V	3 kΩ
62	ERJ6ENF3301V	3.3 kΩ
63	ERJ6ENF3601V	3.6 kΩ
64	ERJ6ENF3901V	3.9 kΩ
65	ERJ6ENF4301V	4.3 kΩ
66	ERJ6ENF4701V	4.7 kΩ
67	ERJ6ENF5101V	5.1 kΩ
68	ERJ6ENF5601V	5.6 kΩ
69	ERJ6ENF6201V	6.2 kΩ
70	ERJ6ENF6801V	6.8 kΩ
71	ERJ6ENF7501V	7.5 kΩ
72	ERJ6ENF8201V	8.2 kΩ
73	ERJ6ENF9101V	9.1 kΩ
74	ERJ6ENF1002V	10 kΩ
75	ERJ6ENF1102V	11 kΩ
76	ERJ6ENF1202V	12 kΩ
77	ERJ6ENF1302V	13 kΩ
78	ERJ6ENF1502V	15 kΩ
79	ERJ6ENF1602V	16 kΩ
80	ERJ6ENF1802V	18 kΩ
81	ERJ6ENF2002V	20 kΩ
82	ERJ6ENF2202V	22 kΩ
83	ERJ6ENF2402V	24 kΩ
84	ERJ6ENF2702V	27 kΩ
85	ERJ6ENF3002V	30 kΩ
86	ERJ6ENF3302V	33 kΩ
87	ERJ6ENF3602V	36 kΩ
88	ERJ6ENF3902V	39 kΩ
89	ERJ6ENF4302V	43 kΩ
90	ERJ6ENF4702V	47 kΩ
91	ERJ6ENF5102V	51 kΩ
92	ERJ6ENF5602V	56 kΩ
93	ERJ6ENF6202V	62 kΩ
94	ERJ6ENF6802V	68 kΩ
95	ERJ6ENF7502V	75 kΩ
96	ERJ6ENF8202V	82 kΩ
97	ERJ6ENF9102V	91 kΩ
98	ERJ6ENF1003V	100 kΩ
99	ERJ6ENF1103V	110 kΩ
100	ERJ6ENF1203V	120 kΩ

No	Manufacturer part number	Resistance
101	ERJ6ENF1303V	130 kΩ
102	ERJ6ENF1503V	150 kΩ
103	ERJ6ENF1603V	160 kΩ
104	ERJ6ENF1803V	180 kΩ
105	ERJ6ENF2003V	200 kΩ
106	ERJ6ENF2203V	220 kΩ
107	ERJ6ENF2403V	240 kΩ
108	ERJ6ENF2703V	270 kΩ
109	ERJ6ENF3003V	300 kΩ
110	ERJ6ENF3303V	330 kΩ
111	ERJ6ENF3603V	360 kΩ
112	ERJ6ENF3903V	390 kΩ
113	ERJ6ENF4303V	430 kΩ
114	ERJ6ENF4703V	470 kΩ
115	ERJ6ENF5103V	510 kΩ
116	ERJ6ENF5603V	560 kΩ
117	ERJ6ENF6203V	620 kΩ
118	ERJ6ENF6803V	680 kΩ
119	ERJ6ENF7503V	750 kΩ
120	ERJ6ENF8203V	820 kΩ
121	ERJ6ENF9103V	910 kΩ
122	ERJ6ENF1004V	1 MΩ
123	ERJ6ENF1104V	1.1 MΩ
124	ERJ6ENF1204V	1.2 MΩ
125	ERJ6ENF1304V	1.3 MΩ
126	ERJ6ENF1504V	1.5 MΩ
127	ERJ6ENF1604V	1.6 MΩ
128	ERJ6ENF1804V	1.8 MΩ
129	ERJ6ENF2004V	2 MΩ
130	ERJ6ENF2204V	2.2 MΩ