







Front



Back

















- Charger for lead-acid batteries (flooded, Gel and AGM) and li-ion batteries (lithium iron and lithium manganese)
- · Built-in 3 stage programmable charging curve
- · Universal AC input / Full range
- · Built-in active PFC function
- · Fanless design, cooling by free air convection
- Built-in temperature compensation function
- Protection: Short circuit / Over voltage / Over temperature / Battery under voltage / Battery over voltage / Battery reverse polarity protection
- · 3 years warranty



Applications

- · Radio system backup solution
- Electric scooter charger
- Surveillance system


■ GTIN CODE

MW Search: https://www.meanwell.com/serviceGTIN.aspx

Description

ENC-120 is a single output 120W AC/DC desktop type charger with 3 stage charging curve. In addition to the embedded pre-defined charging curves, the default curve is programmable and thus able to accommodate different types of batteries, such as lead-acid batteries (gel, flooded and AGM) and li-ion batteries (lithium iron and lithium manganese). With the rugged mechanical design along with the high efficiency circuitry, ENC-120 operates for the ambient temperature range -30~+70°C under free air convection.

■ Model Encoding





SPECIFICATION


MODEL		ENC-120-12	ENC-120-24	ENC-120-48		
	BOOST CHARGE VOLTAGE(Vboost)(default)	14.4V	28.8V	57.6V		
	FLOAT CHARGE VOLTAGE(Vfloat)(default)		27.6V	55.2V		
	CHARGE VOLTAGE RANGE Note.3		18 ~ 30V	36 ~ 60V		
	OUTPUT CURRENT(CC) (default)		4A	2A		
OUTPUT	RATED POWER	115.2W	115.2W	115.2W		
	RECOMMENDED BATTERY	110.244	110.244	110.244		
	CAPACITY (AMP HOURS) Note.4 LEAKAGE CURRENT FROM	30 ~ 80AH	15 ~ 40AH	10 ~ 20AH		
	BATTERY (Typ.)	<1mA				
		90 ~ 264VAC 127 ~ 370VDC				
	FREQUENCY RANGE	47 ~ 63Hz				
	POWER FACTOR (Typ.)	PF>0.98/115VAC, PF>0.95/230VAC at full load				
INPUT	EFFICIENCY (Typ.)	89%	90%	90.5%		
	AC CURRENT (Typ.)	1.25A/115VAC 0.63A/230VAC				
	INRUSH CURRENT (Typ.)	COLD START 65A at 230VAC				
	LEAKAGE CURRENT	<3.5mA/240VAC				
	SHORT CIRCUIT Note.6	$Protection\ type: Shut\ down\ O/P\ voltage,$	re-power on to recover			
	OVER VOLTAGE Note.7	15.5 ~ 18.2V	31 ~ 36.5V	62.1 ~ 72.9V		
PROTECTION	OVER VOLTAGE Note.7	Protection type: Shut down and latch off	o/p voltage, re-power on to recover			
	REVERSE POLARITY	By internal fuse				
	OVER TEMPERATURE	Shut down O/P voltage, recovers automate	tically after temperature goes down			
FUNCTION	TEMPERATURE COMPENSATION					
	WORKING TEMP.	-30 ~ +70°C (Refer to "Derating Curve")				
	WORKING HUMIDITY	20 ~ 95% RH non-condensing				
ENVIRONMENT	STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH non-condensing				
	TEMP. COEFFICIENT	±0.05%/°C (0~50°C)				
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, 60min. ea	ach along X, Y, Z axes			
	SAFETY STANDARDS	IEC62368-1, UL62368-1, EAC TP TC 004, BSMI CNS14336-1 approved; Meet BS EN/EN62368-1				
	WITHSTAND VOLTAGE	I/P-O/P:3KVAC I/P-FG:2KVAC O/P-FG:0.5KVAC				
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG; O/P-FG:100M Ohms / 500VDC / 25°C/ 70% RH				
		Parameter	Standard	Test Level / Note		
		Conducted	BS EN/EN55032 (CISPR32) / FCC PART15 (CISPR22)	Class B		
	EMC EMISSION	Radiated	BS EN/EN55032 (CISPR32) / FCC PART15 (CISPR22)	Class B		
		Harmonic Current	BS EN/EN61000-3-2			
SAFETY&		Voltage Flicker	BS EN/EN61000-3-3			
-		BS EN/EN55024, BSMI CNS13438	20 211121101000 0 0			
EMC (Note 8)		Parameter	Standard	Test Level / Note		
(ESD	BS EN/EN61000-4-2	Level 3, 8KV air ; Level 2, 4KV contact		
		Radiated	BS EN/EN61000-4-3	Level 2, 3V/m		
		EFT / Burst	BS EN/EN61000-4-4	Level 2, 1KV		
	EMC IMMUNITY			·		
		Surge	BS EN/EN61000-4-5	Level 2, 1KV/Line-Line,Level 3, 2KV/Line-Ear		
		Conducted	BS EN/EN61000-4-6	Level 2, 3Vrms		
		Magnetic Field	BS EN/EN61000-4-8	Level 1, 1A/m		
		Voltage Dips and Interruptions	BS EN/EN61000-4-11	>95% dip 0.5 periods, 30% dip 25 periods >95% interruptions 250 periods		
	MTBF	1726.4K hrs min. Telcordia SR-332 (Bellcore); 206.1K hrs min. MIL-HDBK-217F (25°C)				
OTHERS	DIMENSION	192*178*45.5mm (L*W*H)				
	PACKING	0.98Kg; 10pcs/10.8Kg /1.38CUFT				
NOTE	All parameters NOT speciall This is the range when prog This is MEAN WELL's sugg Derating may be needed ur This protection mechanism Each model incorporates a Voltage stage whereas 115	y mentioned are measured at 230VAC inp gramming Vboost or Vfloat by using SBP-0 ested range. Please consult your battery no ider low input voltages. Please check the consistency of s specified for the case the short circuit of MCU-controlled dynamic over voltage protects of Vfloat over Float stage. dered as an independent unit, but the final	=	ature. ximum charging current limitation. Constant Current stage and Constant whole system complies with the		

9. The ambient temperature derating of 3.5° C/1000m with fanless models and of 5° C/1000m with fan models for operating altitude higher than 2000m(6500ft).

(as available on http://www.meanwell.com)




■ Block Diagram



■ Derating Curve

■ Static Characteristics






■ Function Manual

1. Charging Curve

- X This series provides a 3 stage charging. The default curve is programmable, whereas other pre-defined curves can be activated by the means of the DIP switch; please refer to the table below and the Mechanical Specification.
- ** To accommodate the parameters of the charging curve, SBP-001, the smart battery charging programmer designed by MEAN WELL, and a personal computer are needed. Please contact MEAN WELL for details.
- O Default 3 stage charging curve



© Suitable for lead-acid batteries (flooded, Gel and AGM) and Li-ion batteries (lithium iron and lithium manganese).


© Embedded 3 stage charging curve

MODEL	Description	CC(default)	Vboost	Vfloat
	Default, programmable		14.4	13.8
12V	Pre-defined, gel batter	8A	14	13.6
120	Pre-defined, flooded battery	OA	14.2	13.4
	Pre-defined, AGM battery		14.5	13.5
	Default, programmable		28.8	27.6
24V	Pre-defined, gel battery	4A	28	27.2
240	Pre-defined, flooded battery	44	28.4	26.8
	Pre-defined, AGM battery		29	27
	Default, programmable		57.6	55.2
48V	Pre-defined, gel battery	2A	56	54.4
400	Pre-defined, flooded battery		56.8	53.6
	Pre-defined, AGM battery	tery		54

2. Front Panel LED Indicators & Corresponding Signal at Function Pins

LED	Description
Green	Float (stage 3)
Orange	Charging (stage 1 or stage 2)







Case No. 252 Unit:mm

45.5

() LED

SWITCH





Terminal Pin No. Assignment (TB1):

Pin No.	Assignment
1,2	+V
3.4	-V

Note: Please use wires with a cross section of $0.5 - 4.0 \text{ mm}^2$ ($12 \sim 20 \text{AWG}$) for connection. Recommended wires strip length is 9 mm and screw torque is 4.0 lb-inch ($0.4 \sim 0.5 \text{Nm}$).

DIP SW:

1	2	Description
OFF	OFF	Default, programmable
ON	OFF	Pre-defined, Gel battery
OFF	ON	Pre-defined, flooded battery
ON	ON	Pre-defined, AGM battery

Connector Pin No. Assignment (CN31): HRS DF11-6DP-2DS or equivalent

Pin No.	Assignment	Mating Housing	Terminal
1	Prog-+3.3V		
2	Prog- GND		
3	Prog- RX	HRS DF11-6DS	HRS DF11-**SC
4	Prog-TX	or equivalent	or equivalent
5	RTH+		
6	RTH-		



■ Accessory List

	Quantity	
1	NTC sensor wire	1
2	NTC mating wire	1

