


Data Sheet

K Series 420.D.101.10

Analog Meters with Moving-Iron Movement 90° Dial





EQ 48 K EQ 72 K EQ 96 K EQ 144 K

with Slide-In-Dial

Application

The moving-iron panel meters **EQ 48/72/96/144 K** (K series) housed in moulded thermoplastic cases are mainly used for the measurement of AC currents and voltages in the usual technical frequency range of $16^{2}/_{3}$... 100 Hz.

Moving-iron meters indicate rms-values practically independent of wave form even of high harmonics. Error of indication may occur for extreme wave forms (e.g. phase gating controls) and / or frequencies above 100 Hz.

These meters are **not** suitable for use with shunts or tachogenerators due to their high power consumption.

The K-series meters offer application-oriented advantages in switchboard and generating set production, also suitable for mosaic panel mounting. The bezel, the glass window and the dial can be easily exchanged on site.

Movements

Moving-iron movement with pivot suspension, spring loaded shock absorbing jewel bearings and silicon oil damping.

Mechanical Data

case details	in control	/ switchgea	e suitable to r panels, m anels, stacl	
material of case		nate thermo rdant with l	oplastics, JL rating of	94 V – 0
material of window	glass 🖡			
colour of bezel	black (sim	ilar to RAL	9005) 🔶	
position of use	vertical ±	5° 🔶		
panel fixing	screw clar or spring o		ept EQ 144	4 K)
mounting	stackable	next to eac	h other	
panel thickness	\leq 40 mm			
terminals voltmeters and ammeters up to 30 A ammeters ≥ 40 A ammeters >60 A	hexagon studs, M4 screws and wire clamps E3 threaded studs M6 with nuts threaded studs M8 with nuts			
dimensions (in mm)	EQ 48 K	EQ 72 K	EQ 96 K	EQ 144 K
bezel	□ 48	□ 72	□ 96	□ 144
case	□ 42.5	□ 66	□ 90	□ 136
depth	53	53	53	53
panel cutout	□ 45+0.6	□ 68+0.7	□ 92+0.8	□ 138 ⁺¹
weight approx.	0.1 kg	0.15 kg	0.2 kg	0.25 kg

Electrical Data

measuring unit frequency range	AC voltage / current 16 ² / ₃ 100 Hz	
power consumption voltmeters ammeters ≤ 15 A ammeters >15 A		
overload capacity (acc. continuously	to DIN EN 60 051-1) 1.2 times rated voltage	/ current
voltmeters 5 s max.	2 times, 1000 V max.	
ammeters 5 s max. 1 s max.	EQ 48 K 10 times, 200 A max. -	EQ 72/96/144 K 10 times 40 times, up to 250 A
measurement category	CAT III	
operating voltage	refer to Measuring Rang	ges
pollution level	2	
enclosure code	 IP 52 case front side IP 00 for terminals without protection against accidental contact IP 20 for terminals protected against accidental contact 	

Measuring Ranges

measuring ranges	operating	voltage		
AC current	EQ 48 K	EQ 72 K	EQ 96 K	EQ 144 K
1; 1,5; 2,5; 4; 5; 6; 10; 15; 25 A ¹) 40; 60; 100 A ¹) ³)	300 V _	300 V 300 V	300 V 300 V	600 V 600 V
AC voltage	EQ 48 K	EQ 72 K	EQ 96 K	EQ 144 K
60 V, 100 V	150 V	150 V	150 V	150 V
150 V	150 V	150 V	150 V	150 V
250 V	300 V	600 V	600 V	600 V
400 V, 500 V	300 V	600 V	600 V	600 V
600 V	600 V	600 V	600 V	600 V
750 V, 800 V	600 V	600 V	600 V	600 V
750 V, 800 V ³)	-	1000 V	1000 V	1000 V
900 V, 1000 V	600 V	600 V	600 V	600 V
900 V, 1000 V ³)	-	1000 V	1000 V	1000 V
for use on CT/VT N/1 A, N/5 A ¹) N/100 V, N/110 V ²)	EQ 48 K 150 V 150 V	EQ 72 K 150 V 150 V	EQ 96 K 150 V 150 V	EQ 144 K 150 V 150 V
Diagon state transformer ratio when ordering				

Please state transformer ratio when ordering.

¹) full scale value = 2 times rated value (overload scaling)
 ²) full scale value = 1.2 times rated value (- " -)

³) not for EQ 48 K

Scaling

pointer	bar / knife-edge pointer			
pointer deflection	0 90°			
scale characteristics	practically above 10%		III-scale val	ue
scale division	coarse-fine			
scale length	EQ 48 K 41 mm	EQ 72 K 61 mm	EQ 96 K 97 mm	EQ 144 K 146 mm
overload scaling				
ammeters	2 times rated current			
voltmeters for use on voltage transformers	1.2 times rated voltage			



Data Sheet

Analog Meters with Moving-Iron Movement 90° Dial

Accuracy at Reference Conditions

accuracy class

1.5 according to DIN EN 60 051 - 1

reference conditions

ambient temperature position of use input wave form frequency others

23°C nominal position ±1° • rated measuring value sinusoidal, distortion factor \leq 5% 45 ... 65 Hz DIN EN 60 051 - 1

influences

ambient temperature position of use frequency

stray magnetic field

23°C±2K nominal position ±5° 15 ... 100 Hz (voltage) 15 ... 400 Hz (current) 0.5 mT

Environmental

climatic suitability operating temperature range	climatic class 3 acc. to VDE/VDI 3540 sheet 2 $-10 \dots +55$ °C
storage temperature range	–25 +65 °C
relative humidity	≤ 75% annual average, non–condensing
shock resistance	15 g, 11 ms
vibration resistance	2.5 g, 5 55 Hz

Rules and Standards

DIN 43 718	Measurement and control; front-frames and frontpanels of measurement and control equipment; principal dimensions
DIN 43 802	Line scales and pointers for indicating electrical measuring instruments; general requirements
DIN 16 257	Nominal positions and position symbols used for measuring instruments
DIN EN 60 051	Direct acting indicating analogue electrical measuring instruments and their accessories
-1	Part 1: Definitions and general requirements common to all parts
-2	Part 2: Special requirements for ammeters and voltmeters
-9	Part 9: Recommended test methods
DIN EN 60 529	Enclosure codes by housings (IP-code)
DIN EN 61 010-1	Safety requirements for electrical measuring, control and laboratory equipment Part 1: General requirements
DIN EN 61 326-1	Electrical equipment for measurement, con- trol and laboratory use – EMC requirements Part 1: General requirements
DIN IEC 61 554	Panel mounted equipment – Electrical measuring instruments – Dimensions for panel mounting
VDE/VDI 3540 sheet 2	reliability of measuring and control equipment (classification of climates)

Options

case

window	non–glaring glass
colour of bezel	gray (similar to RAL 7037)
index marking pointer	red, front adjustable
position of use	on request 15165°
marine application	non–certified or type approval by "Germanischer Lloyd"


terminal safety protection

full-sized rear cover (except direct-connected ammeters > 25 A), protective sleeves to go on hexagon studs and M4 screws with wire clamps E3


protection against accidental contact (hand and fingers) acc. to VBG 4 / DIN 57 106, sec. 100

dial


Connections



AC current (for use on current transformer)



Dimensions



Ordering Information

4	
type EQ	moving-iron panel meter
front dimensions 48 K 72 K 96 K 144 K	48 mm x 48 mm 72 mm x 72 mm 96 mm x 96 mm 144 mm x 144 mm
measuring ranges	refer to preceding table
window	glass ¹) non-glaring glass
colour of bezel	black (similar to RAL 9005) ¹) gray (similar to RAL 7037)
index marking pointer	none ¹) red, front adjustable
position of use	vertical ¹) on request 15 165° **)
marine application	none ¹) non-certified type approval by "Germanischer Lloyd"
panel fixing	screw clamps ¹) spring clamps (except EQ 144 K)
terminal safety protection	none ¹) full-sized rear cover protective sleeves
dial	according to measuring range or standard series for use on CT/VT ¹) non-calibrated, with dial symbols blank dial scale division and figuring 0 100% according to standard series additional lettering on request ²) additional figuring on request ²) coloured marks red, green or blue ²) coloured sector red, green or blue ²)
overload scaling (ammeters)	no overload range 2 times rated current ¹) 5 times rated current
dial illumination for EQ 72/96 K for EQ 144 K for EQ 72/96 K for EQ 144 K for EQ 144 K for EQ 72/96 K for EQ 144 K	none ¹) 1 lamps 6 V, 12 V, or 24 V 2 lamps 6 V, 12 V, or 24 V 1 pluggable LED 24 V DC / 0.4 W 2 pluggable LEDs 24 V DC / 0.4 W internal LED 24 V DC internal LED 24 V DC internal LED 24 V DC on request
logo ¹) Standard	WEIGEL ¹) none OEM logo ²)

¹) Standard
 ²) Please clearly add the desired specifications.

ordering example

EQ 72 K, measuring range 0 \dots 150 V, window non - glaring glass, dial 0 \dots 100%, no logo

Weigel Meßgeräte GmbH

Postfach 720 154	• 90241 Nürnberg • Phone: 0911/42347-0
Erlenstraße 14 •	90441 Nürnberg • Fax: 0911/42347-39
Sales:	Phone: 0911/42347-94
Internet:	http://www.weigel-messgeraete.de
e–mail:	vertrieb@weigel-messgeraete.de

- specifications subject to change without notice; date of issue 08/14 -

