

EB-980W

DATASHEET / BROCHURE



Raise the bar with this bright and scalable, 3,800 lumens, WXGA projector, that offers multiple connectivity solutions and is simple to set up.

Optimise your students' learning potential with this bright WXGA projector that's capable of producing a large and scalable screen size. Excessive downtime is a thing of the past with this reliable projector that can deliver up to 10 years' worth of lessons before a replacement lamp is required or the air filter needs attention¹. It has a range of connectivity solutions and is fuss free to set up.

Excellent visibility for every student

With this WXGA projector, content will be bright, vivid and clear, ensuring that everyone can engage with the lesson. Providing excellent visibility, this projector is scalable up to 300 inches and is bright even in high ambient lighting conditions. It's all thanks to the high 3,800-lumen output and 15,000:1 contrast ratio.

Minimal maintenance

When resources are limited, our reliable projectors and long-lasting lamps help to eliminate downtime and unnecessary service costs. Imagine what you could achieve with minimal interruptions - our projectors help to make that a reality with up to 10 years' worth of lessons before a replacement lamp is required or the air filter needs attention¹.

Easy set up

Every classroom is different so you need a projector that is simple to set up and position. With our wide 1.6x optical zoom and vertical/horizontal keystone correction, it's easy to get up and running quickly.

Utilise multiple devices

Capture your students' attention and nurture a collaborative environment with hassle-free connectivity solutions. With the iProjection app, it's easy to display content from PCs and smart devices². The split-screen function can be utilised to show content from multiple devices simultaneously, while the moderator function lets you review content before it is displayed.

KEY FEATURES

- **Bright and vivid display**
WXGA projector offering 3,800 lumens and 15,000:1 contrast ratio
- **Minimal maintenance**
10 years' worth of lessons before maintenance is required¹
- **Flexible installation**
Horizontal/vertical keystone correction and 1.6x optical zoom
- **Enhanced connectivity**
Dual HDMI ports, MHL support, RJ-45 Ethernet, optional Wi-Fi
- **Collaborative features**
iProjection app, split-screen function, moderator function



EPSON
EXCEED YOUR VISION

PRODUCT SPECIFICATIONS

TECHNOLOGY

Projection System	3LCD Technology, RGB liquid crystal shutter
LCD Panel	0,59 inch with MLA (D9)

IMAGE

Colour Light Output	3.800 lumen- 2.410 lumen (economy)
White Light Output	3.800 lumen - 2.410 lumen (economy) In accordance with ISO 21118:2012
Resolution	WXGA, 1280 x 800, 16:10
Contrast Ratio	15.000 : 1
Lamp	UHE, 210 W, 6.000 h durability, 12.000 h durability (economy mode)
Keystone Correction	Auto vertical: ± 30 °, Manual horizontal ± 30 °
Colour Reproduction	Upto 1.07 billion colours

OPTICAL

Projection Ratio	1,38 - 2,24:1
Zoom	Manual, Factor: 1,6
Image Size	29 inches - 280 inches
Projection Distance Wide/Tele	1,79 m - 2,92 m (60 inch screen)
Projection Lens F Number	1,51 - 1,99
Focal Distance	18,2 mm - 29,2 mm
Focus	Manual
Offset	10 : 1

CONNECTIVITY

USB Display Function	3 in 1: Image / Mouse / Sound
Interfaces	USB 2.0 Type A, USB 2.0 Type B, RS-232C, Wireless LAN IEEE 802.11b/g/n (optional), VGA in (2x), VGA out, HDMI in (2x), Composite in, Component in (2x), RGB in (2x), Stereo mini jack audio out, Stereo mini jack audio in (2x), Ethernet interface (100 Base-TX / 10 Base-T), MHL, Microphone input
Epson iProjection App	Ad-Hoc / Infrastructure

ADVANCED FEATURES

Security	Kensington lock, Security cable hole, Wireless LAN unit lock, Wireless LAN security, Password protection
Features	AV mute slide, Automatic keystone correction, Built-in speaker, Direct Power on/off, Document Camera Compatible, Easy OSD pre-setting, Horizontal and vertical keystone correction, MHL audio/video interface, Network projection, OSD copy function, PC Free, Quick Corner, Split-Screen-Function, Wireless LAN capable, iProjection set-up by QR code

OTHER

Warranty	24 months Carry in, Lamp: 12 months or 1.000 h (whichever comes first) Optional warranty extension available
----------	---

LOGISTICS INFORMATION

SKU	V11H866040
EAN code	8715946642642
Country of Origin	Philippines
Layer	6 Units



**EPSON
WORLD LEADER
IN PROJECTORS**
Source: Futuresource Consulting Ltd.

Epson Deutschland GmbH
Otto-Hahn-Str. 4
D-40670 Meerbusch
Info-Line: 02159 92 79 500
Telefax: +49 (0) 2159/538-3000
www.epson.de

Epson in Österreich
Info-Line: 01 253 49 78 333
www.epson.at
Epson in der Schweiz
Info-Line: 022 592 7923
www.epson.ch

Alle Marken und eingetragenen Warenzeichen sind das Eigentum der Seiko Epson Corporation oder der jeweiligen Rechteinhaber.
Diese Produktinformationen können ohne vorherige Ankündigung geändert werden.

EB-980W

WHAT'S IN THE BOX

- VGA cable
- Main unit
- Power cable
- Remote control incl. batteries

OPTIONAL ACCESSORIES

- ELPLP96
V13H010L96
- Ceiling Mount (White) - ELPMB23
V12H003B23
- Soft Carry Case - ELPKS70
V12H001K70
- Wireless LAN Adapter - ELPAP10
V12H731P01
- Ceiling Pipe (700mm) - ELPFP14
V12H003P14
- Ceiling Pipe (450mm) - ELPFP13
V12H003P13
- Active Speakers (2 x 15W) - ELPSP02
V12H467040
- Control and Connection Box - ELPCB02
V12H614040

1. Based on six hours of use per day, five days a week, over 39 weeks of school use in a year.
2. 2-Requires iProjection App and an internet connection – compatible with IOS, Android and Google Chromebook devices only, and file sharing limitations may apply.

EPSON®