



EV busbars 1Ph., 12HP, 80A for PLS. CLS. PKN., PFIM, PFHM, PFNM



Part no. **EVG-16/1PHAS/12MODUL**
 Catalog No. **291466**

Similar to illustration

Delivery program

Basic function		Busbar
Basic function accessories		Busbar for miniature circuit-breaker Busbar for residual-current circuit-breakers Busbar for combined residual-current/power circuit-breaker
Busbar type		Single phase
Product range		EVG

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Phase busbar (EC000215)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Phase busbar (ecl@ss10.0.1-27-37-13-06 [ACN992011])		
Number of phases		1
Number of poles		1
Suitable for number of devices		12
Module width	mm	0
Cross section	mm ²	16
Length	mm	213.6
Rated permanent current I _u	A	80
Type of electric connection		Fork
Insulated		Yes
Rated surge voltage	kV	4
Conditioned rated short-circuit current I _q	kA	25
Max. rated operation voltage U _e	V	415
Rated short-time withstand current I _{cw}	kA	0
Suitable for devices with N-conductor		No
Suitable for devices with auxiliary switch		No

Dimensions

