

Eaton 186279

Catalog Number: 186279

Eaton Moeller® series C22 Key-operated actuator, RMQ compact solution, maintained, 1 N/O, Cable (black) with non-terminated end, 4 pole, 3.5 m, 2 positions, MS1, Bezel: titanium

General specifications



Product Name	Catalog Number
Eaton Moeller® series C22 Key-operated actuator	186279
	EAN
	4015081817801
Product Length/Depth	Product Height
3597 mm	30 mm
Product Width	Product Weight
30 mm	0.143 kg
Certifications	Catalog Notes
VDE 0660	Not suitable for master key systems
UL	
CSA	
IEC/EN 60947-5-1	
CE	
CSA File No.: 165628	
CSA Class No.: 321103	
UL File No.: E29184	
UL 508	
CSA-C22.2 No. 14-18 and No. 94.2-15	
CE marking	
UL Category Control No.: NKCR	
UL listed, CSA certified	

Product specifications

Type

Key-operated button

Accessories

1 key included with supplied equipment.

Actuator color

Black

Product Category

RMQ compact solution

Actuator function

Switching function latching

Maintained

Key withdrawable in position 0

Key withdrawable in position 1

Electric connection type

Other

Fitted with:

Front ring

Operating frequency

100 Operations/h

Pollution degree

3

Climatic proofing

Damp heat, cyclic, to IEC 60068-2-30

Damp heat, constant, to IEC 60068-2-78

Connection to SmartWire-DT

No

Rated impulse withstand voltage (Uimp)

800 V AC

Actuator type

Key

Actuator diameter

4.7 mm

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-30 °C

Resources

Catalogs

[eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-00004157.pdf](#)

[DA-DC-00004135.pdf](#)

Drawings

[eaton-operating-c22-key-operated-actuator-dimensions.eps](#)

[eaton-operating-c22-key-operated-actuator-3d-drawing.eps](#)

eCAD model

[DA-CE-ETN.C22-WRS-MS1-K10-P65](#)

Installation instructions

[IL047016ZU](#)

Installation videos

[Eaton's RMQ compact solution pilot devices](#)

mCAD model

[DA-CS-c22_ws_open_cable](#)

[DA-CD-c22_ws_open_cable](#)

Sales notes

[eaton-rmq-mci-multi-color-light-indicator-flyer-fl047005en-en-us.pdf](#)

System overview

[Pilot devices - selection aid](#)

Wiring diagrams

[eaton-operating-c22-pushbutton-wiring-diagram-002.eps](#)

Number of contacts (change-over contacts)

0

Number of contacts (normally closed contacts)

0

Number of contacts (normally open contacts)

1

Opening diameter

22.5 mm

Opening height

0 mm

Operating torque

0.5 Nm

Rated insulation voltage (Ui)

250 V

Rated operational current (Ie) at AC-15, 24 V

4 A

Rated operational current (Ie) at DC-13, 24 V

3 A

Bezel color

Titanium

Cable material

PUR

Key code

MS1

Bezel material

Plastic

Design

Cable end open

Classical

Mounting position

As required

Rated conditional short-circuit current (Iq)

1 kA

Cable length

3.5 m

Connection type

Cable (black) with non-terminated end, 4 pole

Overvoltage category

III

Control circuit reliability

1 failure per 17,000,000 switching operations (statistically determined, at 17 V DC/7 mA: N/O contact

Degree of protection

IP66

IP65, rear

NEMA Other

Shock resistance

30 g, Mechanical, Shock duration 11 ms

Number of switch positions

2

Tightening torque

2 Nm, Threaded ring

Short-circuit protection rating

Max. 4 A gG/gL, Fuse, Contacts

Supply voltage - max

0 V

Supply voltage - min

0 V

Switching angle

60 °

Width opening

0 mm