

# **Product description**

### **MAIN FEATURES**

COMPACT, UP TO 12 POSITIONS

- 25'000 switching cycles with up to 6 Ncm switching torque
- > Gold plated contacts: 3 micron
- > Robust metal bushing and shaft
- > Operating temperature range: -40 to +85 °C
- > IP68 front panel sealing
- > Various options and customizations







### **PRODUCT VARIETY**

- Soldering eyelets or pins for PCB
- Poles x positions per wafer from 1 x 12 to 4 x 3
- 1 or 2 wafers
- Detent angle 30°, 36° or 60°
- Shorting or non-shorting
- Switching torque: 2, 4 or 6 Ncm
- Front panel sealing IP60 or IP68
- Configurable end stops
- Shaft diameter: 3, 4 or 6 mm
- Shaft length

#### **TYPICAL APPLICATIONS**

- Industrial controls
- Avionics, measurement and test systems
- Medical and audio equipment
- Transport and constructions machines

### **POSSIBLE CUSTOMIZATIONS**

- Shaft dimension and shape
- Central lock dimensions
- Switching torque
- Hollow shaft, inner shaft
- Push function | pull to turn function
- Others



# **Dimensions and pin assignment**

### **SWITCH DESIGN**

WITH SOLDERING EYELETS

1 Wafer



2 Wafers



WITH PINS FOR PCB



### PIN ASSIGNMENT AND DRILLING DIAGRAM

30° DETENT ANGLE



Dimensions in mm

Tolerances according to DIN ISO 2768-1 (m), unless otherwise specified



# **Dimensions and pin assignment**

### FRONT PANEL CUT OUT



### SHAFT Ø 4 MM, NUT M8 X 0.75





IP68-Version (pin-cutting from behind the front panel)

8,2

ட

 $\sim$ 

SHAFT Ø 6 MM, NUT M10 X 0.75



## **NUT (SUPPLIED)**

#### SHAFT Ø 3 MM



Screw wrench 10 mm M6 x 0.75

SHAFT Ø 4 MM



Screw wrench 10 mm M8 x 0.75

SHAFT Ø 6 MM



Screw wrench 14 mm M10 x 0.75

Dimensions in mm

Tolerances according to DIN ISO 2768-1 (m), unless otherwise specified



# **ORDERING INFORMATION**

## **ORDERING CODE**

01	-	-	_	-	_	-	-	-	-	-	-	-	-	-	
			_												
BASIC CODE												SHAF	T DIAM	ETER	
See standard types												0 4 m M 3 m N 6 m	nm nm nm		
NUMBER OF WAFER	25														
See standard types											NUM	IBER OF	POSITI	ONS	
NUMBER OF POLES											00 3 11 10 09 9 08 3 07 2	Standard 11 positic 10 positic 9 positior 8 positior 7 positior	ons ons is is		
FACTORY SET CHAR See standard types	ACTER		_								06 05 04 03 02	6 positior 5 positior 4 positior 3 positior 2 positior	15 15 15 15		
SWITCHING MODE										SHA	FT LENG	GTH (AL	)		
<ul><li>3 Shorting</li><li>4 Non-shorting</li></ul>										000	59 mr 39.2 r 28 mr Custo	n (Ø3m mm (stand n (Ø6m mized	m shaft) dard Ø 4 m shaft)	mm sha	ft)
	IE										(shaff e.g. 1	length ro 0.3 mm =	unded fo = 10.5 m	m or 10	omm, mm)
<ul> <li>4 Ncm (standard)</li> <li>M 2 Ncm</li> <li>N 6 Ncm</li> </ul>						/				<sup>1</sup> Cust AL r Max. Ø 3 c	tomized sho neasured fr shaft lengtl and 4 mm =	aft length (A om base of h (AL): 80 mm	.L) housing (se	ee picture b	oelow)
						_				₽ŏr €	nm = 28 mr	n 			
									PIN S	TYLE	IP SEA				
									00 20 30 <sup>2</sup> 70 <sup>2</sup> <sup>2</sup> Only shaft	Solde Pins f Solde Pins f deliverat	or PCB   or PCB   oring eye or PCB   ole for versi	lets   IP6 IP60 lets   IP6 IP68 on with a w	0 8 afer with 3	or 4 mm	



# **ORDERING INFORMATION**

### **PREFERENCE TYPES SELECTION CHART**<sup>1</sup>

#### DETENT ANGLE 30°, SHORTING

CONTACT ARRANGEMENT	NUMBER OF WAFERS	FUNCTION	PART NUMBER	1
	(MAX. 2 WAFERS AVAILABLE)	(POLES X POSITIONS)	WITH SOLDERING EYELETS	WITH PINS FOR PCB
	-=	1 x 12   endless rotating	01-1123	01-1123-20
		2 x 12   endless rotating	01-2123	_
9*••• <sup>2</sup> 5 8 7 6	-==	1 x 12	01-1183	01-1183-20
		2 x 12	01-2183	_
11 23		1 x 11	01-1113	01-1113-20
10 • <b>O</b> • 4 9 • • • 5 8 7 6		2 x 11	01-2113	_
1A2A3A 6B 5B 55A 4B 56A 3B2B1B		2 x 6	01-1263	01-1263-20
		4 x 6	01-2263	_
1A2A 3A 3D 2D 2D 1D 3C 2B 3C 2C 2B 3B 3C2C1C		4 x 3	01-1433	01-1433-20
		8 x 3	01-2433	_

#### DETENT ANGLE 30°, NON-SHORTING

CONTACT ARRANGEMENT	NUMBER OF WAFERS (MAX. 1 WAFERS AVAILABLE)	FUNCTION (POLES X POSITIONS)	PART NUMBER WITH SOLDERING EYELETS	WITH PINS FOR PCB
	-=	1 x 12   endless rotating	01-1124	01-1124-20
9 8 7 6		1 x 12	01-1184	01-1184-20
11, <b>1</b> , <b>2</b> , 3 10, <b>0</b> , 4 9, <b>8</b> , <b>7</b> , 65	-=	1 x 11	01-1114	01-1114-20
6B 5B 4B 3B2B1B		2 x 6	01-1264	01-1264-20
1A2A3A 3D 2D 2B 1D 3C2C1C	- <del></del>	4 x 3	01-1434	01-1434-20



# **ORDERING INFORMATION**

### **PREFERENCE TYPES SELECTION CHART<sup>1</sup>**

#### DETENT ANGLE 36°, SHORTING

CONTACT ARRANGEMENT	NUMBER OF WAFERS	FUNCTION	PART NUMBER		
	(MAX. 2 WAFERS AVAILABLE)	(POLES X POSITIONS)	WITH SOLDERING EYELETS	WITH PINS FOR PCB	
10 1 2 9 <b>6 1</b> 3	-=	1 x 10   endless rotating	01-1103	01-1103-20	
8 <b>0 1</b> 7 <b>6</b> 5		1 x 10	01-1193	01-1193-20	

### DETENT ANGLE 60°, NON-SHORTING

CONTACT ARRANGEMENT	NUMBER OF WAFERS (MAX. 2 WAFERS AVAILABLE)	FUNCTION (POLES X POSITIONS)	PART NUMBER WITH SOLDERING EYELETS	WITH PINS FOR PCB
		1 x 6   endless rotating	01-1104	01-1104-20
		1 x 6	01-1164	01-1164-20
3B, 2A 2B, 5, 2A 2B, 5, 2A 3A		2 x 3	01-1234	01-1234-20
2D 2A 2D 2A 1B 1D 22 12 22B 22B		4 x 2	01-1424	01-1424-20

### PACKAGING

Foam polystyrene box:

10 pieces

#### **ACCESSORIES AND SPARE PARTS**

Hex nut M8 x 0.75: Hex nut M6 x 0.75: Hex nut M10 x 0.75: Stop pins (end stop): Part number 4024-81 (10 pieces / bag), brass, nickel plated Part number 4024-80 (10 pieces / bag), brass, nickel plated Part number 4024-82 (10 pieces / bag), brass, nickel plated Part number 4007-36 (10 pieces / bag) Part number 4007-35 (50 pieces / bag)



# **Customized solutions**

## HOLLOW SHAFT SYSTEM

HOLLOW SHAFT



FRONT PANEL CUT OUT

Front panel cut out see on the pages before.

The hollow shaft enables the operation of either two switches or e.g. a switch and a potentiometer. The inner shaft (Ø 3 mm) must be ordered separatly.

INNER SHAFT



For switches with mounting plate or hollow shaft. Hollow shaft must to be ordered separately. Please state exact length.

## SWITCH WITH TWO SHAFTS



Front panel cut out see on the pages before.

FRONT PANEL CUT OUT

It is possible to operate two switches individually on the same mounting by using two independently roating shafts. For ordering, the type number of each switch must be given and specified.



# **Specifications**

#### **MECHANICAL DATA**

Detent angle   positions:	30° detent angle   12 positions 36° detent angle   10 positions 60° detent angle   6 positions
Rotary limitation   end stop:	Configurable
Switching torque:	2, 4 or 6 Ncm (±25 % in new condition)
Rotational life:	> 25'000 cycles (tested at room temperature)
Allowed shaft load:	500 N push, 500 N pull and 100 N side load (static at 20 mm from the support surface)
Rotational stop strength:	30° detent angle: > 100 Ncm 36° and 60° detent angle: > 150 Ncm
Fastening torque of nut (front panel mounting):	M6 x 0.75: < 100 Ncm M8 x 0.75: < 300 Ncm M10 x 0.75: < 300 Ncm

#### **ELECTRICAL DATA**

Electrical connection:	Soldering eyelets Pins for PCB
Switching voltage:	< 42 VDC (resistive load)
Switching current:	< 2000 mA (resistive load)
Contact resistance:	< 10 mΩ (in new condition)
Switching capacity:	< 1 pF (between the contacts)
Switching function:	1 x 12 to 4 x 3 poles x positions per wafer, max. 2 wafers
Switching mode:	Shorting (for 30° and 36° detent angle) Non-shorting (for 30° and 60° detent angle)
Dielectric strength:	500 VDC during 60 s (pin-to-pin, pin-to-housing)
Insulation resistance:	> 1 GΩ at 500 VDC (pin-to-pin, pin-to-housing, in new condition)

#### MATERIALS

Shaft:	Stainless steel 1.4305	
Bushing   housing:	Nickel silver, fiberglass reinforced plastic	
Contact surface:	Cu alloy (Au plated)	
Insulation material:	Wafer: PEAK or ceramic Rotor: Polybutylen	
Soldering leads:	Cu alloy (Au plated)	
Hex nut:	Brass (nickel plated)	

#### **ENVIRONMENTAL DATA**

Operating temperature:	-40 to +85 °C (IEC 60068-2-14)	
Storage temperature:	-40 to +85 °C (IEC 60068-2-14)	
IP sealing against front panel:	IP60 without sealing IP68 with shaft and front panel sealing (2 bar, 1 h)	
Vibration:	10 G <sub>RMS</sub> at 10 to 2'000 Hz	
Flammability:	UL94-HB	
SOLDERING CONDITIONS		
Hand soldering:	< 340 °C during 2 s	
Wave soldering:	< 280 °C during 5 s	

©Copyright 2018 by Elma Electronic AG, CH-8620 Wetzikon. Subject to technical modifications, all data supplied without liability.

#### Please contact our sales team for more details.

China: +86 21 5866 5908 France: +33 388 56 72 50 Germany: +49 7231 97 34 0 Israel: +972 3 930 50 25 Singapore: +65 6479 8552 Switzerland: +41 44 933 41 11 United Kingdom: +44 1234 838 822 United States: +1 510 656 3400