

# F204 A-40/0,03



Products Low Voltage Products and Systems Modular DIN Rail Products Residual Current Devices RCDs  
Residual Current Devices RCDs

## General Information

<b>Extended Product Type:</b>	F204 A-40/0,03
<b>Product ID:</b>	2CSF204101R1400
<b>EAN:</b>	8012542783503
<b>Catalog Description:</b>	F204 A-40/0,03 Residual Current Dev.
<b>Long Description:</b>	The RCCBs F200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous and selective AC and A types is completed with some configurations for special applications.

## Additional Information

<b>Country of Origin:</b>	Italy (IT)
<b>Customs Tariff Number:</b>	85363030
<b>Data Sheet, Technical Information:</b>	2CSC400002D0209
<b>Declaration of Conformity - CE:</b>	2CSC423001D2701
<b>E-nummer:</b>	2160126
<b>EAN:</b>	8012542783503
<b>EPLAN Catalog Tree:</b>	Electrical engineering / Protection devices / Ground fault current circuit breaker
<b>EPLAN Function Definition:</b>	Ground fault current circuit-breaker / Ground fault current circuit breakers, 8 connection points / Ground fault current circuit breaker, four-pole 1 2 3 4 5 6 7 8
<b>ETIM 4:</b>	EC000003 - Residual current circuit breaker (RCCB)
<b>ETIM 5:</b>	EC000003 - Residual current circuit breaker (RCCB)
<b>ETIM 6:</b>	EC000003 - Residual current circuit breaker (RCCB)
<b>Environmental Information:</b>	S-P-00081
<b>Instructions and Manuals:</b>	2CSF423001D6402
<b>Invoice Description:</b>	F204 A-40/0,03 Residual Current Dev.
<b>Maximum Operating Voltage UL/CSA:</b>	480Y/277 V AC
<b>Minimum Order Quantity:</b>	1 piece
<b>Number of Poles:</b>	4
<b>Object Classification Code:</b>	Q
<b>Operating Characteristic:</b>	Instantaneous
<b>Options Provided:</b>	-
<b>Package Level 1 EAN:</b>	8012542783503
<b>Package Level 1 Gross Weight:</b>	0.403 kg
<b>Package Level 1 Height:</b>	0.078 m
<b>Package Level 1 Length:</b>	0.096 m
<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	0.082 m
<b>Position of Neutral Terminals:</b>	Right
<b>Power Loss:</b>	at Rated Operating Conditions per Pole 3.2 W
<b>Product Main Type:</b>	F200
<b>Product Name:</b>	Residual Current Device
<b>Product Net Depth:</b>	0.069 m
<b>Product Net Height:</b>	0.085 m
<b>Product Net Weight:</b>	0.360 kg
<b>Product Net Width:</b>	0.070 m
<b>Rated Current (I<sub>n</sub>):</b>	40 A

<b>Rated Frequency (f):</b>	50 ... 60 Hz
<b>Rated Operational Voltage:</b>	230 / 400 V AC
<b>Rated Residual Current:</b>	30 mA
<b>Rated Voltage (U<sub>r</sub>):</b>	230/400 V
<b>RoHS Information:</b>	2CSC423001K0201
<b>RoHS Status:</b>	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q3
<b>Selling Unit of Measure:</b>	piece
<b>Short Description:</b>	Residual Current Device F204 A-40/0,03
<b>Standards:</b>	IEC/EN 61008 UL 1053
<b>Type of Residual Current:</b>	A type
<b>Accessories Available:</b>	Yes

