



Order No: 0140CDJ

SOLDERING IRON i-TOOL TRACE, 150 W / 24 V

The i-TOOL TRACE soldering iron offers the user superior performance. The extremely lightweight and powerful fine soldering iron features 150 W power and SENSOTRONIC temperature control. This ensures very fast heat-up and even faster reheating, which ensures a stable temperature profile.

The automatic standby function guarantees economical and energy-efficient soldering. The adjustable standby parameters (timing, temperature) ensure an optimally coordinated usability of the soldering iron without unnecessary waiting times.

The thermally optimized tip design and a variety of different tip geometries bring the heat to the solder joint with pinpoint accuracy and cover a wide range of applications.

Tip'n'Turn is the patented concept for combining soldering tip and heating element. The bayonet lock allows the soldering tip to be changed quickly even when hot, either with the use of the 0A58 holder or by hand.

The heating element and tips can be changed separately so that each part only needs to be replaced when really necessary, thereby helping to save resources.

Technical data:

Temperature range: 50 °C - 450 °C

Nominal power: 150 W Secondary Voltage: 24 V Weight (g): 72 g

Scope of Supply:

Soldering iron i-TOOL TRACE (0140CDJ), Soldering tip ERSADUR (0142CDLF16/SB)

Matching soldering tips:

Tip series 142

Accessories:

Holder A 58 (0A58), Dry cleaner (0008M)