F3S-TGR-N□C

Hall coded non-contact switches monitor the status of guarding doors. Stainless steel housing for high hygiene demands in the food industry are available.

- Based on hall technology
- Connect up to 3 switches in series
- LED supports easy diagnosis
- Operates with all OMRON safety controllers
- · Operates behind stainless steel fittings
- Non-contact no abrasion no particles
- Compensation of mechanical tolerances
- Suitable for high pressure cleaning, CIP/SIP processes due IP69K (pre-wired types)
- Conforms to safety categories up PLe acc. EN ISO13849-1



Model Number Structure

F3S-TGR-N \square C-21- \square 3

Type

L: Elongated Sensor
S: Small Sensor
M: Miniature Sensor
B: Barell Sensor

2. Housing Material

P: Plastic Housing
M: Stainless Steel Housing

H: Hygienic designed Stainless Steel Housing
F: Special Food Type Stainless Steel Housing

3. Cable Length/connection

05: 5 m Cable

05-R*: 5 m Cable exit to the right

10: 10 m Cable

10-R*: 10 m Cable, exit to the right

M1J8: M12 male connector, 8 pin, fitted with 250 mm cable M1J8-R*: M12 male connector, 8 pin, fitted with 250 mm cable

exit to the right

* only for F3S-TGR-NMPC and F3S-TGR-NMHC

Ordering Information

Polyester Housing

| Туре | Cable connection | Contact configuration | Order code | |
|-------------------|---|-----------------------|------------------------|--|
| Elongated Sensors | 5 m pre-wired | | F3S-TGR-NLPC-21-05 | |
| | 10 m pre-wired | | F3S-TGR-NLPC-21-10 | |
| - | M12, 8 pin, fitted with 250 mm cable | | F3S-TGR-NLPC-21-M1J8 | |
| Small Sensors | 5 m pre-wired | - | F3S-TGR-NSPC-21-05 | |
| 1 | 10 m pre-wired | | F3S-TGR-NSPC-21-10 | |
| | M12, 8 pin, fitted with 250 mm cable | | F3S-TGR-NSPC-21-M1J8 | |
| | 5 m pre-wired | ONC/4NO | F3S-TGR-NMPC-21-05 | |
| Miniature Sensors | 10 m pre-wired | 2NC/1NO | F3S-TGR-NMPC-21-10 | |
| | M12, 8 pin, fitted with 250 mm cable | | F3S-TGR-NMPC-21-M1J8 | |
| | 5 m pre-wired, cable exit right | 1 | F3S-TGR-NMPC-21-05-R | |
| | 10 m pre-wired, cable exit right | | F3S-TGR-NMPC-21-10-R | |
| | M12, 8 pin, fitted with 250 mm cable exit right | = | F3S-TGR-NMPC-21-M1J8-R | |
| Barrel Sensors | 5 m pre-wired | 1 | F3S-TGR-NBPC-21-05 | |
| | 10 m pre-wired | 1 | F3S-TGR-NBPC-21-10 | |
| | M12, 8 pin, fitted with 250 mm cable | | F3S-TGR-NBPC-21-M1J8 | |

Stainless steel housing

| Туре | Cable connection | Contact configuration | Order code | |
|-------------------|--------------------------------------|-----------------------|----------------------|--|
| Elongated Sensors | 5 m pre-wired | | F3S-TGR-NLMC-21-05 | |
| 3 | 10 m pre-wired | | F3S-TGR-NLMC-21-10 | |
| 1 | M12, 8 pin, fitted with 250 mm cable | | F3S-TGR-NLMC-21-M1J8 | |
| Small Sensors | 5 m pre-wired | | F3S-TGR-NSMC-21-05 | |
| | 10 m pre-wired | 2NC/1NO | F3S-TGR-NSMC-21-10 | |
| 7.7 | M12, 8 pin, fitted with 250 mm cable | | F3S-TGR-NSMC-21-M1J8 | |
| Barrel Sensors | 5 m pre-wired | | F3S-TGR-NBMC-21-05 | |
| 200 | 10 m pre-wired | | F3S-TGR-NBMC-21-10 | |
| 6 S | M12, 8 pin, fitted with 250 mm cable | | F3S-TGR-NBMC-21-M1J8 | |

Hygienic and food types

| Туре | Cable connection | Contact configuration | Order code | |
|----------------------|---|-----------------------|------------------------|--|
| Small Sensors | 5 m pre-wired | | F3S-TGR-NSHC-21-05 | |
| | 10 m pre-wired | | F3S-TGR-NSHC-21-10 | |
| | M12, 8 pin, fitted with 250 mm cable | | F3S-TGR-NSHC-21-M1J8 | |
| Small Sensors | 5 m pre-wired | | F3S-TGR-NSFC-21-05 | |
| (Special food types) | 10 m pre-wired | | F3S-TGR-NSFC-21-10 | |
| | M12, 8 pin, fitted with 250 mm cable | 2NC/1NO | F3S-TGR-NSFC-21-M1J8 | |
| | 5 m pre-wired | | F3S-TGR-NMHC-21-05 | |
| Miniature Sensors | niature Sensors 10 m pre-wired | | F3S-TGR-NMHC-21-10 | |
| | M12, 8 pin, fitted with 250 mm cable | | F3S-TGR-NMHC-21-M1J8 | |
| | 5 m pre-wired, cable exit right | | F3S-TGR-NMHC-21-05-R | |
| | 10 m pre-wired, cable exit right | | F3S-TGR-NMHC-21-10-R | |
| | M12, 8 pin, fitted with 250 mm cable exit right | | F3S-TGR-NMHC-21-M1J8-R | |

Accessories

| | | Order code | |
|-----------------------------------|---|----------------------------|--|
| | 2 m | Y92E-M12PURSH8S2M-L | |
| Cables 9 nin | 5 m | Y92E-M12PURSH8S5M-L | |
| Cables 8-pin | 10 m | Y92E-M12PURSH8S10M-L | |
| | 25 m | Y92E-M12PURSH8S25M-L | |
| | M12 T-connector for M12 connector - types | F39-TGR-NT | |
| T | 0.6 m, M12-8pin | Y92E-M12FSM12MSPURSH806M-L | |
| T-connector connection ca- ble | 2 m, M12-8pin | Y92E-M12FSM12MSPURSH82M-L | |
| 5.0 | 5 m, M12-8pin | Y92E-M12FSM12MSPURSH85M-L | |
| | 10 m, M12-8pin | Y92E-M12FSM12MSPURSH810M-L | |
| | for F3S-TGR-NLPC | F39-TGR-NLPC-A | |
| | for F3S-TGR-NSPC | F39-TGR-NSPC-A | |
| | for F3S-TGR-NMPC | F39-TGR-NMPC-A | |
| | for F3S-TGR-NCPC | F39-TGR-NCPC-A | |
| | for F3S-TGR-NWPC | F39-TGR-NWPC-A | |
| Actuators | for F3S-TGR-NBPC | F39-TGR-NBPC-A | |
| Actuators | for F3S-TGR-NLMC | F39-TGR-NLMC-A | |
| | for F3S-TGR-NSMC | F39-TGR-NSMC-A | |
| | for F3S-TGR-NBMC | F39-TGR-NBMC-A | |
| | for F3S-TGR-NSHC | F39-TGR-NSHC-A | |
| | for F3S-TGR-NSFC | F39-TGR-NSFC-A | |
| | for F3S-TGR-NMHC | F39-TGR-NMHC-A | |
| Mounting screws | Set of Torx safety screws (M4, 4 × 30 mm, 4 × 20 mm, 4 × 10 mm; incl. washers and Torx bit) | F39-TGR-N-SCREWS | |

Control units

| | | Order code |
|-------------------------------------|------------|--|
| | G9SA G9SB | G9SA-301 G9SA-501 G9SA-321-T075 G9SA-321-T15 G9SA-321-T30 G9SB-2002-C G9SB-2002-A G9SB-200-B |
| Safety relay units | G9SX | G9SB-200-D G9SB-3012-A G9SB-301-B G9SB-3012-C G9SB-301-D G9SX-BC202-R_ G9SX-AD322-T15-R_ G9SX-AD322-T150-R_ G9SX-ADA222-T150-R_ G9SX-ADA222-T150-R_ |
| Programmable standalone controllers | G9SP-N | G9SP-N10S G9SP-N10D G9SP-N20S |
| Programmable network controllers | NE1A | NE1A-SCPU01-V1 |

Specifications

Mechanical data

| | | Plastic housing | Stainless steel housing |
|--------------------------------------|----------------|--|--|
| Indicator | _ | LED | |
| Operating distance | OFF → ON (Sao) | 8 mm: NMPC, NBPC 10 mm: NLPC, NSPC | 8 mm: NMHC, NBMC 10 mm: NLMC, NSMC, NSHC, NSFC |
| | ON → OFF (Sar) | 12 mm: NMPC, NBPC 20 mm: NLPC, NSPC | 12 mm: NMHC, NBMC 20 mm: NLMC, NSMC, NSHC, NSFC |
| Recommended setting gap | _ | 5 mm | • |
| Actuator approach apped | Min. | 4 mm/s | |
| Actuator approach speed | Max. | 1,000 mm/s | |
| Switching frequency | Max. | 1 Hz | |
| Operating temperature | - | –25 to 80°C | -25 to 105°C |
| Enclosure protection | Flying lead | IP69K | |
| Enclosure protection | M12 connector | IP67 | |
| Cable material | Flying lead | PVC, 8 core, Ø 6 mm o.d. | |
| Cable material | M12 connector | 250 mm, PVC, Ø 6 mm o.d. | |
| Mounting bolts | _ | 2 × M4 | |
| Tightening torque for mounting bolts | Max. | 1 Nm | |
| Shock resistance (IEC 68-2-27) | _ | 11 ms, 30 g | |
| Vibration resistance (IEC 68-2-6) | - | 10 to 55 Hz, 1 mm | |
| Material | - | Black polyester | Stainless steel 316 |

Electrical data

| | | Plastic housing | Stainless steel housing |
|-----------------------|------------------|------------------------|-------------------------|
| Sensor technology | _ | Hall | |
| Serial switching | - | up to 3 pcs. in series | |
| Power supply | - | 24 VDC ±10% | |
| Rated loads | NC contacts Max. | 0.2 A @ 24 VDC | |
| nateu loaus | NO contact Max. | 0.2 A @ 24 VDC | |
| Dielectric withstand | _ | 250 VAC | |
| Insulation resistance | _ | 100 ΜΩ | |
| Switching current | Min. | 1 mA, 10 VDC | |


Reliability data

| | Plastic housing | Stainless steel housing |
|--|--|-------------------------|
| EN ISO 13849-1 | up to PLe depending upon system architecture | |
| EN 62061 up to SIL3 depending upon system architecture | | cture |
| PFHd | 2.52 × 10 ⁻⁸ | |
| Proof test interval (Life) 47 years | | |
| MTTFd (@ nop: 8 cycles per hour) | 470 years | |

Approved standards

| EN standards certified by TÜV Rheinland |
|---|
| EN ISO13849-1 |
| EN 60204-1 |
| EN ISO 14119 |
| EN/IEC 60947-5-3 |
| UL 508, CSA C22.2 |
| BS 5304 |
| EN 1088 conformance |


Operating characteristics




5 mm misalignment tolerance after setting

Connection diagram

Cable version



M1J8-Connector version (M12 male)




Note: If the auxiliary circuit is not fitted or not used then cut and discard the yellow/green or yellow/pink conductors.

Dimensions

Elongated Sensor (Sensor/Actuator)


F3S-TGR-NLPC






F3S-TGR-NLMC






Small Sensor (Sensor/Actuator) F3S-TGR-NSPC






F3S-TGR-NSMC






F3S-TGR-NSHC







F3S-TGR-NSFC












Miniature Sensor (Sensor/Actuator, left side version)


F3S-TGR-NMPC














F3S-TGR-NMHC












Barrel Sensor (Sensor/Actuator)

F3S-TGR-NBPC F3S-TGR-NBMC






Wiring examples (Single head connection up to category 4 acc. EN954-1)


G9SB

Single Sensor Application with G9SB-2002-C

(up to Safety PLe acc. EN ISO 13849-1)




Series connection Application, up to 3 Sensors with G9SB-2002-C




G9SA

Single Sensor Application with G9SA-301

(up to Safety PLe acc. EN ISO 13849-1)




Series connection Application, up to 3 Sensors with G9SA-301




G9SP

Single Sensor Application with G9SP

(up to Safety PLe acc. EN ISO 13849-1)




Series connection Application, up to 3 Sensors with G9SP



T-Connector and Connection Cable

Series connection with 2 or 3 Sensors for example with G9SA-301



Safety Precautions

/!\ WARNING

Be sure to turn OFF the power before performing wiring. Do not touch charge parts (e.g., terminals) while power is ON. Doing so may result in electric shock.



Do not allow the actuator to come close to the switch with the door open. Doing so may cause machinery to start operating and may result in injury.



Keep actuators (magnets) away from magnetically sensitive equipment like PC harddisks, floppy disks etc. The magnetic field of the magnet will damage existing data.



Application Precautions

- Do not use the product in locations subject to explosive or flammable gases.
- · Do not use load currents exceeding the rated value.
- · Be sure to wire each conductor correctly.
- Be sure to confirm correct operation after completing mounting and adjustment.
- Do not drop or attempt to disassemble the product.
- Be sure to use the correct combination of switch and actuator.
- Use a power supply of the specified voltage. Do not use power supplies with large ripples or power supplies that intermittently generate incorrect voltages.
- Capacitors are consumable and require regular maintenance and inspection.

Installation Locations

Do not install the product in the following locations. Doing so may result in product failure or malfunction.

- · Locations subject to direct sunlight
- Locations subject to humidity levels outside the range 35% to 85% or subject to condensation due to extreme temperature changes
- · Locations subject to corrosive or flammable gases
- Locations subject to shocks or vibration in excess of the product ratings
- · Locations subject to dust (including iron dust) or salts

Take appropriate and sufficient countermeasures when using the product in the following locations.

- · Locations subject to static electricity or other forms of noise
- Locations subject to possible exposure to radioactivity
- · Locations subject to power supply lines
- It is advisable to mount the switches on non ferrous materials.
 The presence of ferrous material can effect switching sensitivity.

Solvents


Ensure that solvents, such as alcohol, thinner, trichloroethane, or gasoline do not adhere to the product. Solvents may cause markings to fade and components to deteriorate.

Guard Stops


/ CAUTION


Use guard stops in the way shown below to ensure that the switch and actuator do not make contact when the guard door is closed.






Mounting Direction






Using for Hinged Doors

On hinged doors, install the Sensor at an opening edge as shown below.



Mutual Interference

If the switch and actuator are mounted in parallel, be sure to separate them by at least 25 mm, as shown below.



F3S-TGR-N□C

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

Cat. No. E14E-EN-05

In the interest of product improvement, specifications are subject to change without notice.