

Over current switch, 2A, 1Np, C-Char, AC

Part no. FAZ-C2/1N Article no. 278662 Catalog No. FAZ-C2/1N



Similar to illustration

Delivery program			
Basic function			Miniature circuit-breakers
Number of poles			1 pole+N
Tripping characteristic			C
Application			Switchgear for industrial and advanced commercial applications
Rated current	In	Α	2

kA

15

FAZ

as required

Technical data

Product range

Rated switching capacity acc. to IEC/EN 60947-2

Electrical			
Standards			IEC/EN 60947-2 IEC/EN 60898
Rated operational voltage	U _e	V	
	U _e	V AC	240/415
		V DC	60 (per pole)
Rated switching capacity acc. to IEC/EN 60947-2		kA	15
Operational switching capacity		kA	7.5
Characteristic			B, C, D
Max. back-up fuse		A gL/gG	125
Selectivity Class			3
Lifespan	Operations		> 10000

Mechanical

Direction of incoming supply

Standard front dimension	ı	mm	45
Enclosure height	1	mm	80
Terminal protection			Finger and back-of-hand proof to BGV A2
Mounting width per pole	1	mm	17.5
Mounting			IEC/EN 60715 top-hat rail
Degree of Protection			IP20, IP40 (when fitted)
Terminals top and bottom			Twin-purpose terminals
Terminal capacities	1	mm ²	
	1	mm ²	1 x 25
	1	mm ²	2 x 10
Thickness of busbar material	1	mm	0.8 2
Mounting position			As required

Design verification as per IEC/EN 61439

Rated operational current for specified heat dissipation In A 2 Heat dissipation per pole, current-dependent Pvid W 1.5 Static heat dissipation, non-current-dependent Pvs W 0 Heat dissipation, non-current-dependent Pvs W 0 Heat dissipation capacity Pdiss W 0 Operating ambient temperature min. °C 40 Operating ambient temperature max.				
Heat dissipation per pole, current-dependent P _{vid} W 0 Equipment heat dissipation, current-dependent P _{vid} W 1.5 Static heat dissipation, non-current-dependent P _{vs} W 0 Heat dissipation capacity P _{diss} W 0 Operating ambient temperature min.	Fechnical data for design verification			
Equipment heat dissipation, current-dependent P_{vid} W 1.5 Static heat dissipation, non-current-dependent P_{vs} W 0 Heat dissipation capacity P_{diss} W 0 Operating ambient temperature min. °C -40	Rated operational current for specified heat dissipation	I_n	Α	2
Static heat dissipation, non-current-dependent P _{vs} W 0 Heat dissipation capacity P _{diss} W 0 Operating ambient temperature min. °C -40	Heat dissipation per pole, current-dependent	P _{vid}	W	0
Heat dissipation capacity Pdiss W 0 Operating ambient temperature min. C -40	Equipment heat dissipation, current-dependent	P _{vid}	W	1.5
Operating ambient temperature min. °C -40	Static heat dissipation, non-current-dependent	P _{vs}	W	0
	Heat dissipation capacity	P _{diss}	W	0
Operating ambient temperature max. °C 75	Operating ambient temperature min.		°C	-40
	Operating ambient temperature max.		°C	75

	linear, per +1 °C, results in a 0.5% reduction of current carrying capacity
EC/EN 61439 design verification	
10.2 Strength of materials and parts	
10.2.2 Corrosion resistance	Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures	Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat	Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects	Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation	Meets the product standard's requirements.
10.2.5 Lifting	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions	Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances	Meets the product standard's requirements.
10.5 Protection against electric shock	Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components	Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections	Is the panel builder's responsibility.
10.8 Connections for external conductors	Is the panel builder's responsibility.
10.9 Insulation properties	
10.9.2 Power-frequency electric strength	Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage	Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material	Is the panel builder's responsibility.
10.10 Temperature rise	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.


Technical data ETIM 6.0

Circuit breakers and fuses (EG000020) / Miniature circuit breaker (MCB) (EC000042)


Electric engineering, automation, process control engineering / Electrical installation, device / Miniature circuit breaker system (MCB) / Miniature circuit breaker (MCB) (ecl@ss8.1-27-14-19-01 [AAB905011])


[AAB905011])		
Release characteristic		C
Number of poles (total)		2
Number of protected poles		2
Nominal rated current	Α	2
Nominal rated voltage	V	230
Rated short-circuit breaking capacity Icn EN 60898 at 230 V	kA	10
Rated short-circuit breaking capacity Icn EN 60898 at 400 V	kA	10
Rated short-circuit breaking capacity Icu IEC 60947-2 at 230 V	kA	15
Rated short-circuit breaking capacity Icu IEC 60947-2 at 400 V	kA	15
Voltage type		AC
Current limiting class		3
Frequency	Hz	50 - 60
Concurrently switching N-neutral		Yes
Suitable for flush-mounted installation		No
Over voltage category		3
Pollution degree		2
Width in number of modular spacings		2
Built-in depth	mm	70.5
Additional equipment possible		Yes
Degree of protection (IP)		IP20


Characteristics




Let-through energy I²t According to IEC/EN 60898










Tripping characteristic at 30 °C: B, C, D to IEC/EN 60898

Dimensions



Additional product information (links)

AWA1220-1755 Circiut-breaker

AWA1220-1755 Circiut-breaker ftp://ftp.moeller.net/DOCUMENTA

ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/17550701.pdf