

CERTIFICATION, TROUBLESHOOTING and INSTALLATION tools

for professionals who install and maintain critical network cabling infrastructure.



Featured Copper Cable Test Solutions

www.flukenetworks.com/CopperTestingTools

CableIQ[™] Qualification Tester

- Works on live networks to provide Ethernet switch detection and link configuration
- Measure cabling performance (10/100/1000 Mbps)
- Diagnose opens, shorts, split pairs, insertion loss, crosstalk, noise issues
- Graphically maps wiring configuration and shows distance to faults
- Tests twisted-pair, coax, and audio
- Locate and trace cables with IntelliTone 200 Digital Probe (included with CIQ-KIT)

MicroScanner² **Cable Verifier**

- Displays cable length, wiremap, cable ID, and distance to fault • Detects Ethernet.
- POTS and PoE • Locates virtually any cable
- or wire pair with IntelliTone™ digital and analog toning
- Tests RJ11, RJ45, coax, with no adapters
- "Oversized" backlit LCD makes results crystal clear in any work environment

TS[°]100 Cable Fault Finder

- Measure cable length on spools
- Numeric distance display
- Identify pairs with SmartTone[™]
- generation technology
- Identify and locate distance to opens and shorts
- Works on any two or more conductor cable up to 3,000 feet (915 meters)

MicroMapper[™]

• Simple verification of wiremaps and identification of faults with LEDs



- Remote identifier enables one-person testing
- Built-in tone generator for tracing installed cables hidden in walls, floors and ceilings. Works with Pro3000[™] Tone and Probe (sold separately)



MultiFiber[™] Pro **MPO** Tester

- Automatic scanning and testing of all fibers in MPO connectors
- MM and SM versions available
- No more fan-out cords when testing MPO fiber trunks
- Easily interpret test results on 8 or 12 fibers with minimal navigation
- Automatically measures and reports polarity

SimpliFiber[®] Pro Power Meter / Light Source

- Multiple kit configurations with light sources for single mode, multimode and PON fiber optics
- Single-port, simultaneous dual-wavelength feature completes testing in half the time and saves measurements from both wavelengths into one record
- Min/Max capability automates • tracking of intermittent power fluctuations

Fiber QuickMap[™] / OneShot[™] PRO

- Quickly and efficiently locate connections and breaks
- QuickMap tests MM fiber to 1,500 meters (4,921 ft)
- OneShot PRO tests SM fiber to 23 km (15 mi)
- Simple set-up
- Six-second test timeeliminates lengthy blind troubleshooting
- Large display shows loss in dB and distance in meters or feet

VisiFault[™] **Visual Fault Locator**

- Locates tight bends, breaks and bad connectors
- Verifies polarity and identifies fibers
- Bright red visible laser light with continuous and flashing modes
- Ergonomic case survives drops, impacts and vibration



















Copper Cable Toners and Probes

www.flukenetworks.com/CopperTestingTools

Pro3000[™] Analog Tone and Probe


- Tone and trace on non-active networks
- Identify exact pair with SmartTone technology and five distinct tones



- Loud speaker on probe easy to hear through drywall, wood, and other material
- Clips allow easy access to individual pairs and RJ11 easily connects to telephone jacks—no need for adapters



- Digital toning eliminates noise and false signals
- SmartTone[™] analog toning isolates individual wire pairs



- Visible end-to-end continuity test
- Built in wire mapper
- Works on twisted pair, audio, and video cabling

	-					
	Pro 3000	Intelli- tone Pro	Micro- Mapper	TS100	MS2-100	CIQ-100
Port Location ID						
Digital Toning		1			1	1
Analog Toning	1	1	1	1	1	1
Switch Presence		1			1	1
VDV Service Detection					1	1
Cable Verification						-
Cable Wiremap		1	1		Graphical	Graphica
Cable Length				1	1	1
Qualified Cabling Speed (10/100/1000/VoIP)						1
Cable Troubleshooting						
Identify open/short	1	1	1	1	1	1
Distance to open/short				1	1	1
Locate crosstalk fault						1
Identify and locate impedance fault						1



Fiber Optic Cleaning Kits

- Eliminates the #1 cause of fiber optic link failure: contamination
- Supports all fiber connector types in datacenter and campus environments
- Quick Cleaners—easily clean fiber end-faces and ports
- Solvent pen precisely dispenses specially formulated fiber optic cleaning solution
- Cards for convenient cleaning of fiber end-face

FI-500 FiberInspector[™] Micro

Fiber Cleaning and Inspection www.flukenetworks.com/FiberInspectionTools

 PortBright[™] illumination to find ports in dark and dense panels Auto-focus for stable images in



- Includes 4 UPC tips (LC, SC, 1.25 mm and 2.50 mm)
- APC tips available

Quick Clean[™] Cleaners

- Available in 1.25 mm, 2.5 mm, and MPO styles Just push and the "click" lets you
- know it's done • Clean over 500 end-faces
- per unit • Tip extender to 208 mm for hard to reach connectors
- Used with OTDRs to characterize fiber links Standards

(TRCs)

• Used for

certifying

systems in

cabling



compliant reference grade connectors

accordance with standards

Reference grade connectors

Fiber Launch Cables

Test Reference Cords





Termination Tools

www.flukenetworks.com/TerminationTools

Termination Tools and Adapters

Ergonomic design, high-quality materials and Fluke Networks guality for separating, stripping and cutting wire. Perfect tools for your every job.







4 and 8 position Modular Adapters

Impact Tools

D914[™] Series Impact Tools

- Hook, spudger and blade storage tools are built into the handle
- Select low impact for 24/26 gauge wire or high impact for 22-gauge wire
- Optional Phillips-head or flat screwdriver blade
- Supports a variety of torque tool bits and sockets
- Easy blade insertion, locks in place
- D914S features soft touch rubber handle and ergonomic design



- Terminate jacks eight times faster than traditional impact tools. The patented design seats and terminates all wires simultaneously. Builtin blade cuts off the excess wire eliminating the need for a secondary trim step
- High-guality, consistent terminations
- Ergonomic design reduces hand fatigue
- Convenient, built-in stripper
- Multiple versions support several jack manufacturers

Pro-Tool[™] Kits

- Ergonomically designed Dur-a-Grip[™] pouch for convenient tool storage on belt
- D914[™] and D814[™] industry standard punchdown tools make for solid terminations
- Easy to use cable stripper quickly rings and slits many types of cable
- Probe Pic checks for loose or damaged connections
- Cut and strip wire with Electricians' D-Snips[™]
- Three kit combinations available



Telephone Butt-In Test Sets

www.flukenetworks.com/ButtInTestSets

Comparison Chart			The second se	The second second			
	TS [®] 54 TDR	TS®52 PRO	TS®22A	TS®22	TS®25D	TS [®] 30/ TS [®] 120*	TS®19
TDR for distance to Open, Shorts	1						
Built-in toner	1						
Display—backlit LCD and glow-in-the-the dark keypad	1	1			LCD only		
Extended range high-impedance DataSafe™ operation in monitor mode	1	1			1		
High-impedance DataSafe operation in monitor mode	1	1	1		 ✓ 	1	1
Data lockout protection	1	1			1		
DSL/POTS filtering technology	✓	1			 Image: A set of the set of the		
Low/high voltage indication	1	1			1		
Low current (mA) indication	1	1			1		
Over voltage and current protection	1	1	1	1	 ✓ 	1	
Waterproof—exceeds American Military Spec. MIL-STD-810E	1	1					
RainSafe [™] —safe in severe weather conditions	1	1	1	1		1	
DropSafe™—passes 20 foot (6 meter) drop test onto concrete	1	1	1	1		1	
Stores nine 18-digit numbers in repertory dialer (speed dialing)	1	1	1	1	1		





The System for Certifying, Managing and **Reporting on your Cabling Installation Projects**

ala ala ala .

www.flukenetworks.com/Versiv



Certify

DSX CableAnalyzer[™] Series **Copper Certification**

- Unmatched speed for Cat 5-8
- Graphically displays the source of failures including crosstalk, return loss and shield faults
- Meets TIA 2G and IEC Level V the most stringent accuracy requirements
- Endorsed by cabling vendors worldwide

Certification Management

Upload and consolidate test

results from remote sites

 Track last location used and calibration status of your



- Fastest time to certify—two fibers at two wavelengths in six seconds
- Encircled Flux compliant
- Single module performs both SM and MM testing
- SM testing to 130 km
- Built-in Visual Fault Locator

OptiFiber[®] Pro OTDR

- Industry's shortest event and attenuation dead zones
- Simple set-up and fast trace times
- EventMap[™] view negates the need for OTDR Trace Analysis
- Bi-directional testing from one end with SmartLoop[™]
- SM testing to 130 km
- Built-in Visual Fault Locator

Report

LinkWare[™] PC **Cable Test Management** Software

- Electronically save, maintain and archive test results
- Generate professional, customizable reports
- Provides a statistical view of your entire cable plant's performance
- Compliant with TIA 606-B



VERSIV makes you **MONEY**every time you use it

Versiv users report a 66% reduction in problems with testing and a 10% increase in overall profitability.



Fluke Networks operates in more than 50 countries worldwide. To find your local office contact details, go to www.flukenetworks.com/contact or call: 1-800-283-5853 ©2017 Fluke Corporation. Printed in U.S.A. 3/2017 7001151D

LinkWare Live

Manage

LinkWare[™] Live

devices

and cable ID's

entire fleet

Track project status from smart Create and manage test setups

Fluke Networks P.O. Box 777, Everett, WA USA 98206-0777



FI-7000

FiberInspector[™] **Pro**

• Automated Pass/Fail certification of fiber optic

connector end-faces

• Graphical indication of problem areas

• Compliant with IEC 61300-3-35

• Fully documents results using

LinkWare[™] PC or LinkWare[™] Live