




## BUILDING APPLICATIONS

# FLIR EXX-SERIES™

The FLIR E75, E85, E95, and the entry-level E53 Advanced Thermal Imaging Cameras bring superior sensitivity and a true 42° field of view\* together in a user-friendly, handheld platform. These cameras feature a vibrant 4" LCD that makes it easy to spot the subtle indications of building deficiencies and moisture intrusion. With built-in tools such as laser-assisted autofocus\*, on-screen area measurement†, and Wi-Fi capability, the FLIR Exx-Series will help you quantify and document air leaks, moisture, and other building problems.

[www.flir.com/Exx-Series](http://www.flir.com/Exx-Series)



### Find Hidden Deficiencies

Uncover hard-to-find building envelope deficiencies and moisture penetration

- Detects temperature differences down to 0.03°C for early identification of air leaks and moisture\*
- MSX® image enhancements add perspective to scenes, with edge detail on windows and doors
- The true 42° field of view (FOV) standard lens allows for surveys of wide areas with a single lens\*
- Measure the area (m² or or ft²) of moisture intrusion on screen† with data from laser-assisted autofocus\*



### Document Problems Quickly

Report problems in buildings for insurance claims, pre-insurance audits, and inspections

- Built-in voice annotation and customizable work folders makes finding and documenting problems easier and more efficient
- Connect over Wi-Fi to the FLIR Tools mobile app for faster reporting and sharing of images
- Append images with FLIR moisture meter data via the METERLiNK® connection
- Streamlined reporting features through FLIR Tools+ simplifies insurance claims and inspection paperwork



### Inspect More Efficiently

FLIR designed all four Exx-Series cameras to make your work faster, safer, and more efficient

- Vibrant, 4" touchscreen with 160° viewing angle
- Comfort-designed handle and convenient buttons enable safe, one-handed operation
- Rugged, water-tight chassis and scratch-resistant Dragontrail™ cover glass
- Backed by FLIR's industry-leading 2-5-10 warranty

\*E75, E85, E95 models

†E85, E95 models

SPECIFICATIONS

Features By Camera		E53	E75	E85	E95
IR Resolution		240 × 180 (43,200 pixels)	320 × 240 (76,800 pixels)	384 × 288 (110,592 pixels)	464 × 348 (161,472 pixels)
UltraMax®		—	307,200 pixels	442,368 pixels	645,888 pixels
Object Temperature Range		-20°C to 120°C (-4°F to 248°F) 0°C to 650°C (32°F to 1200°F)	-20°C to 120°C (-4°F to 248°F) 0°C to 650°C (32°F to 1200°F) Optional 300°C to 1000°C (572°F to 1830°F)	-20°C to 120°C (-4°F to 248°F) 0°C to 650°C (32°F to 1200°F) 300°C to 1200°C (572°F to 2192°F)	-20°C to 120°C (-4°F to 248°F) 0°C to 650°C (32°F to 1200°F) 300°C to 1500°C (572°F to 2732°F)
Focus		Manual	Continuous, one-shot laser distance meter (LDM), one-shot contrast, manual	Continuous, one-shot laser distance meter (LDM), one-shot contrast, manual	Continuous, one-shot laser distance meter (LDM), one-shot contrast, manual
Field of View (FOV)		24° × 18°	42° × 32° (10 mm lens), 24° × 18° (18 mm lens), 14° × 10° (29 mm lens)	42° × 32° (10 mm lens), 24° × 18° (18 mm lens), 14° × 10° (29 mm lens)	42° × 32° (10 mm lens), 24° × 18° (18 mm lens), 14° × 10° (29 mm lens)
Lens Identification		—	Automatic	Automatic	Automatic
Time-lapse (Infrared)		—	—	—	10 sec to 24 hours
Laser Area Measurement		—	—	Yes	Yes
Laser Distance Measurement		—	Yes, on-screen	Yes, on-screen	Yes, on-screen
Measurement Presets		No measurement, center spot, hot spot, cold spot, 3 spots, hot spot-spot*	No measurement, center spot, hot spot, cold spot, User Preset 1, User Preset 2	No measurement, center spot, hot spot, cold spot, User Preset 1, User Preset 2	No measurement, center spot, hot spot, cold spot, User Preset 1, User Preset 2
Spotmeter		3 in live mode	1 in live mode	3 in live mode	3 in live mode
Area		1 in live mode	1 in live mode	3 in live mode	3 in live mode
Picture-in-Picture		Centered infrared area on the visual image	Resizable and movable	Resizable and movable	Resizable and movable

Common Features	
Detector Type and Pitch	Uncooled microbolometer, 17 µm
Thermal Sensitivity/NETD	<0.04°C @ 30°C (86°F), 24° lens
Spectral Range	7.5 - 14.0 µm
Image Frequency	30 Hz
F-Number	f/1.3, 24° lens
Digital Zoom	1-4x continuous
Image Presentation and Modes	
Display	4", 640 × 480 pixel touch screen LCD with auto-rotation
Digital Camera	5 MP, 53° × 41° FOV
Color Palettes	Iron, Gray, Rainbow, Arctic, Lava, Rainbow HC
Image Modes	Infrared, visual, MSX®, Picture-in-Picture
MSX®	Embosses visual details on full resolution thermal image
Measurement and Analysis	
Accuracy	±2°C (±3.6°F) or ±2% of reading for ambient temperature 15°C to 35°C (59°F to 95°F) and object temperature above 0°C (32°F)
Alarms	Moisture alarm, insulation alarm, measurement alarms
Color Alarm (Isotherm)	Above/below/interval/condensation/insulation
Compass, GPS	Yes; automatic GPS image tagging
METERLINK®	Yes; several readings
Laser Pointer	Yes; dedicated button

\*Hot spot to center spot Delta measurement

Specifications are subject to change without notice.  
For the most up-to-date specs, go to [www.flir.com](http://www.flir.com)

**CORPORATE HEADQUARTERS**  
FLIR Systems, Inc.  
27700 SW Parkway Ave.  
Wilsonville, OR 97070  
PH: +1 877.773.3547

**LATIN AMERICA**  
FLIR Systems Brasil  
Av. Antonio Bardella, 320  
Sorocaba, SP 18085-852  
Brasil  
PH: +55 15 3238 7080

**CHINA**  
FLIR Systems Co., Ltd  
Rm 1613-16, Tower II  
Grand Central Plaza  
138 Shatin Rural Committee Rd.  
Shatin, New Territories  
Hong Kong  
PH: +852 2792 8955

**EUROPE**  
FLIR Systems, Inc.  
Luxemburgstraat 2  
2321 Meer  
Belgium  
PH: +32 (0) 3665 5100



The World's Sixth Sense®

Image Storage	
Storage Media	Removable SD card (8 GB)
Image File Format	Standard JPEG with measurement data included
Video Recording and Streaming	
Radiometric IR Video Recording	Real-time radiometric recording (.csq)
Non-Radiometric IR or Visual Video	H.264 to memory card
Radiometric IR Video Streaming	Yes, over UVC or Wi-Fi
Non-Radiometric IR Video Streaming	H.264 or MPEG-4 over Wi-Fi; MJPEG over UVC or Wi-Fi
Communication Interfaces	USB 2.0, Bluetooth, Wi-Fi, DisplayPort
Video Out	DisplayPort over USB Type-C
Additional Data	
Battery Type	Li-ion battery, charged in camera or on separate charger
Battery Operating Time	Approx. 2.5 hours at 25°C (77°F) ambient temperature and typical use
Operating Temperature Range	-15°C to 50°C (5°F to 122°F)
Storage Temperature Range	-40°C to 70°C (-40°F to 158°F)
Shock/Vibration/Encapsulation; Safety	25 g / IEC 60068-2-27, 2 g / IEC 60068-2-6, IP 54 /IEC 60529; EN/UL/CSA/PSE 60950-1
Weight/Dimensions	1 kg (2.2 lbs), 27.8 × 11.6 × 11.3 cm (11.0 × 4.6 × 4.4 in)
Box Contents	
Infrared camera with lens, battery (2 ea), battery charger, front protection, straps (hand, wrist), hard transport case, lanyards, lens caps, lens cleaning cloth, power supplies, 8 GB SD card, Torx wrench, cables (USB 2.0 A to USB Type-C, USB Type-C to USB Type-C, USB Type-C to HDMI)	

[www.flir.com](http://www.flir.com)  
NASDAQ: FLIR

Equipment described herein may require US Government authorization for export purposes. Diversion contrary to US law is prohibited. Imagery for illustration purposes only. Specifications are subject to change without notice. ©2018 FLIR Systems, Inc. All rights reserved. (03/18)

17-3307-INS-Exx BLD