

Router - FL MGuard RS4000 TX/TX VPN - 2200515

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Security appliance in metal housing, with extended temperature range, SD card slot, VPN for 10 VPN tunnels (optionally up to 250 with additional license), intelligent firewall with full scope of functions for maximum security and easy configuration, router with NAT/1:1 NAT, optional CIFS integrity monitoring

Why buy this product

- Maximum security
- Maximum performance
- Central management tool

RoHS

Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 597289
GTIN	4046356597289
Weight per Piece (excluding packing)	725.000 g
Custom tariff number	85176200
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	45 mm
Height	130 mm
Depth	114 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C

Router - FL MGUARD RS4000 TX/TX VPN - 2200515

Technical data

Ambient conditions

Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)

Interfaces

Interface 1	Ethernet
No. of ports	2 (RJ45 ports)
Connection method	RJ45
Transmission physics	Ethernet in RJ45 twisted pair
Transmission speed	10/100 Mbps
Transmission length	100 m (per segment)
Signal LEDs	Supply voltage, data transmission, error, link, activity
Interface 2	Signal contact
Connection method	Plug-in/screw connection via COMBICON
Interface 3	VPN - release button
Connection method	24 V DC/250 mA can be connected as an option

Function

Basic functions	Router with intelligent firewall and VPN for 10 tunnels (up to 250 supported with optional additional license), CIFS Integrity Monitoring (as an option), metal housing, slot for SD memory card, extended temperature range, high-performance firewall/VPN: up to 124 Mbps/40 Mbps
Supported browsers	HTTPS support required
Processor	330 MHz
Status and diagnostic indicators	LEDs:P1, P2, Fault, State, Error, LAN, WAN
Signal contact control voltage	24 V DC (typical)
Signal contact control current	250 mA (short-circuit resistant)

Security functions

Dynamic Host Configuration Protocol (DHCP) support	Server or Relay Agent
Network Time Protocol (NTP) client	Client
Link Layer Discovery Protocol (LLDP)	As per protocol 802.2
Remote Syslog Logging	On external server
Virtual private network (VPN) throughput	max. 40 Mbps (Router mode, VPN bidirectional throughput) max. 27 Mbps (Stealth mode, VPN bidirectional throughput)
Number of VPN tunnels	10 (up to 250 tunnels with additional license as an option)
Encryption methods	DES, 3DES, AES-128, -192, -256
Internet Protocol Security (IPsec) mode	ESP tunnel / ESP transport
Authentication	X.509v3 certificates with RSA or PSK
Data integrity	MD5, SHA-1
1:1 Network Address Translation (NAT) in the VPN	Supported
Firewall data throughput	max. 124 Mbps (Router mode, default firewall rules, bidirectional throughput)

Router - FL MGUARD RS4000 TX/TX VPN - 2200515

Technical data

Security functions

	max. 61 Mbps (Stealth mode, default firewall rules, bidirectional throughput)
Firewall rules	Configurable stateful inspection firewall with full scope of functions
Filtering	MAC and IP addresses, ports, protocols
Protection against	IP spoofing, DoS and Syn Flood Protection
Routing	Standard routing, NAT, 1:1-NAT, port forwarding

Network expansion parameters

Maximum conductor length (twisted pair)	100 m
---	-------

Supply voltage

Supply voltage	24 V DC (redundant)
Residual ripple	3.6 V _{pp} (within the permitted voltage range)
Supply voltage range	11 V DC ... 36 V DC
Typical current consumption	100 mA (at U _S = 24 V DC)
Max. current consumption	0.24 A

General

Mounting type	DIN rail
Type AX	Stand-alone
Net weight	725 g
Housing material	Metal

Conformity with EMC directives

Developed in acc. with standard	IEC 61000-6.2
Test standard	IEC 61000-4-2 (ESD)
Test result	6 kV contact discharge, 8 kV air discharge
Test standard	IEC 61000-4-3 (immunity to radiated interference)
Test result	10 V/m (80 MHz ... 2000 MHz)
Test standard	IEC 61000-4-4 (burst)
Test result	2 kV power line, 1kV data line
Test standard	IEC 61000-4-5 (surge)
Test result	power line: 2 kV (line/earth), 1 kV (line/line), 1kV data line
Test standard	IEC 61000-4-6 (immunity to conducted interference)
Test result	3 V (10 kHz ... 150 kHz), 10 V (150 kHz ... 80 MHz)

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Developed in acc. with standard	IEC 61000-6.2
Test standard	IEC 61000-4-2 (ESD)
Test result	6 kV contact discharge, 8 kV air discharge
Test standard	IEC 61000-4-3 (immunity to radiated interference)
Test result	10 V/m (80 MHz ... 2000 MHz)
Test standard	IEC 61000-4-4 (burst)

Router - FL MGUARD RS4000 TX/TX VPN - 2200515

Technical data

Standards and Regulations

Test result	2 kV power line, 1kV data line
Test standard	IEC 61000-4-5 (surge)
Test result	power line: 2 kV (line/earth), 1 kV (line/line), 1kV data line
Test standard	IEC 61000-4-6 (immunity to conducted interference)
Test result	3 V (10 kHz ... 150 kHz), 10 V (150 kHz ... 80 MHz)
Type of test	Shock in acc. with EN 60068-2-27/IEC 60068-2-27
Test result	Half-sine 30g, 18 ms, 3 axes
Type of test	Vibration resistance in acc. with EN 60068-2-6/IEC 60068-2-6
Test result	5g, 150 Hz
Noise emission	EN 55022 / Class B
Noise immunity	EN 61000-6-2:2005
Conformance	CE-compliant

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27240409
eCl@ss 4.1	27240409
eCl@ss 5.0	27242215
eCl@ss 5.1	19030101
eCl@ss 6.0	19170103
eCl@ss 7.0	19170103
eCl@ss 8.0	19170103
eCl@ss 9.0	19170103

ETIM

ETIM 3.0	EC001423
ETIM 4.0	EC001478
ETIM 5.0	EC001478
ETIM 6.0	EC001478

UNSPSC

UNSPSC 6.01	20142601
UNSPSC 7.0901	20142601
UNSPSC 11	20142601
UNSPSC 12.01	20142601
UNSPSC 13.2	43222609

Router - FL MGUARD RS4000 TX/TX VPN - 2200515

Approvals

Approvals

Approvals

EAC / EAC / UL Listed / cUL Listed / cULus Listed

Ex Approvals

UL Listed / cUL Listed / cULus Listed

Approval details

EAC		RU *- DE.A*30.B.01735
-----	--	--------------------------

EAC		EAC-Zulassung
-----	--	---------------

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
-----------	--	---	---------------

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
------------	--	---	---------------

cULus Listed			
--------------	--	--	--

Accessories

Accessories

License

License - FL MGUARD LIC FW/VPN RD - 2702193



License for activating the firewall/router and VPN redundancy function on an FL MGUARD device pair

Router - FL MGuard RS4000 TX/TX VPN - 2200515

Accessories

License - FL MGuard LIC FW RD - 2701356



License for activating the firewall/router redundancy function on an FL MGuard device pair

License - FL MGuard LIC LIFETIME FW - 2700184



License for lifetime software update of FL MGuard field devices.

License - FL MGuard LIC CIM - 2701083



License for activating CIFS Integrity Monitoring (CIM) on an FL MGuard

License - FL MGuard LIC VPN-10 - 2700194



License for up to 10 additional VPN online connections

License - FL MGuard LIC VPN-250 - 2700193



License for up to 250 additional VPN online connections

Router - FL MGuard RS4000 TX/TX VPN - 2200515

Accessories

License - FL MGuard LIC OPC INSP - 2702191



License for activating the OPC inspector function on an FL MGuard

License - FL MGuard LIC VPN-100 - 2702546



License for up to 100 additional VPN online connections

Parameterization memory

Memory - SD FLASH 512MB - 2988146



Program and configuration memory, plug-in, 512 Mbyte.

Remote control software

License - MGuard SECURE VPN CLIENT LIC - 2702579



License for mGuard Secure VPN Client v10.0x
