\$FLIR




PRO-GRADE THERMAL CAMERAS FOR SMARTPHONES

FLIR ONE® Pro-Series

The FLIR ONE Pro and FLIR ONE Pro LT give you the power to find invisible problems faster than ever. With robust features such as multiple temperature meters and level/span controls, FLIR ONE Pro cameras work as hard as you do. The revolutionary VividIR[™] image processing helps you see more details, FLIR MSX[®] adds sharpness and perspective, and the FLIR OneFit[™] adjustable connector extends up to 4 mm to fit many popular protective cases. Whether you're inspecting electrical panels, looking for HVAC problems, or finding water damage, the FLIR ONE Pro and FLIR ONE Pro LT are tools no serious professional should be without.

www.flir.com/flironepro



VividIR[™] IMAGE PROCESSING

Detect problems with precision thanks to the FLIR ONE Pro-Series' enhanced processing power

- Unique image processing technique generates images with up to 4x as many pixels for improved temperature measurement accuracy
- Enhances native IR resolution to output crisply detailed thermal images that are easy to interpret
- When combined with MSX[®]—which enhances thermal images with visual details—the FLIR ONE Pro-Series offers unsurpassed image quality for a mobile IR solution

PRO AND PRO LT MODELS

Get great results from the Pro LT or upgrade to the FLIR ONE Pro for higher resolution and improved sensitivity

- Choose the FLIR ONE Pro to record crisp 19,200 pixel IR images at a thermal sensitivity of 70 mK
- Record images with better clarity and temperature measurement accuracy by putting more pixels on the target
- Measure temperatures up to 400°C (752°F) with the FLIR ONE Pro, compared to a temperature maximum of 120°C (248°F) with the Pro LT

HARD-WORKING APP Advanced, work-based features mean more

professional problem solving and functionality

- Set multiple temperature spot meters and regions of interest for concurrent measurements
- See around corners or into awkward spaces by connecting to an Apple Watch or Android smartwatch
- Access real-time thermal tips through the FLIR ONE app and prepare professional reports through FLIR Tools[®] mobile app

SPECIFICATIONS

Specifications by product	FLIR ONE Pro LT	FLIR ONE Pro
Thermal pixel size	17 µm	12 µm
Thermal resolution	4,800 pixels (80 × 60)	19,200 pixels (160 × 120)
Thermal sensitivity	100 mK	70 mK
Object temperature range	-20°C to 120°C (-4°F to 248°F)	-20°C to 400°C (-4°F to 752°F)
Common features	'	'
Certifications	MFi (iOS version), RoHS, CE/ FCC, CEC-BC, EN62133	
Operating temperature	0°C to 35°C (32°F to 95°F), battery charging 0°C to 30°C (32°F to 86°F)	
Non-operating temperature	-20°C to 60°C (-4°F to 140°F)	
Size (w \times h \times d)	68 × 34 × 14 mm (2.7 × 1.3 × 0.6 in)	
Weight (incl. battery)	36.5 g	
Mechanical shock	Drop from 1.8 m (5.9 ft)	
Optical data		
Spectral range	8 – 14 μm	
Visual resolution	1440 × 1080	
HFOV / VFOV	50° ±1° / 43° ±1°	
Frame rate	8.7 Hz	
Focus	Fixed 15 cm — infinity	
Measurement		
Accuracy	$\pm 3^{\circ}$ C (5.4°F) or $\pm 5\%$, ty the difference between scene temperature. App after start-up when the to 35°C (59°F to 95°F) a within 5°C to 120°C (41	ambient and blicable 60 sec unit is within 15°C and the scene is
Emissivity correction	Matte, Semi-Matte, Semi-Glossy, Glossy	
Measurement correction	Emissivity; Reflected a	pparent

temperature (22°C / 72°F)

Shutter	Automatic/Manual
Power	
Battery life	Approximately 1 hr
Battery charge time	40 min
Interfaces	
Video	Male Lightning (iOS), Male USB-C (Android), Micro-USB (Android)
Charging	Female USB-C (5V/1A)
Арр	
Image presentation modes	Infrared, visual, MSX, gallery
VividIR	Yes
VividIR Palettes	Yes Gray (white hot), Hottest, Coldest, Iron, Rainbow, Rainbow HC, Arctic, Lava, and Wheel
	Gray (white hot), Hottest, Coldest, Iron, Rainbow,
Palettes	Gray (white hot), Hottest, Coldest, Iron, Rainbow, Rainbow HC, Arctic, Lava, and Wheel
Palettes Capture modes Video and still image	Gray (white hot), Hottest, Coldest, Iron, Rainbow, Rainbow HC, Arctic, Lava, and Wheel Video, photo, time-lapse
Palettes Capture modes Video and still image display/capture	Gray (white hot), Hottest, Coldest, Iron, Rainbow, Rainbow HC, Arctic, Lava, and Wheel Video, photo, time-lapse Saved as 1440 × 1080 Radiometric JPG, MPEG-4 (file format
Palettes Capture modes Video and still image display/capture File formats	Gray (white hot), Hottest, Coldest, Iron, Rainbow, Rainbow HC, Arctic, Lava, and Wheel Video, photo, time-lapse Saved as 1440 × 1080 Radiometric JPG, MPEG-4 (file format MOV (iOS), MP4 (Android))



Specifications are subject to change without notice. For the most up-to-date specs, go to www.flir.com

CORPORATE HEADQUARTERS FLIR Systems, Inc.

27700 SW Parkway Ave. Wilsonville, OR 97070 PH: +1 877.773.3547

LATIN AMERICA FLIR Systems Brasil Av. Antonio Bardella, 320 Sorocaba, SP 18085-852 Brasil PH: +55 15 3238 7080



CHINA

FLIR Systems Co., Ltd Rm 1613-16, Tower II Grand Central Plaza 138 Shatin Rural Committee Rd. Shatin, New Territories Hong Kong PH: +852 2792 8955

EUROPE

The World's Sixth Sense®

FLIR Systems, Inc. Luxemburgstraat 2 2321 Meer Belgium PH: +32 (0) 3665 5100 www.flir.com NASDAQ: FLIR

Equipment described herein is subject to US export regulations and may require a license prior to export. Diversion contrary to US law is prohibited. Imagery for illustration purposes only. Specifications are subject to change without notice. ©2018 FLIR Systems, Inc. All rights reserved. 06/18

18-1165-INS_EMEA