

## FLIR CM276<sup>™</sup> Clamp Meter and Thermal Imaging Camera with METERLiNK<sup>®</sup>

# Key Features:

- Reduces inspection and troubleshooting time for solar photovoltaic, electrical, and mechanical systems with its advanced thermal and visual camera.
- IGM™ (Infrared Guided Measurement) for safer non-contact thermal inspections.
- Advanced connectivity and analysis through the METERLiNK® app.

### Main Applications:

- For the inspection of critical assets found in commercial property, data centers, production, and manufacturing facilities. Streamline inspections and troubleshooting while taking key measurements, collecting data and preparing reports.
- Used by solar farm managers and technicians to quickly detect PV cell issues and provide thorough, efficient analysis of PV systems, reducing overall toolkit costs (1500 V PV test leads optional).
- Ideal for electrical service providers to large facilities who incorporate thermal imaging and visual documentation into their services, aligning with NFPA 70B requirements.

www.flir.com/CM276

Image modes	Thermal MSX (Multi Spectral Dynamic Imaging) Thermal camera only Digital camera only	
Visual Imaging		
Resolution	2 MP (1600 × 1200 pixels)	
Focus	Fixed	
Field of view	71° × 56°	
Measurement & Analysis		
AC/DC current	Range 600.0 A / Basic accuracy ±2.0%	
AC/DC voltage	Range 1000 V / Basic accuracy ±1.0%	
Auto range	Yes, with manual range option	
Capacitance	Range 1000 µF / Basic accuracy ±1.0%	
Continuity check threshold	${<}30~\Omega$ beeper on, ${>}150~\Omega$ beeper off	
Diode	Range 1.5 V / Basic accuracy ±1.5%	
Flex input AC A	Range 3000 A / Basic accuracy ±1.0%	
Flex input frequency counter	Range 10.00 kHz / Basic accuracy ±0.1%	
Inrush AC current	Range 600.0 A / Basic accuracy ±3.0%	
(continued)		

This product is subject to United States export regulations and may require US authorization prior to export, reexport, or transfer to non-US persons or parties. Diversion contrary to US law is prohibited For assistance with confirming the Jurisdiction & Classification of Teledyne FLIR, LLC products, please contact exportquestions@fiir.com. @2023 Teledyne FLIR, LLC. All rights reserved.

Revised 12/13/23 FLIR\_CM276\_datasheet-A4-23-1205

## SPECIFICATIONS

Thermal Imaging	
Color palettes	Iron, rainbow, arctic, white hot, and black hot
Display size	2.4 in TFT screen
Field of view [V x H]	44° × 57°
Focus	Fixed
Storage media	eMMC 8 GB
IR resolution	160 × 120 (19,200 pixels)
Sensitivity	150 mK
IR imaging spectral response	8 µm to 14 µm
Thermal imaging detector	FLIR Lepton® microbolometer
IR temperature measurement range	-10°C to 300°C (14°F to 572°F)
IR temperature resolution	0.1°C (0.1°F)
IR temperature accuracy	$\pm 3^\circ \text{C}$ (5.4°F) or $\pm 3\%$ of the reading; whichever is greater
Emissivity adjustment	0.10 to 1.00 (default is 0.95); select from three presets or set manually
Laser pointer type	Class 1
Laser pointer power	≤0.39 mW
Laser wavelength	640 nm to 660 nm

For more information and to find your local support number, visit: **FLIR.com/contactsupport www.FLIR.com** 



# FLIR CM276<sup>™</sup>

Clamp Meter and Thermal Imaging Camera with METERLiNK®

#### SPECIFICATIONS, CONT.

LoZ mode AC voltage	Range 60.00 V, 600.0 V, 1000 V / Basic accuracy $\pm 1.0\%$	
LoZ mode DC voltage	Range 60.00 V, 600.0 V, 1000 V / Basic accuracy ±1.0%	
Measuring rate	3 samples per second	
Resistance	Range 60K $\Omega$ / Basic accuracy ±1.0%	
Temperature accuracy	±3°C (5.4°F) or ±3% of rdg; whichever is greater	
Temperature range	-10°C to 300°C (14°F to 572°F)	
True RMS	Yes	
VFD AC current	Range 600.0 A / Basic accuracy ±2.0%	
VFD AC voltage	Range 1000 V / Basic accuracy ±1.0%	
PV DC V	Range 1000 V / Basic accuracy ±2.0% with TA82 Range 1500 V / Basic accuracy ±2.0% with TA85/TA86 (optional accessories)	
PV DC power	Range 900 kVA / Basic accuracy ±2.0%	
Communication & Data Storage		
Connectivity	Bluetooth®	
Data logging & storage	10 sets of 40K scalar measurements, 30K images	
Power		
Auto power off	For device: option to OFF, 2, 5, or 10 minutes For worklight only: option to OFF, 5, 15, or 30 minutes	
Battery	Rechargeable 3.7 V, 5400 mAh LiPo	
General		
Size (L x W x H)	272 mm × 100 mm × 51.5 mm (10.7 in × 3.94 in × 2.0 in)	
Weight	560 g (19.8 oz)	
Jaw opening	35 mm (1.37 in)	
IP rating	IP40	
Worklights	2 × white LED	
In the box	FLIR CM276 Clamp Meter, CAT IV 600 V Silicone Test Leads (TA82), USB Type-A to Type-C Cable, Soft Carrying Case, FLIR Quick Start Guide, FLIR Warranty Card	
Environmental & Certification	ons	
Drop test	2 m (6.5 ft)	
Warranty	10 year	

Specifications subject to change.	For the most up-to-date specifications, please visit flir.com.	
opeenications subject to enalige.	Tor the most up to date specifications, picase visit inteorn.	



For more information and to find your local support number, visit: **FLIR.com/contactsupport www.FLIR.com** 

Ordering Information	Order #
FLIR CM276 IGM Clamp Meter with METERLiNK	793950392768
FLIR TA85 PV Test Leads	793950377857
FLIR TA86 MC4 PV Plugs	793950377864

This product is subject to United States export regulations and may require US authorization prior to export, reexport, or transfer to non-US persons or parties. Diversion contrary to US law is prohibited. For assistance with confirming the Jurisdiction & Classification of Teledyne FLIR, LLC products, please contact exportquestions@flir.com. @2023 Teledyne FLIR, LLC. All rights reserved.

Revised 12/13/23 FLIR\_CM276\_datasheet-A4-23-1205