



Digital residual current circuit-breaker, 25A, 4p, 30mA, type G/B

Part no. FRCDM-25/4/003-G/B
Article no. 167892
Catalog No. FRCDM-25/4/003-G/B

Similar to illustration

Delivery programme

Basic function			Residual current circuit breakers , digital
Pole			4 pole
Application			Switchgear for industrial and commercial applications
Rated current	I_n	A	25
Rated short-circuit strength	I_{cn}	kA	10 with back-up fuse
Rated fault current	$I_{\Delta N}$	A	0.03
Type			Type G/B (ÖVE E 8601)
Tripping		A	Short time-delayed
Product range			FRCDM
Sensitivity			All current sensitive
Impulse withstand current			Surge-proof, 3 kA
Contact sequence			

Technical data

Electrical

Types conform to			IEC/EN 61008 IEC/EN 62423 ÖVE E 8601
Current test marks			As per inscription
Tripping		A	10 ms delayed
Rated operating voltage	U_n	V AC	240/415
Rated frequency	f	Hz	50
Limit values of the operating voltage			
electronic		V AC	50 - 456
Test circuit		V AC	196 - 264
Rated fault current	$I_{\Delta n}$	mA	30
Sensitivity			All current sensitive
Rated insulation voltage	U_i	V	440
Rated impulse withstand voltage	U_{imp}	kV	4 (1.2/50µs)
Rated short-circuit strength	I_{cn}	kA	10 with back-up fuse
Impulse withstand current			3 kA (8/20 µs) surge-proof
Max. admissible back-up fuse			
Short-circuit	gG/gL	A	63
Overload	gG/gL	A	63
Rated making and breaking capacity / Rated residual making and breaking capacity	$I_m / I_{\Delta m}$	A	500
lifespan			
Electrical		Operation	2000
Mechanical		Operation	10000

Dry auxiliary contact

Rated switching capacity			
30 VDC (resistive load)		A	2
240 VAC (resistive load)		A	0.25

Max. switching duty (resistive load)	W	60
Max. switching voltage AC	V	240
Max. switching voltage DC	V	220
Maximum switching current	A	2
Min. switching capacity (reference value)		10 μ A, 10 mV DC
lifespan		
Electrical (at 20 switching operations per minute) 2 A 30 VDC resistive load	Operations	$\geq 10^5$
Electrical (at 20 switching operations per minute) 1 A 30 VDC resistive load	Operations	$\geq 5 \times 10^5$
Terminal capacity	mm ²	0.25 - 1.5

Mechanical

Standard front dimension	mm	45
Device height	mm	80
Built-in width	mm	70 (4TE)
Mounting		Quick attachment with 2 latch positions for DIN-rail IEC/EN 60715
Degree of Protection		IP20 switches IP 40 enclosed
Terminals top and bottom		Twin-purpose terminals
Terminal protection		Busbar tag shroud to BGV A3, ÖVE-EN 6
Terminal cross-section		
Solid	mm ²	1.5 - 35
Stranded	mm ²	2 x 16
Terminal cross-section		M5 (with cross-recessed screw as defined in EN ISO 4757-Z2, Pozidriv PZ2)
Tightening torque of fixing screws	N/m	2 - 2.4
Thickness of busbar material	mm	0.8 - 2
Admissible ambient temperature range	°C	-25 - +55
Permissible storage and transport temperatures	°C	-35 - +60
Climatic proofing		according to IEC/EN 61008
Mounting position		As required
Contact position indicator		red / green
Trip indication		white / blue

Design verification as per IEC/EN 61439


Technical data for design verification			
Rated operational current for specified heat dissipation	I_n	A	25
Heat dissipation per pole, current-dependent	P_{vid}	W	0
Equipment heat dissipation, current-dependent	P_{vid}	W	4.6
Static heat dissipation, non-current-dependent	P_{vs}	W	0
Heat dissipation capacity	P_{diss}	W	0
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	55
			0
IEC/EN 61439 design verification			
10.2 Strength of materials and parts			
10.2.2 Corrosion resistance			
10.2.2.1 Verification of thermal stability of enclosures			Meets the product standard's requirements.
10.2.2.2 Verification of resistance of insulating materials to normal heat			Meets the product standard's requirements.
10.2.2.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects			Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation			Meets the product standard's requirements.
10.2.5 Lifting			Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact			Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions			Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES			Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances			Meets the product standard's requirements.
10.5 Protection against electric shock			Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9 Insulation properties		
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 6.0


Circuit breakers and fuses (EG000020) / Residual current circuit breaker (RCCB) (EC000003)		
Electric engineering, automation, process control engineering / Electrical installation, device / Residual current protection system / Residual current circuit breaker (RCCB) (ecl@ss8.1-27-14-22-01 [AAB906011])		
Number of poles		4
Nominal rated voltage	V	415
Nominal rated current	A	25
Rated fault current	A	0.03
Mounting method		DIN rail
Leakage current type		B
Selective protection		No
Short-circuit breaking capacity (I _{cn})	kA	10
Surge current capacity	kA	3
Frequency		50 Hz
Additional equipment possible		Yes
Degree of protection (IP)		IP20
Construction size (in accordance with DIN 43880)		1
Width in number of modular spacings		4
Built-in depth	mm	70.5
Short-time delayed tripping		Yes

Characteristics



Tripping current frequency range: | FRCdM, 30 mA, type B

Dimensions



Additional product information (links)

Product overview (Web)

<http://www.eaton.eu/Europe/Electrical/ProductsServices/CircuitProtection/DigitalCircuitBreakers/index.htm>