# FLUKE ®

# 566 and 568 Multipurpose Thermometers



Fluke 568



The Fluke 566 and included accessories



The Fluke 568 and included accessories

## Included accessories

FlukeView\* Forms software (568 only), USB cable (568 only), K-type thermocouple bead probe, 2 AA batteries, hard carrying case, quick start guide, and users manual.

#### Ordering information

Fluke 566 Infrared thermometer Fluke 568 Infrared thermometer

11344-eng Rev. 01

# The two-in-one infrared and contact thermometer with an innovative graphical display

With a straight-forward, menu-driven user interface and graphical display, the Fluke 566 and 568 multipurpose thermometers make even complex temperature measurements easy. Quickly navigate and adjust emissivity, start data logging, or turn on and off alarms, with just a few pushes of a button. For added convenience, both rugged handheld thermometers combine contact and non-contact temperature measurement capability, providing a total temperature measurement solution for any service and maintenance program.

- Easily access advanced features with the soft-key buttons and graphical display
- Measure smaller targets from farther away using the IR thermometer
- Adjustable emissivity and built-in table of common materials for higher IR accuracy
- Quickly identify problems with the MIN, MAX, AVG, and DIF functions
- 2-color flashing alarm alerts you visually when measurements exceed limits
- Includes Type K thermocouple bead probe
- Compatible with all standard miniconnector K-type thermocouples
- Data logging with a date/time stamp
- Soft rubber boot for increased ruggedness
- User interface available in 6 languages



Choose your language



Select the measurement surface



See complete measurement details in seconds

# **Product specifications**

(Check the Fluke web for detailed specifications)

	566	568	
Infrared temperature range	-40 °C to 650 °C	-40 °C to 800 °C	
Infrared accuracy	$<$ 0 °C : $\pm$ (1.0 °C + 0.1°/1 °C); > 0 °C : $\pm$ 1 % or $\pm$ 1.0 °C, whichever is greater		
Display resolution	0.1	0.1 °C	
Infrared spectral response	8 μm to 14 μm		
Infrared response time	< 500 msec		
Input temperature range	-270 °C to 1372 °C		
Input accuracy	-270 °C to -40 °C: $\pm$ (1 °C + 0.2 °/1 °C) -40 °C to 1372 °C: $\pm$ 1 % or 1 °C, whichever is greater		
D:S (Distance to measurement spot size)	30:1	50:1	
Laser sighting	Single-point laser < 1 mw output Class 2 (II) operation, 630 nm to 670 nm		
Minimum spot size	19 mm		
Emissivity adjustment		By built-in table of common materials or digitally adjustable from 0.10 to 1.00 by 0.01	
Data logging with Date/Time stamp	20 points	99 points	
PC interface and cable	None	USB 2.0 with FlukeView <sup>®</sup> Forms software	
Hi/Low alarms	Audible and two-color visual		
Min/Max/Avg/Dif	Yes		
Display	Dot matrix 98 x 96 pi	Dot matrix 98 x 96 pixels with function menus	
Backlight	Two levels, normal and extra bright for darker environments		
Trigger Lock	Yes		
Switchable between Celsius and Fahrenheit	Ye	Yes	

Power: 2 AA/LR6 Batteries (566); 2 AA/LR6 Batteries and USB for use with a PC (568) Battery life: Used continuously; laser and backlight on: 12 hours; laser and backlight off: 100 hours

Weight: 0.965 kg (566); 1.026 kg (568) Size (HxLxW):  $25.4 \text{ cm} \times 19.1 \text{ cm} \times 6.9 \text{ cm}$  Operating temperature:  $0 ^{\circ}\text{C}$  to  $50 ^{\circ}\text{C}$  Storage temperature:  $-20 ^{\circ}\text{C}$  to  $60 ^{\circ}\text{C}$  Two years warranty

### **Recommended Accessories**



H6 Infrared Thermometer



80PK-8
Pipe Clamp
Temperature
Probe



80PK-9 General



9



80PK-11 80PK-25 Velor SureGrip Temperature Piercing Probe Probe

80PK-26 SureGrip General Purpose Probe