

FLUKE®

ScopeMeter® 190 Series and ScopeMeter® 120 Series

Technical Data











ScopeMeter 190 Series: Speed, performance and analysis power

For demanding applications, the ScopeMeter 190C and 190B Series high-performance oscilloscopes offer specifications usually found on top-end bench instruments. They're ideal for engineers who need the full capabilities of a high-performance scope in a handheld, battery powered instrument.

- ✓ Dual input 200, 100 or 60 MHz bandwidth
- \checkmark Up to 2.5 GS/s real-time sampling per input
- Choice between a high resolution Color (190C) or Black and White (190B) display
- High waveform resolution of 3000 datapoints per channel
- Digital Persistence for analyzing complex dynamic waveforms like on an analog scope (190C Series)
- Fast display update rate for seeing dynamic behavior instantaneously
- ✓ Connect-and-View[™] automatic triggering, a full
- Range of manual trigger modes plus external triggering
- ✓ Frequency Spectrum using FFT analysis (190C)
- 27,500 points per input record length using ScopeRecord™ mode
- ✓ Automatic capture and replay of 100 screens
- ✓ Four hours rechargeable NiMH battery pack
- ✓ 1,000V CAT II and 600V CAT III safety certified
- ✓ Up to 1,000V independently floating isolated inputs

ScopeMeter 120 Series: Three-in-one simplicity

The compact ScopeMeter 120 Series is the rugged solution for industrial troubleshooting and installation applications. It's a truly integrated test tool, with oscilloscope, multimeter and "paperless" recorder in one affordable, easy-to-use instrument. Find fast answers to problems in machinery, instrumentation, control and power systems.

- A dual input 40 MHz or 20 MHz digital oscilloscope
- ☑ Two 5,000 counts true-rms digital multimeters
- Cursor measurements (Fluke 124)
- ✓ A dual input TrendPlot[™] recorder
- ✓ Connect-and-View[™] trigger simplicity for handsoff operation
- Shielded test leads for oscilloscope, resistance, continuity and capacitance measurements
- ✓ Up to seven hours battery operation
- 600V CAT III safety certified
- ✓ Optically isolated RS-232 interface
- Rugged, compact case

Technical Specifications 190C and 190B Series

OSCILLOSCOPE MODE VERTICAL DEFLECTION

	Fluke 199C Fluke 199B	Fluke 196C, Fluke 196B	Fluke 192B	
Bandwidth	200 MHz	100 MHz	60 MHz	
Rise time	1.7 ns	3.5 ns	5.8 ns	

Bandwidth limiter User selectable: 10 kHz, 20 MHz or off

Number of inputs 2 plus external trigger. All inputs isolated from

each other and ground.

Input coupling
AC or DC, with ground level indicator
Input sensitivity
2 mV/div to 100 V/div (Fluke 190C Series);
5 mV/div to 100 V/div (Fluke 190B Series)
Normal/Invert
On both input channels; switched separately
Variable Attenuator
Variable Gain on input channel A

Variable Attenuator Variable Gain on input channel A Input voltage 1000V CAT II, 600 V CAT III rated - See 'general

specifications' for further details.

Vertical resolution 8 bit

Accuracy \pm (1.5% of reading + 0.04 x range/div)

Input impedance 1 $M\Omega \pm 1\%$ // 15 pF \pm 2 pF

HORIZONTAL

Fluke 199C	Fluke 196C	Fluke 192B
Fluke 199B	Fluke 196B	
2.5 GS/s	1 GS/s	500 MS/s
2	2	2
5 ns	10 ns/div	
to 5	to 5 s/div	
	Fluke 199B 2.5 GS/s 2 5 ns	Fluke 199B Fluke 196B

Maximum record length 3000 points per input in Scope-mode;

27,500 points per input in ScopeRecord™ roll

mode (5 ms/div ... 2 min/div)

Accuracy \pm (0.01% of reading + 1 pixel)

Glitch capture 50 nsec (5 µsec/div to 1 min/div)

DISPLAY AND ACQUISITION

	Fluke 190C	Fluke 190B	
Display	144 mm	144 mm	
	Full Color LCD	Monochrome LCD	
Display modes	Input A, Input B, dual, average, Replay		
Persistence modes	Digital Persistence:	Persistence	
	short / medium /	on / off	
	long / infinite		

Visible screen width 12 divisions in scope mode

Waveform Mathematics A+B, A-B, A*B, all with user selectable scaling

of resultant; A versus B (X-Y-mode); Frequency Spectrum using FFT analysis (190C only). Normal, auto, single shot, ScopeRecord™, roll, glitch capture, waveform compare, waveform

compare with automatic "Pass / Fail testing" (in 199C and 196C only)

TRIGGER AND DELAY

Acquisition modes

Source Input A, input B, external trigger input. All input

references isolated from each other and from ground.

Modes Automatic Connect-and-View™, free run, single shot, edge, delay, video, video line, selectable

pulsewidth, dual slope (190C only), N-cycle

(190C only)

Connect-and-View[™] Advanced automatic triggering that recognizes

signal patterns, automatically sets up and continuously adjusts triggering, time base and amplitude. Automatically displays stable waveforms of complex and dynamic signals like motor drive and control signals. Can be switched off if so

desired.

Video triggering NTSC, PAL, PAL+, SECAM. Includes field 1, field

2 and line select.

Pulse width triggering Pulse width qualified by time. Allows for trigge-

ring $\langle t, \rangle t$, =t, $\neq t$, where t is selectable in

minimal steps of 0.01 div or 50 nsec
Time delay 1 full screen of pre-trigger view or up

1 full screen of pre-trigger view or up to 100 screens (=1200 divisions) of post-trigger delay. Both rising and falling transitions, when

crossing the trigger level, initiate an acquisition

(190C only)

N-cycle triggering Triggers on N-th occurrence of a trigger event;

N to be set in the range 2 to 99 (190°C only).

AUTOMATIC CAPTURE OF The instrument ALWAYS memorizes the last **100 SCREENS** 100 screens (no user setup required). When

Replay

Dual slope triggering

100 screens (no user setup required). When an anomaly occurs on screen, the REPLAY button can be pressed to review the full screen sequence over and over. Instrument can be set up for triggering on glitches or intermittent anomalies and will operate in "baby-sit" mode

and will capture 100 events.

Manual or continuous replay. Displays the captured 100 screens as a "live" animation, or under manual control. Each screen has date-

and time-stamp.

Replay storage Up to 2 sets of 100 screens each can be saved

for later recall and analysis.

FFT - FREQUENCY SPECTRUM ANALYSIS (190C only) Shows frequency content of oscilloscope

waveform using Fast Fourier Transform
Window Automatic, Hamming, Henning or None
Automatic Window Digitally re-samples acquired waveform to get
optimum frequency resolution in FFT resultant

Vertical Scale Linear / Logarithmic, in volts

Frequency Axis Logarithmic; frequency range automatically set as function of timebase range of oscilloscope

WAVEFORM COMPARE AND PASS/FAIL TESTING

Waveform compare Provides sto

Provides storage and display of a reference waveform for visual comparison with newly acquired waveforms. Reference is derived from an acquired waveform and can be modified in the ScopeMeter or externally using FlukeView

Software.

Pass/Fail Testing (199C, 196C) In waveform compare mode, the Color

ScopeMeter can be set up to store only matching ("Pass") or only non-matching ("Fail") acquired waveforms in the replay memory bank

for further analysis.

AUTOMATIC SCOPE MEASUREMENTS

Vdc, Vac rms, Vac+dc, Vpeak max, Vpeak min, Vpeak to peak, Aac, Adc, Aac+dc, frequency (Hz), risetime, falltime, power factor, Watts, VA, VA reactive, phase, pulsewidth (pos./neg.), dutycycle (pos./neg.), temperature °C, temperature °F, dBV, dBm into 50Ω and 600Ω VPWM ac, VPWM ac+dc for measurement on pulsewidth modulated motordrives and frequency inverters

CURSOR MEASUREMENTS

Source Input A, input B or the Mathematical Result trace

(excl. A vs B curve)

Dual horizontal lines Voltage at cursor 1 and 2, voltage between cur-

sors

Dual vertical lines Time between cursors, 1/T between cursors (in Hz), voltage between markers, risetime with

markers, falltime with markers; Vrms between cursors (190C only), Watts between cursors

(190C only)

Single vertical line Min-Max and Average voltage at cursor position;

Frequency and RMS-value of individual frequency component in FFT Result (190C only)

ZOOM Up to 16x horizontal zoom

METER MODE

Via 4 mm banana inputs. Fully isolated from scope inputs and scope ground. The specified accuracy is valid over the temperature range 18 °C to 28 °C (65 °F to 82 °F). Add 10 % of specified accuracy for each degree C below 18 °C or above 28 °C.

MAXIMUM RESOLUTION 5 000 counts

VOLTMETER RANGES ACCURACY

500mV, 5V, 50V, 500V, 1,000V

Vdc

 \pm (0.5 % + 5 counts) Vac true rms

15 Hz...60 Hz: \pm (1 % + 10 counts) 60 Hz...1 kHz: \pm (2.5 % + 15 counts)

Vac+dc true rms

dc...60 Hz: \pm (1 % + 10 counts) 60 Hz...1 kHz: \pm (2.5 % + 15 counts)

OHMS

 500Ω , $5k\Omega$, $50k\Omega$, $500k\Omega$, $5M\Omega$, $30M\Omega$ Ranges

Accuracy \pm (0.6 % + 5 counts)

OTHER METER FUNCTIONS

Beeper on $< 50\Omega$ ($\pm 30\Omega$) Continuity

Diode test Up to 2.8V

Amps Adc, Aac, Aac+dc using an optional current

clamp or shunt. Scaling factors: 0.1 mV/A ...

100 V/A

Temperature (°C, °F) With optional accessories. Scale factors 1 °C/mV

or 1 °F/mV

Input impedance $1 \text{ M}\Omega \pm 1\% // 10 \text{ pF} \pm 2 \text{ pF}$

Auto/manual ranging, relative measurements Advanced meter functions

(Zero reference), TrendPlot recording

RECORDER MODE

SCOPE-RECORD-Dual input waveform storage mode. ROLL MODE

Source and display Input A, Input B, Dual 27,500 points per input. Memory depth

Each point consist of Min-Max pair.

Min-Max values Min-Max values are measured at high sample rate ensuring capture and display of glitches.

Time base range 5 ms/div to 1 min/div 2 min/div Recorded timespan 6 sec to 24 hr 48 hr Glitch capture 50 ns 250 ns Sample rate 20 MS/s 4 MS/s Resolution 200 usec to 2 sec 4.8 sec

Recording modes Single sweep, continuous roll, Start-on-Trigger

(through external), Stop-on-Trigger (through

external)

Stop-on-Trigger ScopeRecord mode can be stopped by an (through External) individual trigger event, or by an interruption of

a repetitive trigger signal.

Horizontal scale Time from start, time of day

7.00m Up to 100x

Memory Up to 2 dual input ScopeRecord waveforms can

be saved for later recall and analysis.

TRENDPLOTTM Single or dual input electronic paperless chart recorder. Plots, displays and stores meter RECORDING

and scope measurements.

Source and display Input A. Input B or DMM input

18,000 points record per input. Per record point Memory depth

a minimum, a maximum and an average value, plus a date- and timestamp are stored.

Ranges

- normal view 5 s/div to 30 min/div - in view-all mode 5 min/div to 48 hr/div

(overview of total record)

Recorded timespan Up to 22 days with a resolution of 1

minute

Recording mode Continuous roll for the duration of the

full recordable timespan

5 measurements per second or more Measurement speed

Time from start, time of day Horizontal scale

Zoom Up to 64x zoom

Memory Up to 2 TrendPlot recordings can be saved for

later recall and analysis.

CURSOR MEASUREMENTS - ALL RECORDER MODES

Source Input A, B or DMM input

Dual vertical lines Min-Max or Average voltage. Time between

cursors

Min-Max or Average voltage. Absolute date and Single vertical line

time or time from start

GENERAL SPECIFICATIONS

INPUT VOLTAGE RATINGS

1,000V CAT II, 600V CAT III Maximum probe voltage

(Maximum voltage between 10:1 probe tip (VPS200)

and reference lead)

Floating voltage 1,000V CAT II, 600V CAT III

(Maximum voltage between earth ground and any

terminal (signal input or shielding))

Independently isolated inputs 1,000V CAT II, 600V CAT III

(Maximum voltage between any terminal of one input or probe (VPS200) and any other terminal of another

input or probe (VPS200))

Maximum voltage on BNC

300V CAT III input directly (input A or B)

Maximum voltage on

1,000V CAT II, 600V CAT III meter input

MEMORY SAVE AND RECALL

Scope memories 10 memory locations that each can contain two

waveforms plus corresponding setup.

2 memory locations that each can contain 100 Recorder memories

> captured dual input scope screens, or a dual input ScopeRecord (27,500 Min-Max pairs per input), or a dual input Trendplot (18,000 min-

max pairs).

REAL-TIME CLOCK Time and date stamp for ScopeRecord,

100 captured screens and TrendPlots.

CASE

Design Rugged, shock proof with integrated protective

holster

Drip and dust proof IP51 according to IEC529

Shock and Vibration Shock 30g, Vibration (sinusoidal) 3g according

to MIL-PRF-28800F Class 2.

115.2 x 86.4 mm (4.54 x 3.4 inches) Display Size

Resolution 320 x 240 pixels

Contrast and brightness User adjustable, temperature compensated

	Fluke 190C	Fluke 190B	
DISPLAY	Bright full-color LCD	Bright LCD with backlight	
	with backlight		
BRIGHTNESS	80 Cd/m2 typ. using	125 Cd/m ² typ. using	
	power adapter	power adapter	

MECHANICAL DATA

256 x 169 x 64 mm (10.1 x 6.6 x 2.5 inches)

Weight 2 kg (4.4 lbs)

POWER

Country specific line voltage adapter/battery Line power

charger included.

Rechargeable NiMH (installed) Battery power

Battery operating time 4 hours Battery charging time 4 hours

Battery power saving Auto power down with adjustable power down

functions time. On screen battery power indicator SAFETY

EN61010-1 (2nd edition) Pollution Degree 2; Compliance

CAN/CSA C22.2 No. 1010.1:

ANSI/ISA S82.01.

ENVIRONMENTAL

0 °C to +50 °C Operating temperature Storage temperature -20 °C to +60 °C

Humidity 10 °C to 30 °C: 95% RH non condensing 30 °C to 40 °C: 75% RH non condensing

40 °C to 50 °C: 45% RH non condensing

Maximum operating altitude 3,000 m (10,000 feet) 12 km (40,000 feet)

Maximum storage altitude Electro-Magnetic-

Compatibility (EMC) EN 61326-1 for emission and immunity

OPTICALLY ISOLATED PC/PRINTER INTERFACE

To printer Supports HP Laserjet®, DeskJet, Epson FX/LQ,

Seiko DPU-414 and Postscript printers via

optional PAC 91

To PC Transfer instrument settings, screen images and

waveform data, compatible with FlukeView® software for Windows® via optional PM9080.

WARRANTY 3 years (parts and labor) on main instrument,

1 year on accessories.

Technical Specifications ScopeMeter 120 Series

OSCILLOSCOPE MODE VERTICAL DEFLECTION

Bandwidth and risetime	Fluke 124	Fluke 123
 with VPS40 probes 	40 MHz	20 MHz
input A and B directly	40 MHz	20 MHz
 with STL120 Shielded Test Leads 	12.5 MHz	12.5 MHz
Instrument risetime (input directly)	8.75 ns	17.5 ns

Number of inputs Input coupling Input sensitivity

AC, DC with ground level indicator 5 mV ... 500 V/div (with included VPS40 (Fluke 124) and STL120 shielded test leads measure up to 600Vrms CAT III)

Vertical resolution 8 bit

 \pm (2% of reading + 0.05 x Accuracy

range/div)

 $1~\text{M}\Omega \pm 1\%~\text{//}~225~\text{pF}$ with STL120 Input impedance

shielded test leads

 $1 \text{ M}\Omega \pm 1\% // 20 \text{ pF} \pm 3 \text{ pF}$ with

BB120

 $5 \text{ M}\Omega \pm 1 \% // 15.5 \text{ pF with}$ VPS40, 10:1 Voltage probe

HORIZONTAL

Maximum sample rate Fluke 124: 2.5 GS/s for repetitive

signals; 25 MS/s for single shot Fluke 123: 1.25 GS/s for repetitive signals; 25 MS/s for single shot

Number of digitizers

Time base range 10 ns/div to 1 min/div (Fluke 124); 20 ns/div to 1 min/div (Fluke 123)

Maximum record length 512 Min-Max points per input Accuracy \pm (0.1% of reading + 1 pixel) Glitch detect 40 ns

DISPLAY AND ACQUISITION

Display modes Input A, input A and B, envelope,

smooth

Acquisition modes Normal, single shot, roll, glitch

capture (always on)

TRIGGER AND DELAY

Source Input A, input B, external via

optional ITP120

Automatic Connect-and-View™, Modes Free Run, Edge, Single Shot, Video,

Video Line

Connect-and-View™

Advanced automatic triggering that recognizes signal patterns and automatically sets up and continuously adjusts triggering, time base and amplitude. Automatically displays

stable pictures of complex and

dynamic signals like motor drive and control signals.

NTSC, PAL, PAL+, SECAM. Includes Video triggering

line select

Time delay Up to 10 divisions pre-trigger view

MEASUREMENTS

VDC, VAC, VAC+DC, Vpeak max, Vpeak min, Vpeak to peak, frequency (Hz), positive pulse width, negative pulse width, positive duty cycle, negative duty cycle, Amp AC, Amp DC, Amp AC+DC, Phase, Temperature °C, Temperature °F, dBV, dBm into 50Ω and 600Ω . (Amps, °C or °F with optional

probes)

CURSOR MEASUREMENTS (124 only)

Sources Input A, Input B Modes Single or dual vertical cursor, dual

horizontal cursor, rise- or falltime

Measurements:

Single vertical line Average, min value, max value, time from start of recording in roll mode

Dual vertical lines ΔV at markers, time between

cursors, 1/T between cursors (in Hz) High, low or ΔV - readout, rise- and Dual horizontal lines

falltime: transition time, 0 %-level, 100 %-level, with markers at 10 %

and 90 %

Accuracy As oscilloscope

DUAL INPUT METER

The specified accuracy is valid over the temperature range 18 °C to 28 °C (65 °F to 82 °F). Add 10 % of specified accuracy for each degree

C below 18 °C or above 28 °C.

Max. meter bandwidth 40 MHz (for Fluke 124) and 20 MHz

(for Fluke 123) VDC

500mV, 5V, 50V, 500V, 1,250V Ranges

Max. Resolution 5,000 counts Accuracy \pm (0.5% + 5 counts)

VAC RMS

500mV, 5V, 50V, 500V, 1,250V Ranges

Max. Resolution 5,000 counts

1 Hz...60 Hz: $\pm (1\% + 10 \text{ counts})$ Accuracy 60 Hz...1 kHz: ±(2.5% + 15 counts)

20 kHz...1 MHz (5% + 20 counts)

VAC+DC TRUE RMS

500mV, 5V, 50V, 500V, 1,250V Ranges

Max. Resolution 5,000 counts

DC ... 60 Hz: $\pm (1\% + 10 \text{ counts})$ Accuracy

60 Hz...1 kHz: ±(2.5% + 15 counts) 20 kHz...1 MHz \pm (5% + 20 counts)

OHMS

Ranges 500Ω , $5k\Omega$, $50k\Omega$, $500k\Omega$, $5M\Omega$,

30MQ

Max. Resolution 5.000 counts

 \pm (0.6% of reading + 5 counts) Accuracy

CAPACITANCE

functions

50 nF ... 500μF Ranges Max. Resolution 5,000 counts

Accuracy \pm (2% of reading + 10 counts)

OTHER METER FUNCTIONS

Up to 70 MHz (Fluke 124) and up to Frequency

40 MHz (Fluke 123) Continuity Beeper on $< 30\Omega$

Diode test Up to 2.8V

Amp DC, Amp AC, Amp AC+DC Amps

using an optional current clamp or shunt. Scaling factors: 0.1 mV/Amp ...

100 V/Amp

Temperature (°C, °F) With optional accessories. Scale

factors 1 mV/°C or 1 mV/°F

Number of inputs

Input impedance $1M\Omega \pm 1\% // 10 pF \pm 2 pF$ Advanced meter Auto/manual ranging

TouchHold®

Relative measurements (zero reference) TrendPlot recording

RECORDER MODE

TRENDPLOTTM Dual input electronic paperless chart RECORDING recorder. Plots and displays the actual, mini-

mum, maximum and average of any measure-

Source and display Input A, Input A and B

15 s/div till 2 days per division (automatic) Range Recorded timespan Up to 16 days with a resolution of 1.5 hours

Recording mode Continuous with automatic vertical scaling and

horizontal time compression

Measurement speed 2.5 measurements per second

maximum

Horizontal scale Time from start

GENERAL SPECIFICATIONS

CASE Design

Rugged, shock proof with integrated protective holster

Drip and dust proof IP51 according to IEC529

Shock and Vibration Shock 30g, Vibration 3g according to

MIL-T-28800E, Type III, Class 3, Style B

DISPLAY Bright LCD with CCFL backlight, 35/60 cd/m²

without/with adapter

72 x 72mm (2.8 x 2.8 inch) Size

Resolution 240 x 240 pixels

Contrast and brightness User adjustable, temperature

compensated

MEMORY SAVE 20 (Fluke 124) and 10 (Fluke 123)

AND RECALL instrument screens with user set-ups and user

REAL-TIME CLOCK Time and date stamp TrendPlot recording

POWER

Line power Country specific line voltage

adapter/battery charger included

Rechargeable Ni-MH BP130 (installed in Fluke Battery power

124) or rechargeable NiCd BP120 (installed in

Fluke 123)

Battery operating time Up to 7 hours using BP130, up to 5 hours using BP120

Battery charging time 5 hours (Fluke 123), 7 hours (Fluke 124)

Battery power saving Auto power down with adjustable

functions power down time. On screen battery power

indicator

MECHANICAL DATA Size

50 x 115 x 232 mm (2 x 4.5 x 9.1 inches)

Weight 1.2 kg (2.5 lb.)

SAFETY

Compliance EN61010-1 (2nd edition) Pollution Degree 2;

CAN/CSA C22.2 No. 1010.1:

ANSI/ISA S82.01.

INPUT VOLTAGE RATINGS

Maximum input voltage 600V CAT III (Maximum voltage between input and reference lead)

Maximum input voltage

600 V CAT III, 1000 V CAT II

using VPS40 Probe

(Maximum voltage between probe tip input and reference lead)

Floating voltage 600V CAT III

Maximum voltage between earth ground and any terminal (signal input or reference lead)

Maximum voltage between Instrument has common grounds

reference leads

connected via selfrecovering fault protection. For different ground potential measurements between inputs use DP120 differential voltage

probe.

ENVIRONMENTAL

To PC

Operating Temperature 0°C to +50°C -20°C to +60°C Storage temperature

Humidity 10°C to 30°C, 95% RH non condensing

30°C to 40°C, 75% RH non condensing 40°C to 50°C, 45% RH non condensing

Maximum operating altitude 2,000m (6,500 feet)

3,000m (10,000 feet) voltages ≤ 400V

Maximum storage altitude 12 km (40,000 feet) Electro-Magnetic-Emission EN50081-1 Compatibility (EMC) (EN55022 and EN60555-2) Immunity EN50082-2 (IEC1000-4-2, -3, -4, -5)

OPTICALLY ISOLATED PC/PRINTER INTERFACE

Supports HP Laserjet*, Deskjet*, Epson FX/LQ To printer and postscript printers via optional PAC91

Transfer instrument settings, screen images and

data, compatible with FlukeView* software for

Windows[®] via optional PM9080.

WARRANTY 3 years (parts and labor) on main instrument,

1 year on accessories

FlukeView® ScopeMeter® Software

FlukeView ScopeMeter software helps you get more out of your ScopeMeter:

- · Store instrument's screen copies on the PC, in color (with Fluke 190C-Series only) or in black&white
- · Copy screen images into your reports and documentation
- · Capture and store waveform data from your ScopeMeter on your PC
- · Create and archive waveform references for automatic (Fluke 190C Series) or visual (Fluke 190B and 190C Series) comparison
- Includes waveform analysis, e.g. FFT spectrum analysis
- Copy waveform data into your spreadsheet for detailed analysis
- Use cursors for parameter measurement
- Extended recording of up to four user-selected measurements help you monitor and analyze slow moving signals and related events
- · Logging of other readings directly into other application programs, eg., spreadsheet
- · Add user text to instrument setups and send these to the instrument for operator reference and instructions
- Capture complete Replay sequence into the PC for further analysis and documentation
- English, French and German versions included on a single CD-ROM

System requirements

- Pentium 90 or better
- · CD-ROM drive
- Windows® 95 / 98 / Me / NT 4.0 / 2000 / XP
- · One free RS 232 port
- PM9080 Optically isolated RS232 adapter/cable, available separately or included in SCC120 / SCC190 kit and in ScopeMeter 'S' versions

Supported Instruments

Full support for Fluke 199C, 199B, 199, 196C, 196B, 196, 192B, 192, 124 and 123.



Accessories

Standard Accessories	Fluke 199C, 196C, 199B, 196B, 192B	Fluke 123, 124		
Rechargeable	BP190	BP120 (Fluke 123),		
battery pack (installed)		BP130 (Fluke 124)		
Line voltage adapter /	BC190	PM8907		
Battery charger				
Voltage probes	10:1 voltage probe (VPS200) including	STL120 Shielded Test lead set		
(1 set red, 1 set grey)	hook clip, ground lead with hook clip,	VPS40 high impedance 10:1 probe,		
and accessories	ground lead with mini alligator clip,	40 MHz (1 black, included with		
	4 mm add-on probe tip,	Fluke 124 only);		
	ground lead to 4 mm banana plug	HC120 hook clips,ground leads with		
		mini alligator clips, AC120 alligator		
		clips, BB120 BNC-to-Shielded-		
		banana adapter		
Multimeter testleads	TL75 Hard Point testlead set (1red, 1 black)	TL75 Hard Point test lead (1 black)		
User manual	10 language versions on CD-ROM,	15 language versions on CD-ROM.		
	"Getting Started" booklet included	"Getting Started" booklet included		
	with instrument	with instrument		

Next to the above standard accessories, Fluke offers a wide range of optional accessories like temperature probes, current clamps, high voltage probes, cables, adapters and carrying cases to further assist you in your job. See the Fluke web-site or contact your distributor for details.

SCC190 and SCC120 - Software, Case, Cable kits

The Fluke ScopeMeters are connected to a PC using an optically isolated RS-232 interface cable PM9080, for your safety.

Software and cable can be ordered seperately, or as part of a special value kit: the SCC190 kit or the SCC120 kit. Each of these include a protective hard shell carrying case (model depending on the ScopeMeter model) for safe and convenient storage of instrument and accessories, the FlukeView ScopeMeter Software for Windows and the PM9080 interface cable.





Selection Table

	Color ScopeMeter 190C Series		ScopeMeter 190B Series		ScopeMeter 120 Series		
	Fluke 199C	Fluke 196C	Fluke 199B	Fluke 196B	Fluke 192B	Fluke 124	Fluke 123
Bandwidth	200 MHz	100 MHz	200 MHz	100 MHz	60 MHz	40 MHz	20 MHz
Max. real time sample rate	2.5 GS/s	1 GS/s	2.5 GS/s	1 GS/s	500 MS/s	25 1	MS/s
Max. equivalent time sample rate			-			2.5 GS/s	1.25 GS/s
Display	14.4 cm F	'ull Color LCD	1-	4.4 cm Monochrome Lo	CD	10.2 cm Mor	nochrome LCD
Digital Persistence	Yes, gives anal	og oscilloscope like		-		-	
	waveform dec	ay (user selectable)					
Envelope mode		Yes		Yes		Yes	
Naveform Compare	Visual	Reference		Visual Reference			-
	and Automatic	'Pass / Fail' testing					
Max. record length							
in Scope mode:	3000 point	s per input channel, allow	ing for high time resolu	ition signal analysis us	sing zoom	512 min/max p	ooints per input
in ScopeRecord mode:		27,500 points per	input or more (5 ms/div	72 min/div.)			
Jumber of inputs		2 plus external / DMM i	nput, all isolated from e	each other and from gr	round		2
Jumber of digitizers			2				2
ndependently floating		Up to 1000 V betv	veen inputs, references	and ground			-
solated inputs							
nput sensitivity	2 mV/div.	100 V/div.	į	5 mV/div 100 V/div	ī.	5 mV/div 500 V/div.	
litch capture			to 3 ns using Pulse Wi			40 ns	
		50 r	ns peak detect at 5 μs/c	liv. to 1 min/div.			
limebase range in Scope mode	5 ns/div. to 2 min/div. 10 ns/div			10 ns/div	20 ns/div		
		2 min/div.	1 min/div.	1 min/div.			
rigger types	Connect-and-View™, Free Run, Single Shot, Edge, Delay, Video Frame, Video Line		Connect-and-View™, Free Run,				
	Selectable pulse width and External			Single Shot, E	Edge, Video		
	Dual Slope trigger ar	nd Event trigger (n-cycle)					
cope Measurements			measurements, 30 auto	omatic measurements		cursors +	26 automatic
		d watts measurement on				26 automatic	measurement
	cursor limited	l part of waveform				measurements	
Vaveform Mathematics		$A + B$, $A - B$, $A \times$	B, A versus B (X-Y-mod	le, giving Lissajous dia	grams)		-
	Frequency S	Spectrum (FFT)					
cope-Record Trigger modes			Start on Trigger, Stop				-
apture last 100 screens			Automatic, with Replay	, , ,			-
Oual input TrendPlot	Yes, with Cursors and Zoom		_	es			
Memory for screens/set-ups	10 screens and set-ups;			20	10		
			re made available upor				
Memory for recordings		Two, each can sto	ore 100 scope screens,				
rue RMS multimeter	5000 counts, Volts, Amps, Ohms, Continuity, Diode, T			•			
Safety certified (EN61010-1)	1000 V CAT II / 600 V CAT III (instrument and included accessories)		600 V CAT I	II (instrument			
			and included accessories)				
attery (installed)	4 hr Ni-MH BP190			7 hr Ni-MH	5 hr Ni-Cd		
ine power			Āda	pter / battery-charger	included		
ize (cm)			25.6 x 16.9 x 6.	4 cm		23.2 x 1	1.5 x 5.0 cm
Veight			2 kg			1	.2 kg
C and Printer interface				ally Isolated RS-232 a		<u> </u>	
Varrantv		2	years on main instrum	ont 1 woor on the ster	dord aggoggoriog		

Ordering Information

Fluke 199C	Color ScopeMeter (200 MHz / 2.5 GS/s)
Fluke 199C/S	Color ScopeMeter (200 MHz / 2.5 GS/s) + SCC190
Fluke 196C	Color ScopeMeter (100 MHz / 1 GS/s)
Fluke 196C/S	Color ScopeMeter (100 MHz / 1GS/s) + SCC190
Fluke 199B	ScopeMeter (200 MHz / 2.5 GS/s)
Fluke 199B/S	ScopeMeter (200 MHz / 2.5 GS/s) + SCC190
Fluke 196B	ScopeMeter (100 MHz / 1 GS/s)
Fluke 196B/S	ScopeMeter (100 MHz / 1 GS/s) + SCC190
Fluke 192B	ScopeMeter (60 MHz / 500 MS/s)
Fluke 192B/S	ScopeMeter (60 MHz / 500 MS/s) + SCC190
Fluke 124	Industrial ScopeMeter (40 MHz)
Fluke 124/S	Industrial ScopeMeter (40 MHz) + SCC120 kit
Fluke 123	Industrial ScopeMeter (20 MHz)
Fluke 123/S	Industrial ScopeMeter (20 MHz) + SCC120 kit
SCC190	FlukeView [®] Software + Cable + Case (190 Series)
SCC120	FlukeView [®] Software + Cable + Case (120 Series)
PM9080	Optically Isolated RS-232 adapter/cable
SW90W	FlukeView [®] ScopeMeter Software for Windows [®]

- ScopeMeter test tools come standard with a complete accessory package including line voltage adapter and battery pack
 (installed). ScopeMeter 190B and 190C Series come with probes, probe accessories and multimeter test leads.
 SCC kit includes: Hard-shell carrying case, optically isolated RS-232 interface cable, and FlukeView* for Windows* software.

Fluke Corporation P.O. Box 9090 Everett, WA USA 98206

Fluke Europe B.V. P.O. Box 1186 5602 BD Eindhoven The Netherlands

The Netherlands

For more information call:
In the U.S.A. (800) 443-5853
or Fax (425) 446 -5116
In Europe/M-East/Africa +31 (0)40 2 675 200
or Fax +31 (0)40 2 675 222
In Canada (905) 890-7600
or Fax (905) 890-6866
From other countries +1 (425) 446 -5500
or Fax +1 (425) 446 -5116

Visit us on the world wide web at:

http://www.fluke.com

Fluke (UK) Ltd. 52 Hurricane Way Norwich Norfolk NR6 6JB United Kingdom
Tel.: 0207 942 0700
Fax: 0207 942 0701
E-mail: industrial@uk.fluke.nl

Visit us on the world wide web at:

http://www.fluke.co.uk

© Copyright 2004 Fluke Corporation
All rights reserved. Data subject to change without notice.
ScopeMeter and FlukeView are registered trademarks of Fluke
Corporation. Windows is a registered trademark of Microsoft
Corporation. Printed in the Netherlands. 03/2004.
Pub ID: 10705-eng
Rev. 01