## FS-380P Series – Industrial Strength **Inline Plastic Flow Switch**

Flow Rate Settings: 0.25 GPM to 2.00 GPM Port Size: 3/8" NPT Male and 1/4" Quick Disconnect (QDC) Male Primary Construction Material: Polypropylene Setting Type: Fixed

This rugged inline flow switch offers the same superior performance to non-clogging as its metal cousin (FS-380). The fixed set point and simple design make it a dependable switch. The FS-380P is an ideal choice for coolant applications requiring reliable flow detection in HVAC, semiconductor, welding, medical and other industries, 1/4" quick disconnect units have a host of snap-on mating adapters to fit most piping requirements.


## **Specifications**

Wetted Materials Housing	Glass Reinforced Polypropylene
Piston	PPS Composite
Spring	316 Stainless Steel
O-Ring	Fluorocarbon
Operating Pressure	125 PSI (8.6 bar) @ 70°F (21°C), 50 PSI (3.4 bar) @ 212°F (100°C)
Operating Temperature	0°F to 212°F (-18°C to +100°C)
Set Point Accuracy	20% of Set Point
Set Point Differential	20% Maximum
Switch*	SPST, 10VA, N.O. at no Flow
Electrical Termination	24" to 26" Polymeric Leads, 22 AWG
Filtration	100 Micron
Approvals	CUL


(E c File No. E31926

## Dimensions

1/4" Quick Disconnect Male Adapter See table at bottom right for adapter Part Numbers.



3/8" NPT Port



\*See "Electrical Data" on Page X-5 for more information.

## How To Order

Specify Part Number based on flow settings. Adapters for the 1/4" Quick Disconnect (QDC) Male unit are listed in the table at right.

Flow Settings	Part Numbers			
GPM	3/8" NPT Male	1/4" QDC Male*		
0.07	216445**	216446**		
0.15	209876	203206		
0.25	197081 🗲	197091 🗲		
0.50	197082 🗲	197092 🗲		
1.00	197083 🗲	197093 🗲		
1.50	197084 🗲	197094 🗲		
2.00	197085 🗲	197095 🗲		
* One callestic and a device of violat				

\* See selection of adapters at right. QDC = Quick Disconnect

\*\* Set point accuracy 0.06 to 0.1 GPM

Acetal Adapters for 1/4" Quick Disconnect Male Tube Fitting Units (180°F max.) These adapters are available with or without an integral shut-off valve. The shut-off valve will stop line flow when the adapter is removed from the unit. Flow resumes when connected.



Typical shown: 1/4" NPT Male Pipe Thread with Shut-off Valve

Description	Part Numbers	
Description	Straight Through	with Shut-Off Valve
1/4" NPT Male Pipe Thread	195787 🗲	198063
1/4" BSPT Male Pipe Thread	198064 🗲	195788
3/8" NPT Male Pipe Thread	198065 🗲	198066
3/8″ BSPT Male Pipe Thread	198067 🗲	198068
1/4" 0.D., .27" I.D. (6 mm 0.D., 4.3 mm I.D.) Polytube	198096 🗲	198097
3/8" O.D., 1/4" I.D. (9.5 mm O.D., 6 mm I.D.) Polytube	198099 🗲	198098
1/4" (6.4 mm) I.D. Barb	198401 🗲	198402
5/16″ (7.9 mm) I.D. Barb	198403 🗲	198404
3/8″ (9.5 mm) I.D. Barb	198408 🗲	198405
1/4″ 0.D. (6.4 mm) 0.D. JG®	198470 🗲	198406
3/8″ 0.D. (9.5 mm) 0.D. JG®	198459 🗲	198407

JG<sup>®</sup> is a registered trademark of John Guest USA, Inc.