



# TUV T8

## TUV 36W SLV/6

TUV T8 lamps are double-ended UVC (germicidal) lamps used in professional water and air disinfection units. TUV T8 lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Moreover, they have a long and reliable lifetime, which allows maintenance to be planned for in advance.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

### Product data


General Information		Voltage (Nom)	
Cap base	G13 [ Medium Bi-Pin Fluorescent]	103 V	
Main application	Disinfection	Mechanical and Housing	
Useful life (nom.)	9000 h	Cap-base information	2P
System description	na [-]	Bulb shape	T26 [ T 26mm]
Light Technical		Approval and Application	
Colour Code	TUV	Mercury (Hg) content (nom.)	2.0 mg
Colour designation	- [ Not Specified]	UV	
Depreciation at useful lifetime	10 %	UV-C Radiation	15.0 W
Operating and Electrical		Product Data	
Power (Rated) (Nom)	36 W	Full product code	871150061854210
Lamp current (nom.)	0.44 A		

# TUV T8

Order product name	TUV 36W SLV/6
EAN/UPC – product	8711500618542
Order code	61854210
Local order code	36TUV
SAP numerator – quantity per pack	1

Numerator – packs per outer box	6
SAP material	928048604003
SAP net weight (piece)	135.000 g


## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TUV 36W SLV/6	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

TUV TL-D 36W

## Photometric data



XDPB\_XUTUVTL-D-Spectral power distribution B/W



XDPO\_XUTUVTL-D-Spectral power distribution Colour

