

831.2 | 831 - ADJUSTABLE TAP WRENCHES




Norm :

NF E 66-130

Description :

- Pressure-cast Zamak body. Machined and hardened clamp.
- Finish: grey hammered finish.

Informations :

	831.2
L [mm]	300
Open Position maxi [mm]	4-11
Open Position mini [mm]	4-11
Tapping	M5->M12
[g]	300