

# Panel Heaters 25 - 50 - 100 - 150 -250 - 400 W





### Type 7H.51.0.230.0025

- Heating power 25 W

#### Type 7H.51.0.230.0050

- Heating power 50 W
- Nominal voltage (110...230)V AC/DC
- Safe touch
- PTC resistor, self regulating heating system
- Clip for 35 mm rail (EN 60715) mount

7H.51.0025/0050 Screw terminal



#### 7H.51.0.230.0025



- Heating power 25 W
- Nominal voltage (110...230)V AC/DC
- Safe touch

#### 7H.51.0.230.0050

**finder** 



- Heating power 50 W
- Nominal voltage (110...230)V AC/DC
- Safe touch

\* At 20°C ambient temperature

For outline drawings see page 7

For outline drawings see page 7			
Heating specification			
Heating power *	W	25	50
Heater		PTC resistor, self-regulating heating system	
Housing		Plastic according to UL94 – V0, black	
Supply specification			
Nominal voltage (U <sub>N</sub> )	V AC (50/60 Hz)/DC	110230	110230
Rated current	Α	0.13	0.20
Operating range	V AC/DC	88253	88253
Technical data			
Radiator		Alluminium profile	
Electrical connection		Screw terminals	
Fitting position		Vertical	
Ambient temperature	°C	-45+50	-45+50
Protection category		IP20	IP20
Approvals (according to type)		C€ [A[ c <b>AX</b> °us	

#### **Panel heaters**

# Type 7H.51.0.230.0100

- Heating power 100 W

#### Type 7H.51.0.230.0150

- Heating power 150 W
- Nominal voltage (110...230)V AC/DC
- Safe touch
- PTC self regulating heating system
- Clip for 35 mm rail (EN 60715) mount

7H.51.0100/0150 Screw terminal



#### 7H.51.0.230.0100



- Heating power 100 W
- Nominal voltage (110...230)V AC/DC
- Safe touch

#### 7H.51.0.230.0150



- Heating power 150 W
- Nominal voltage (110...230)V AC/DC
- Safe touch

\* At 20°C ambient temperature

For outline drawings see page 8			
Heating specification			
Heating power *	W	100	150
Heater		PTC resistor, self-regulating heating system	
Housing		Plastic according to UL94 – V0, black	
Supply specification			
Nominal voltage (U <sub>N</sub> )	V AC (50/60 Hz)/DC	110230	110230
Rated current	Α	0.45	0.70
Operating range	V AC/DC	88253	88253
Technical data			
Radiator		Alluminium profile	
Electrical connection		Screw terminals	
Fitting position		Vertical	
Ambient temperature	°C	-45+50	-45+50
Protection category		IP20	IP20
Approvals (according to type)		C€ [A[ c <b>7/1</b> °us	

# **finder**

#### Panel heaters fan assisted

#### Type 7H.51.8.230.0250

- Heating power 250 W

#### Type 7H.51.8.230.0400

- Heating power 400 W
- Nominal voltage 230 V AC
- Safe touch
- PTC resistor, self regulating heating system
- Fast wiring terminals
- Clip for 35 mm rail (EN 60715) mount

7H.51.0250/0400 Screwless terminal









• Nominal voltage 230 V AC • Fan assisted

• Heating power 250 W



7H.51.8.230.0400

- Heating power 400 W
- Nominal voltage 230 V AC
- Fan assisted

\* At 20°C ambient temperature


For outline drawings see page 8

For outline drawings see page 8			
Heating specification			
Heating power *	W	250	400
Heater PTC resistor, self-regulatin		lating heating system	
Air flow rate	m³/h	30	
Housing		Plastic according to UL94 – V0, black	
Supply specification			
Nominal voltage (U <sub>N</sub> )	V AC (50/60 Hz)	230	230
Rated current	А	1	1.7
Operating range	V AC	184253	184253
Technical data			
Radiator		Alluminium profile	
Electrical connection		Screwless terminal	
Fitting position		Vertical	
Ambient temperature	°C	-40+50	-40+50
Protection category		IP20	IP20
Approvals (according to type)		C€ [用] Э)	



### **Ordering information**

Example: 7H series, Panel heaters, heating power 50 W, 110...230 V AC/DC.



0150 = 150 W


0250 = 250 W0400 = 400 W

# **General data**

Terminals		solid cable	stranded cable
Max. wire size	mm <sup>2</sup>	1 x 2.5	1 x 1.5
	AWG	1 x 12	1 x 16
Screw torque	Nm	0.5	

# **Wiring diagrams**

#### Fan assisted version



**NOTE**: Separate supply (L) terminals for the heater and the internal fan allow them to be powered independently.

So, dependent on the specific situation, the installer might wish the heating element to be controlled by an upstream thermostat but require the fan to run continuously (although the latter will significantly reduce the product's life).

1 = L (heater)

2 = N

3 = L (fan)


F = aM 6.3 A


# **finder**

## **Wiring diagrams**

#### **NOT Fan assisted versions**

AC version DC version





#### **SAFETY NOTE**

For reasons of safety and performance, heaters must be mounted in the following way:

- 1. keep a distance of 100 mm. from components above and below and of 60 mm from side components
- 2. install vertically (cables below heater) in the bottom part of cabinet
- 3. do not mount heaters over easily inflammable materials
- 4. do not operate in corrosive ambient air

#### WARNING

Do not cover the heater.


The 7H.51 Heater surface is very hot for 15-20 minutes after disconnecting. During working and maintenance, don't touch it.


Caution: risk of burns.

## **Outline drawings**


7H.51.0025 Screw terminal

















# **Outline drawings**


7H.51.0100 Screw terminal





7H.51.0150 Screw terminal











7H.51.0250 / 0400 Screwless terminal



