Fluke temperature accessories

Turn your digital multimeter into a thermometer

Other temperature accessories

80TK Thermocouple Module

- Converts type K thermocouple signals into mV output
- Connects to DMM via standard banana plugs
- Switch selectable °C or °F
- Range: -50 °C to 1000 °C (-58°F to 1832 °F)
- Includes 80PK-1 probe

80T-150UA Universal Solid State Temperature Probe

- For measurement of air, surface and non-corrosive materials
- Measurement range: -50°C to 150 °C (-58 °F to 302 °F)
- Output: 1 mV/°C or 1 mV/°F (switch selectable)
- Connects to DMM via standard banana plugs

80PK-8, 80PK-10, Pipe Clamp **Temperature Probes**

- Type K thermocouples clamp securely onto pipes for fast temperature and superheat measurements
- Durable ribbon sensors
- 1 m (39 in) lead
- Measure from -29 °C to 149 °C
- 80PK-8 for 6.4 mm to 34.9 mm (0.25 in to 1.375 in)
- 80PK-10 for 32 mm to 64 mm (1.25 in to 2.5 in)

Thermocouple Plug Kits

700TC1

A kit of ten mini-plug connectors. One each of the following: Type J (black) Type K (yellow) Type T (blue) Type E (purple) Type R/S (green) Type B or Cu (white) Type L (J-DIN) (blue) Type U (T-DIN) (brown) Type C (red) Type N (orange)

700TC2

A kit of seven mini-plug connectors. Type J (black), two Type K (yellow), two Type E (purple), one Type T (blue), one Type R/S (green), one

80PK-18, **Pipe Clamp** Temperature

Probe Kit

- Includes both 80PK-8 and 80PK-10 Type K clamps
- Provides full range of pipe measurement sizes
- Includes soft carrying case to conveniently keep both clamps handy for any situation

80CK-M and 80CJ-M Type K and J Male Mini-Connectors

- Isothermal screw ter-
- minal for K or J wire
- Suitable for up to 20 gauge thermocouple wire
- Color coded to industry standards (K-yellow, J-black)
- Two per package

Process tools accessories

BP7240

- Li-ion rechargeable battery; nominal 7.2 volt 4400 mA hr
- Use with 750 Series Calibrators
- NiMH rechargeable battery; nominal
- 7.2 volt, 3500 mA hr Use in 700 and 740

700LTP-1 Low Pressure Test Pump


Hand operated pressure pump designed to generate either vacuum to -13 psi/ -.90 bar or pressures to 100 psi/6.9 bar. Ideal for low pressure applications requiring accurate low pressure testing.

700ILF In-line Filter

The Fluke 700ILF can be used to isolate the calibrator from incidental contact with fluids. Particularly useful with the 718 calibrator to help keep moisture or oils from contaminating the on-board pump.

700PTP-1 Pneumatic **Test Pump**

The Fluke 700PTP is a handheld pressure pump designed to generate either vacuum to -11.6 psi/-0.8 bar or pressure to 600 psi/40 bar.



For extending and repairing type J, K or T thermocouple wires.

- Kit includes 3 m (9 ft) of thermocouple wire and 1 pair of male/female mini-connectors
- Maximum continuous exposure temperature: 260 °C (500 °F)
- 80PK-EXT is compatible with type K thermometers; 80PJ-EXT is designed for type J thermometers, and 80PT-EXT is designed for type T thermometers





700HTP-2 Hvdraulic Test Pump

The Fluke 700HTP is designed to generate pressures up to 10,000 psi/ 700 bar. Use the Fluke 700PRV adjustable relief valves to limit pressures from 94 bar (1360 psi) to 376 bar (5450 psi)

700HTH-1 **Hydraulic Test** Hose

The 700HTH is a 10,000 psi, 700 bar test hose that connects to a calibration unit under test from a Fluke 700HTP hydraulic test pump.


700PMP Pressure Pump

The 700PMP is a handoperated pressure pump to provide pressures up to 150 psi/1000 kPa. Output fitting is 1/8 FNPT.

Fluke 700-IV **Current Shunt**

Conversion factor: 10 mV = 1 mAAccuracy (% of input, one-year): 0.025 % Input current: 0 mA to 55 mA Input resistance: 250 Ω nominal Output resistance: 10 Ω nominal Accuracy specification applies from +18 °C and 28 °C to 50 °C Maximum input voltage: 30 V dc

































8

-







