



GENERAL PRODUCT SPECIFICATION

Item No. UN15-DP-E

Date	16-6-2017	Replaces	15-10-15	No. Pages	1
-------------	-----------	-----------------	----------	------------------	---

Product Description:

Style **Economical** Blanket Rolls; high strength perforation down the middle for the 19 cm wide dimension, & cross-wise for the 23cm long dimension.

Item Size (each) 38 cm wide by 46 m long (**200 pads per roll**)

Color Green

Composition Polypropylene >98%, Surfactant < 1.0%, color pigment < 1.0 %

Structure 96% natural white meltblown nonwoven fibers(<10 microns)
4% white spunbond nonwoven coverstock(<15-30 microns)

Technology Meltblown + spunbond

Absorbency Universal (**Hydrophilic** + Oleophilic)

Bonding Bonded (staggered pattern) + Mechanical entanglement

Intended Application Low -Lint Chemical & Static Resistant Sorbent for Water, Oil, or Solvent Base Liquids.

Absorbency Capacity 75 l per bale (saturated; medium viscosity-12.5x)

Packaging Description:

Package configuration	1-Case	Pkg. Weight	6 kg (5.2kg)
Items per Package	1-Role/Case 200 pads	Pkg. Dimensions	46 cm x 46 cm x 40 cm (H)
Container type	Carton		

Physical Properties:

<u>Parameter</u>	<u>SPC Test Method</u>	<u>Units</u>	<u>Nominal</u>	<u>(+/-)Tolerance</u>
Basis Weight	SPCTM-002	G/M2	295	29
Caliper	SPCTM-020	mm	4.5	0.4
Absorbency (med visc)	SPCTM-004B	gL/gS	12.5	2
Tensile Strength	SPCTM-007	daN	20	2
Color	Visual	-----	Green	per standard

The above properties are “nominal” values used for PROCESS CONTROL when the product is produced and/or inspected. Performance “nominals” may vary depending upon the specific application, and/or the environment being applied, stored, or shipped.

**** The "Absorbency" Spec and "SPCTM004" test method is based on the protocol of ASTM F726, using SAE20 non-detergent as the Oil Type, medium viscosity.**

Attributes Product will be free of foreign material contamination, rips, holes, and tears.

Labeling Each package to be clearly labeled with Company Name, Address, Item No., Date, and/or Package Code (Bar Code).

Certification Make no changes in basic process or composition without notifying customer. Claims for non-conformance of goods must be made within 60-days of delivery.