

MOS FET Relays SOP 4-pin, General-purpose Type

## **High-sensitivity MOS FET relays** in SOP 4-pin packages contribute to equipment power consumption reduction

Contact form: 1a (SPST-NO)

· Load voltage: 60/350 V

• High-sensitivity type \* Driving current: 2.0 mA (recommended condition)



Note: The actual product is marked differently from the image shown here.

### Application Examples

- Semiconductor test equipment
- Test & Measurement equipment
- Communication equipment
- Security equipment
- · Industrial equipment
- Power circuit
- Amusement equipment

#### **Package**

(Unit: mm, Average)

### Model Number Legend

Special SOP 4-pin



Note: The actual product is marked differently from the image shown G3VM- 🗆 🗆 🗆 🗆 🗆 1 2 3 4 5

1. Load voltage 6:60 V

2. Contact form 1 : 1a (SPST-NO) 35: 350 V

4. Additional functions

Y: Dielectric strength between I/O 3,750 V

3. Package

V: Special SOP 4-pin

#### 5. Other informations

When specifications overlap, serial code is added in the recorded order.

## **Ordering Information**

				Continuous	Stick packaging		Tape packaging			
Package	Contact form	Terminals	Load voltage (peak value) *	load current	Model	Minimum package quantity	Model	Minimum package quantity		
Special	1a (SPST-NO)	10 (SDST NO)	Surface		60 V	700 mA	G3VM-61VY4	125 nos	G3VM-61VY4(TR05)	500 pcs.
SOP 4-pin		Γ-NO) mounting Terminals	350 V	110 mA	G3VM-351VY1	125 pcs.	125 pcs.	G3VM-351VY1(TR05)	500 pcs.	

\*The AC peak and DC value are given for the load voltage and continuous load current.

Note: To order tape packaging for Relays with surface-mounting terminals, add "(TR05)" to the end of the model number.

## Absolute Maximum Ratings (Ta = 25°C)


ltem		Symbol	G3VM-61VY4	G3VM-351VY1	Unit	Measurement conditions
	LED forward current	lf	30		mA	
Input	LED forward current reduction rate	ΔI <sub>F</sub> /°C	-0.3		mA/°C	Ta≥25°C
·	LED reverse voltage	VR	6		V	
	Junction temperature	TJ	1	25	°C	
	Load voltage (AC peak/DC)	Voff	60	350	V	
	Continuous load current (AC peak/DC)	lo	700	110	mA	
Output	ON current reduction rate	Δlo/°C	-8.3 -1.1		mA/°C	G3VM-61VY4 : Ta≥50°C G3VM-351VY1: Ta≥25°C
	Pulse ON current	lop	2.1 0.33		Α	t=100 ms, Duty=1/10
	Junction temperature	TJ	125		°C	
Dielectric strength between I/O *		V <sub>I-O</sub>	3,750		Vrms	AC for 1 min
Ambient operating temperature		Та	-40 to +85		°C	1400
Ambient storage temperature		Tstg	-55 to +125			With no icing or condensation
Soldering temperature		_	260			10 s


<sup>\*</sup>The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

## Electrical Characteristics (Ta = 25°C)

	Item	Symbol		G3VM-61VY4	G3VM-351VY1	Unit	Measurement conditions	
			Minimum	1.1 1.27 1.4		V		
	LED forward voltage	VF	Typical				I <sub>F</sub> =10 mA	
			Maximum					
	Reverse current	lr	Maximum	1	0	μΑ	V <sub>R</sub> =5 V	
Input	Capacitance between terminals	Ст	Typical	30		РΕ	V=0 V, f=1 MHz	
	Trigger I ED femiliard comment	let	Typical	0.1	0.2	m A	Io=Continuous load current	
	Trigger LED forward current	IFT	Maximum	1		mA	rated value	
	Release LED forward current	IFC	Minimum	0.01		mA	G3VM-61VY4 : I <sub>OFF</sub> =10 μA G3VM-351VY1: I <sub>OFF</sub> =100 μA	
	Maximum resistance with output ON	Ron	Typical	0.15	28 (22)	Ω	I <sub>F</sub> =2 mA, I <sub>O</sub> =Continuous load current rated value ( ) is a value within t < 1s.	
			Maximum	0.3	50 (35)			
Output	Current leakage when the	ILEAK	Typical	2	1	nA	V Lood voltage rated value	
	relay is open		Maximum	1,000			Voff=Load voltage rated value	
	Capacitance between terminal	Coff	Typical	100	30	РΕ	V=0 V, f=1 MHz	
Capacita	nce between I/O terminals	C <sub>I-O</sub>	Typical	0.8		р <b>F</b>	Vs=0 V, f=1 MHz	
Insulatio	Insulation resistance between I/O terminals		Minimum	1,000		МΩ	V <sub>I-O</sub> =500 VDC, RoH≤60%	
terminals			Typical	10 <sup>8</sup>				
Turn_ON	Turn-ON time  Turn-OFF time		Typical	3	1	ms	I <sub>F</sub> =2 mA, R <sub>L</sub> =200 Ω, V <sub>DD</sub> =20 V	
Tuill-ON			Maximum	6	2			
Turn_OFF			Typical	0.4	0.5	1113		
Tuill-OF			Maximum	1	1			

<sup>\*</sup>Turn-ON and Turn-OFF Times





## **Recommended Operating Conditions**

For usage with high reliability, Recommended Operation Conditions is a measure that takes into account the derating of Absolute Maximum Ratings and Electrical Characteristics.

Each item on this list is an independent condition, so it is not simultaneously satisfy several conditions.


Item	Symbol		G3VM-61VY4	G3VM-351VY1	Unit
Load voltage (AC peak/DC)	V <sub>DD</sub>	Maximum	48	280	V
	lF	Minimum	-		mA
Operating LED forward current		Typical	2		
		Maximum	25		
Continuous load current (AC peak/DC)	lo	Maximum	700	110	
Ambient energting temperature	Ta	Minimum	-40		°C
Ambient operating temperature		Maximum	85		

## **Spacing and Insulation**


Item	G3VM-61VY4 G3VM-351VY		Unit	
iteiii	Mini			
Creepage distances	5.0		mm	
Clearance distances	5			
Internal isolation thickness	0	.2		

## **Engineering Data**


#### LED forward current vs. **Ambient temperature**




#### Continuous load current vs. **Ambient temperature**




#### LED forward current vs. LED forward voltage




### Continuous load current vs. On-state voltage




#### G3VM-351VY1







#### On-state resistance vs. **Ambient temperature** G3VM-61VY4




G3VM-351VY1



Trigger LED forward current vs. Ambient temperature




#### Turn ON, Turn OFF time vs. **LED forward current**




## **Engineering Data**


## Turn ON, Turn OFF time vs. Ambient temperature




#### Current leakage vs. Ambient temperature



## Current leakage vs. Load voltage



## Relative capacity between output terminals vs. Load voltage



## **Appearance/Terminal Arrangement/Internal Connections**

#### **Appearance**

Special SOP 4-pin

Pin 1 mark
OMRON logo


1 OMRON logo
1 OF 1000 A Model name (See note 2.)
2 OMRON SOR Model name (See note 3.)
32 A015 3 Model name (See note 3.)

LOT.NO. Traceability code

Note: 1. The actual product is marked differently from the image shown here. Note: 2. "G3VM" does not appear in the model number on the Relay.

Note: 3. The indentation in the corner diagonally opposite from the pin 1 mark is from a pin on the mold.

# Terminal Arrangement/Internal Connections (Top View)




Dimensions (Unit: mm)

Special SOP 4-pin \*




#### **Surface-mounting Terminals**

Weight: 0.1 g



#### **Actual Mounting Pad Dimensions**

(Recommended Value, Top View)



\*The external dimensions are different from those of the standard SOP 4-pin, but the mounting pad dimensions are the same. **Note:** The actual product is marked differently from the image shown here.

### **Approved Standards**

UL recognized



Model	Approved Standards	Contact form	File No.
G3VM-61VY4 G3VM-351VY1	UL recognized	1a (SPST-NO)	E80555

## **Safety Precautions**

• Refer to the Common Precautions for All MOS FET Relays for precautions that apply to all MOS FET Relays.

MEMO

Please check each region's Terms & Conditions by region website.

**OMRON Corporation Device & Module Solutions Company** 

#### **Regional Contact**

**Americas** 

https://components.omron.com/us

Asia-Pacific

https://components.omron.com/ap

Korea

https://components.omron.com/kr

Europe

https://components.omron.com/eu

China

https://components.omron.com.cn

Japan

https://components.omron.com/jp