

# **Compact 20 A Power Relay**

- 10.5 mm (W) slim size and 1 pole 16 A/20 A switching capability
- High sensitivity of 530 mW coil consumption and further saving energy with holding voltage 50%
- Min. 6.4 mm of insulation distance and 10 kV impulse withstand voltage (between coil and contacts)
- IEC60664-1 Reinforced insulation conformed
- IEC/EN60079-15 conformed. (Only for G5PZ-1A4-E model)





Refer to the Precautions on page 5.

### **■**Model Number Legend

1. Number of Poles 2. Contact Form

1 : 1-pole A : SPST-NO (1a)

3. Enclosure rating

None : Flux protection 4 : Sealed

4. Classification

None : Standard
E : High-capacity

# ■Application Examples

Air conditioners

OA equipments

· Home appliances

· Industrial machinery

# ■Ordering Information

Classification	Contact form	Enclosure rating	Model	Rated coil voltage	Minimum packing unit
Standard		Flux protection	G5PZ-1A	5 VDC	
High-capacity	SPST-NO (1a)	Flux protection	G5PZ-1A-E	12 VDC 24 VDC	100 pcs. / Tray
		Sealed	G5PZ-1A4-E		

Note 1. When ordering, add the rated coil voltage to the model number.

Example: G5PZ-1A DC12

----- Rated coil voltage

However, the notation of the coil voltage on the product case as well as on the packing will be marked as \\_\\_VDC.

# ■Ratings

#### ●Coil

	Item	Rated current (mA)	Coil resistance (Ω)	Must-operate voltage (V)	Must-release voltage (V)	Max. voltage (V)	Power consumption (mW)
Rated voltage				% of rated voltage			
5 VDC		106	47				
12 VDC		44.1	272	75% max.	10% min.	140% (at 23°C)	Approx. 530
24 VDC		22.1	1087			( = 0 0)	

Note 1. The rated current and coil resistance are measured at a coil temperature of 23°C with a tolerance of ±10%.

Note 2. The operating characteristics are measured at a coil temperature of 23°C.

Note 3. The "Max. voltage" is the maximum voltage that can be applied to the relay coil.

#### **●**Contacts

	Classification	Standard	High-c	apacity		
	Enclosure rating	Flux protection	Flux protection Flux protection			
	Model	G5PZ-1A	G5PZ-1A-E	G5PZ-1A4-E		
Item	Load	Resistive load				
Contact type		Single				
Contact materi	al	Ag-alloy (Cd free)				
Rated load		16 A at 250 VAC	20 A at	250 VAC		
Rated carry current		16 A	20 A			
Max. switching voltage		250 VAC				
Max. switching current		16 A	16 A 20 A			

### **■**Characteristics

Classification		Standard	High-c	capacity			
Item Enclosure rating		Flux protection	Flux protection	Sealed			
Contact resistance *1		100 mΩ					
Operate time		15 ms max.					
Release time		5 ms max.					
Insulation resistance *2		1,000 MΩ min.					
Dielectric strength	Between coil and contacts	4,000 VAC 50/60 Hz 1 min					
Dielectric strength	Between contacts of the same polarity	1,000 VAC 50/60 Hz 1 min	I,000 VAC 50/60 Hz 1 min				
Impulse withstand voltage	Between coil and contacts	10 kV (1.2 x 50 μs)					
Vibration resistance	Destruction	10 to 55 to 10 Hz, 0.75 mm single amplitude (1.5 mm double amplitude)					
VIDIALION TESISLANCE	Malfunction	10 to 55 to 10 Hz, 0.75 mm single amplitude (1.5 mm double amplitude)					
Shock resistance	Destruction	1,000 m/s <sup>2</sup>					
Onder resistance	Malfunction	200 m/s <sup>2</sup>					
	Mechanical	2,000,000 operations min.					
Durability Electrical (resistive load)		100,000 operations at 250 VAC, 16 A	50,000 operations at 250 VAC, 20 A	20,000 operations at 250 VAC, 20 A			
Failure rate (P level) (reference value) *3		5 VDC 100 mA					
Ambient operating temperature		-40 to 70°C (with no icing or condensation)					
Ambient operating humidity		5 to 85%					
Weight		Approx. 10.5 g					

Note. Values in the above table are the initial values at 23°C.

- \*1. Measurement conditions: 5 VDC, 1 A, voltage drop method
- \*2. Measurement conditions: Measured at the same points as the dielectric strength using a 500 VDC ohmmeter.
- \*3. This value was measured at a switching frequency of 120 operations/min.

# ■ Actual Load Life (Reference Values)

1. 250 VAC Inverter load (Standard)


Inrush: 240 A (0-P, Rise Time 3 ms or more), Current 16 A, Cut off current 0 A 50,000 operations min. (at 23°C)

2. 250 VAC Inverter load (High-capacity)


Inrush: 240 A (0-P, Rise Time 3 ms or more), Current 20 A, Cut off current 0 A 50,000 operations min. (at 23°C)

# **■**Engineering Data

### Maximum Switching Capacity




#### ● Ambient Temperature vs. Maximum **Coil Voltage**



Note. The maximum coil voltage refers to the maximum value in a varying range of operating power voltage, not a continuous voltage.

#### Shock malfunction



G5PZ-1A 12 VDC Test Item:

Number of Relays: 5 pcs


Test Method:

Shock is applied 3 times in 6 directions along 3 axes and the level at which shock caused malfunction is measured. The energized voltage is 100% of the


rated voltage. 200 m/s<sup>2</sup>

■Dimensions














CAD Data

# **■**Approved Standards

The approval rating values for overseas standards are different from the performance values determined individually. Confirm the values before use.

•UL Recognized: (File No. E41515) CSA Certified: (File No. LR31928)

Model	Contact form	Coil ratings	Contact ratings	Number of test operations
G5PZ-1A			16 A, 277 VAC (Resistive) 70°C	6,000
G5PZ-1A-E	SPST-NO(1a)	5 to 24 VDC	20 A, 277 VAC (Resistive) 70°C	50,000
G5PZ-1A(4)(-E)			20 A, 211 VAC (Resistive) 10 C	6,000

●EN/IEC, VDE Certified: ♠ (Certificate No. 40042966)

Model	Contact form	Coil ratings	Contact ratings	Number of test operations
G5PZ-1A	SPST-NO(1a)	5, 12, 24 VDC	16 A, 250 V AC (Resistive) 70°C	6,000

●EN/IEC, TÜV Certified: △ (Certificate No. R50408241)

Model	Contact form	Coil ratings	Contact ratings	Number of test operations
G5PZ-1A-E	SPST-NO(1a)	5, 12, 24 VDC	20 A, 250 VAC (cosφ=1) 70°C	50,000
G5PZ-1A(4)(-E)				6,000

●CQC Certified: ©© (Certificate No. CQC15002133270)

Model	Contact form	Coil ratings	Contact ratings	Number of test operations
G5PZ-1A			16 A, 250 VAC (cosφ=1) 70°C	6,000
G5PZ-1A-E	SPST-NO(1a)	5, 12, 24 VDC	20 A, 250 VAC (cosφ=1) 70°C	50,000
G5PZ-1A(4)(-E)				6,000

Creepage distance	9.5 mm min.
Clearance distance	6.4 mm min.
Insulation material group	III a
Type of insulation coil-contact circuit open contact circuit	Reinforced (Standard : Pollution degree 2) (High-capacity : Pollution degree 3)
Type of disconnection open contact circuit	Micro disconnection
Rated Insulation voltage	250 VAC
Pollution degree	2
Rated voltage system	250 V
Over voltage category	III
Category of protection according to IEC 61810-1	RT II (Flux protection) / RT III (Sealed)
Tracking resistance according to IEC 60112	PTI 250 V min. (housing parts)
Flammability class according to UL94	V-0

### ■Precautions

### ●Please refer to "PCB Relays Common Precautions" for correct use.


#### Correct Use

#### Handling

For G5PZ flux protection type, do not perform immersion cleaning by boiling or soaking in water.

#### Coil Voltage Reduction (Holding Voltage) after Relay Operation

- If the coil voltage is reduced to the holding voltage after Relay operation, first apply the rated voltage to the coil for at least 100 ms, as shown below.
- A voltage of at least 50% of the rated voltage is required for the coil holding voltage. Do not allow voltage fluctuations to cause the coil holding voltage to fall below this level.



	Applied coil voltage	Coil resistance*	Power consumption
Rated voltage	100%	475 Ω (5 VDC) 272 Ω (12 VDC)	Approx. 530 mW
Holding voltage	50%	1087 Ω (24 VDC)	Approx. 133 mW

The coil resistance were measured at a coil temperature of 23°C with tolerances of ± 10%.

Please check each region's Terms & Conditions by region website.

#### **OMRON Corporation**

**Device & Module Solutions Company** 

#### **Regional Contact**

Americas

https://components.omron.com/us

Asia-Pacific

https://components.omron.com/ap

Korea

https://components.omron.com/kr

Europe

https://components.omron.com/eu

China

https://components.omron.com.cn

Japan

https://components.omron.com/jp

In the interest of product improvement, specifications are subject to change without notice.

Cat. No. K320-E1-02 0423 (0320)

<sup>©</sup> OMRON Corporation 2020-2023 All Rights Reserved.