


Torque Calibration Analysers Data Sheet

8612

Electronic Torque Tester Dremotest E 0.2-3150 N.m / 1.8lbf.in-2323lbf.ft

- For verifying and setting clockwise torque wrenches and torque screwdrivers in the range from 0.2-3150 N.m
- Simple electronic torque tester with integrated torque transducer (DMS)
- With fixed hexagon female drive 1/4". 10,17,36,46 (model dependent)
- With 1/4", 3/8", 1/2", 3/4", 1" and 1.1/2" square drive adaptor or bit adaptor (model dependent)
- High measurement accuracy: +/- 1% tolerance of reading, +/- 1 digit.
- Break point measurement (1st peak)
- Autoreset
- Can be switched from N.m to lbf.ft
- Serial interface RS232
- Optionally available: adaptor for cigarette lighter socket (12V), no 8612-390



When using this product, please ensure that the manufactures recommended maximum torque, applied to the torque tester is not exceeded, as this will result in permanent damage.

N.m	lbf.in	lbf.ft	⊙	□	Resolution	Adaptor □	⚖	Code	No.
0,2-12	1,8-106		6.3		0,001	1/4"; 3/8"	3.0	2288311	8612-012
0,9-55		0,7-40,6	10.0		0,01	1/4"; 3/8"	3.0	1947699	8612-050
9-320		7-236	17.0		0,1	3/8"; 1/2"	3.0	1856111	8612-300
90-1100		66-811	36.0		1	1/2"; 3/4"	10.0	1947702	8612-1000
500-3150		369-2323		40	1	1"	26.0	2529858	8612-3150

Optional accessories:

Description	⚖	Code	No.
Adaptor for cigarette lighter socket	0.2	1878719	8612-390