PCB Relay

G6A

Fully Sealed Relay with High Impulse Dielectric for Use in Telecommunications Equipment

- High sensitivity can be driven by digital circuits.
- Horizontal design allows use in 1/2-inch PCB
- Impulse withstand voltage meets FCC Part 68 requirements.
- Relays can be mounted side-by-side due to low magnetic leakage.
- Single- and double-winding latching relays also available.
- Special models available for low thermoelectromotive force.

RoHS Compliant

Refer to pages 16 to 17 for details.



91 ® FCC

Ordering Information

Single-side Stable Type

Contact		Ag + Au-Alloy
General purpose	DPDT	G6A-274P-ST-US
Low-sensitivity		G6A-274P-ST40-US

Single-winding Latching Type

Contact		Ag + Au-Alloy
General purpose	DPDT	G6AU-274P-ST-US

Double-winding Latching Type

Contact		Ag + Au-Alloy
General purpose	DPDT	G6AK-274P-ST-US
Low-sensitivity		G6AK-274P-ST40-US

Note: When ordering, add the rated coil voltage to the model number.

Example: G6A-274P-ST-US 12 VDC

Rated coil voltage

Model Number Legend

1 2 7 8 9 6

1. Relay Function

None: Single-side stable Single-winding latching

2. Contact Form

DPDT

3. Contact Type

7: Bifurcated crossbar Ag (Au-Alloy) contact

Double-winding latching 4. Enclosure Ratings 4: Fully sealed

5. Terminals

P: Straight PCB

6. Stand-off

ST: Stand-off 0.64 mm

7. Special Function

40: Low-sensitivity (400 mW) LT: Low thermoelectromotive force

8. Approved Standards US: UL, CSA certified

9. Rated Coil Voltage 3, 4.5, 5, 6, 9, 12, 24, 48 VDC

Specifications

■ Coil Ratings

General-purpose, DPDT Relays

Rated voltage		3 VDC	4.5 VDC	5 VDC	6 VDC	9 VDC	12 VDC	24 VDC	48 VDC
Rated current	66.7 mA	44.6 mA	40 mA	33.3 mA	22.2 mA	16.7 mA	8.3 mA	4.9 mA	
Coil resistance		45 Ω	101 Ω	125 Ω	180 Ω	405 Ω	720 Ω	2,880 Ω	9,750 Ω
Coil inductance	Armature OFF	0.07	0.16	0.2	0.29	0.63	1.1	4.5	13.7
(H) (ref. value)	Armature ON	0.065	0.14	0.18	0.26	0.57	1.06	4.1	12.5
Must operate volta	age	70% max	. of rated vo	oltage					
Must release volta	ige	10% min.	of rated vo	Itage					
Max. voltage		200% of rated voltage at 23°C							
Power consumption Approx. 200 mW A					Approx. 235 mW				

Low-sensitivity DPDT Relays

Rated voltage		3 VDC	4.5 VDC	5 VDC	6 VDC	9 VDC	12 VDC	24 VDC	48 VDC
Rated current	133.3 mA	88.9 mA	80 mA	66.7 mA	44.3 mA	33.3 mA	16.7 mA	8.3 mA	
Coil resistance		22.5 Ω	50.6 Ω	62.5 Ω	90 Ω	203 Ω	360 Ω	1,440 Ω	5,760 Ω
Coil inductance	Armature OFF	0.03	0.065	0.08	0.11	0.27	0.52	2.1	7.5
(H) (ref. value)	Armature ON	0.02	0.06	0.07	0.1	0.23	0.43	1.8	6.4
Must operate volta	age	70% max.	of rated volta	age	•	•	•	•	•
Must release volta	ige	10% min. c	f rated volta	ige					
Max. voltage 150% of rated voltage at 23°C									
Power consumption Approx. 400 mW									

Note: 1. The rated current and coil resistance are measured at a coil temperature of 23°C with a tolerance of ±10%.

- 2. Operating characteristics are measured at a coil temperature of 23°C.
- 3. The maximum voltage is the highest voltage that can be imposed on the relay coil.

Single-winding Latching, DPDT Relays

Rated voltage		3 VDC	4.5 VDC	5 VDC	6 VDC	9 VDC	12 VDC	24 VDC	48 VDC
Rated current	33.7 mA	22.2 mA	20 mA	16.7 mA	11.1 mA	8.3 mA	4.2 mA	2.5 mA	
Coil resistance		89 Ω	202 Ω	250Ω	360 Ω	810 Ω	1,440 Ω	5,760 Ω	19,000 Ω
Coil inductance	Armature OFF	0.15	0.34	0.44	0.64	1.38	2.5	9.2	28.5
(H) (ref. value)	Armature ON	0.11	0.25	0.35	0.48	1.07	2	7.2	22
Must operate volta	age	70% max	. of rated v	oltage					
Must release volta	ige	70% max	. of rated v	oltage					
Max. voltage		200% of rated voltage at 23°C							
Power consumption Approx. 100 mW							Approx. 120 mW		

Double-winding Latching, DPDT Relays

Rated voltage			3 VDC	4.5 VDC	5 VDC	6 VDC	9 VDC	12 VDC	24 VDC	48 VDC
Rated current	Rated current			40.2 mA	36 mA	30 mA	20 mA	15 mA	7.5 mA	4.2 mA
Coil resistance			45 Ω	112 Ω	139 Ω	200 Ω	450 Ω	800 Ω	3,200 Ω	11,520 Ω
Coil inductance	Set	Armature OFF	0.037	0.09	0.11	0.16	0.38	0.6	2.1	8.5
(H) (ref. value)		Armature ON	0.027	0.065	0.08	0.12	0.28	0.45	1.5	6.3
	Reset	Armature OFF	0.027	0.065	0.08	0.12	0.28	0.45	1.5	6.3
		Armature ON	0.037	0.09	0.11	0.16	0.38	0.6	2.1	8.5
Must operate vol	tage		70% max.	of rated vol	tage					
Must release volt	age		70% max.	of rated vol	tage					
Max. voltage			200% of rated voltage at 23°C							
Power consumpt	Power consumption									Approx. 200 mW

Note: 1. The rated current and coil resistance are measured at a coil temperature of 23°C with a tolerance of ±10%.

- 2. Operating characteristics are measured at a coil temperature of 23°C.
- 3. The maximum voltage is the highest voltage that can be imposed on the relay coil.

Double-winding Latching, Low-sensitivity DPDT Relays

Rated voltage			3 VDC	4.5 VDC	5 VDC	6 VDC	9 VDC	12 VDC	24 VDC	48 VDC	
Rated current	120 mA	79.9 mA	72.5 mA	60 mA	40 mA	30 mA	15 mA	7.5 mA			
Coil resistance	Coil resistance			56.3 Ω	69 Ω	100 Ω	225 Ω	400 Ω	1,600 Ω	6,400 Ω	
Coil inductance	Set	Armature OFF	0.015	0.04	0.05	0.07	0.16	0.28	1.1	4	
(H) (ref. value)		Armature ON	0.01	0.025	0.035	0.05	0.12	0.2	0.75	2.9	
	Reset	Armature OFF	0.01	0.025	0.035	0.05	0.12	0.2	0.75	2.9	
		Armature ON	0.015	0.04	0.05	0.07	0.16	0.28	1.1	4	
Must operate vol	tage		70% max.	70% max. of rated voltage							
Must release volt	Must release voltage 70% max. of rated voltage										
Max. voltage	150% of rated voltage at 23°C										
Power consumpt	ion		Approx. 360 mW								

Note: 1. The rated current and coil resistance are measured at a coil temperature of 23°C with a tolerance of ±10%.

2. Operating characteristics are measured at a coil temperature of 23°C.

3. The maximum voltage is the highest voltage that can be imposed on the relay coil.

■ Contact Ratings

Item	G6A-274	G6A-274P-ST(40)-US				
Load	Resistive load (cosφ = 1)	Inductive load (cosφ = 0.4; L/R = 7 ms)				
Rated load	0.5 A at 125 VAC; 2 A at 30 VDC 0.3 A at 125 VAC; 1 A at 30 VDC					
Contact material	Ag (Au-Alloy)					
Rated carry current	3 A					
Max. switching voltage	250 VAC, 220 VDC					
Max. switching current	2 A 1 A					
Max. switching power	125 VA, 60 W	62.5 VA, 30 W				
Failure rate (reference value)	0.01 mA at 10 mVDC					

Item	G6AK-274P-ST(40)-US/G6AU-274P-ST-US				
Load	Resistive load (cosφ = 1)	Inductive load (cosφ = 0.4; L/R = 7 ms)			
Rated load	0.5 A at 125 VAC; 2 A at 30 VDC 0.25 A at 125 VAC; 1 A at 30 VDC				
Contact material	Ag (Au-Alloy)				
Rated carry current	3 A				
Max. switching voltage	250 VAC, 220 VDC				
Max. switching current	2 A	1 A			
Max. switching power	125 VA, 60 W	62.5 VA, 30 W			
Failure rate (reference value) (See note.)) 0.01 mA at 10 mVDC				

Note: P level: $\lambda_{60} = 0.1 \times 10^{-6}$ /operation

This value was measured at a switching frequency of 60 operations/min and the criterion of contact resistance is 50 Ω . This value may vary depending on the switching frequency and operating environment. Always double-check relay suitability under actual operating conditions.

■ Characteristics

Contact resistance (See note 1.)	50 m $Ω$ max.
Operate (set) time (See note 2.)	Single-side stable types: 5 ms max. (approx. 3 ms) Latching types: 5 ms max. (approx. 2.5 ms)
Release (reset) time (See note 2.)	Single-side stable types: 3 ms max. (approx. 1.2 ms) Latching types: 5 ms max. (approx. 2.5 ms)
Min. set/reset signal width	10 ms min.
Max. operating frequency	Mechanical: 36,000 operations/hr Electrical: 1,800 operations/hr (under rated load)
Insulation resistance (See note 3.)	1,000 M Ω min. (at 500 VDC); except for set-reset
Dielectric strength	1,000 VAC, 50/60 Hz for 1 min between coil and contacts 1,000 VAC, 50/60 Hz for 1 min between contacts of different polarity 1,000 VAC, 50/60 Hz for 1 min between contacts of same polarity 250 VAC, 50/60 Hz for 1 min between set and reset coils
Impulse withstand voltage	1,500 V (10 x 160 μs) (conforms to FCC Part 68)
Vibration resistance	Destruction: 10 to 55 to 10 Hz, 2.5-mm single amplitude (5-mm double amplitude) Malfunction: 10 to 55 to 10 Hz, 1.65-mm single amplitude (3.3-mm double amplitude)
Shock resistance	Destruction: 1,000 m/s ² (approx. 100G) Malfunction: 500 m/s ² (approx. 50G)
Endurance	Mechanical: 100,000,000 operations min. (at 36,000 operations/hr) Electrical: 500,000 operations min. (at 1,800 operations/hr)
Ambient temperature	Operating: -40°C to 70°C (with no icing)
Ambient humidity	Operating: 5% to 85%
Weight	Approx. 3.5 g

Note: The data shown above are initial values.

Note: 1. The contact resistance was measured with 10 mA at 1 VDC with a voltage drop method.

- 2. Values in parentheses are actual values.
- 3. The insulation resistance was measured with a 500-VDC megohmmeter applied to the same parts as those used for checking the dielectric strength (except between the set and reset coil).


■ Approved Standards

UL (File No. E41515)/CSA (File No. LR31928)


Model	Contact form	Coil ratings	Contact ratings
G6A-274P-ST(40)-US G6AK-274P-ST(40)-US G6AU-274P-ST-US	DPDT	3 to 48 VDC	0.6 A, 125 VAC 2 A, 30 VDC 0.6 A, 110 VDC

Engineering Data

Maximum Switching Power




Ambient Temperature vs. Maximum Coil Voltage



The maximum coil voltage refers to the maximum value in a varying range of operating power voltage, not a continuous voltage.

Endurance





Dimensions

1. All units are in millimeters unless otherwise indicated.


2. Orientation marks are indicated as follows:

G6A-274P-ST(40)-US






Terminal Arrangement/ Internal Connections (Bottom View)




Mounting Holes (Bottom View)

Tolerance: ±0.1




G6AK-274P-ST(40)-US






*Average value


Terminal Arrangement/ **Internal Connections** (Bottom View)






Mounting Holes (Bottom View)

Tolerance: ±0.1




G6AU-274P-ST-US






Terminal Arrangement/ Internal Connections (Bottom View)



Mounting Holes (Bottom View)

Tolerance: ±0.1



Precautions

Long-term Continuously ON Contacts

Using the Relay in a circuit where the Relay will be ON continuously for long periods (without switching) can lead to unstable contacts because the heat generated by the coil itself will affect the insulation, causing a film to develop on the contact surfaces. We recommend using a latching relay (magnetic-holding relay) in this kind of circuit. If a single-side stable model must be used in this kind of circuit, we recommend using a fail-safe circuit design that provides protection against contact failure or coil burnout.


Relay Handling

When washing the product after soldering the Relay to a PCB, use a water-based solvent or alcohol-based solvent, and keep the solvent temperature to less than 40°C. Do not put the Relay in a cold cleaning bath immediately after soldering.

Double-swicthing load in two poles

Double-switching in two poles as shown in the figure below, one pole and two pole interval may become MBB(Make Before Break) mechanically according to the timing of the point of contact switching (By the short-circuit mode), and the malfunction might be caused.

In such a circuit, direct electric switching should be avoided, and concern for contact to be carried after the contact of Relay absolutely switches in condition of no load.



ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

Cat. No. K020-E1-09