

GDM-8261A

6 ½ Digit Dual Measurement Multimeter

FEATURES

- 6 1/2 Digit Display: 1,200,000 Counts
- DCV Basic Accuracy: 0.0035%
- Dual Measurements to Perform Two Selected Measurements Simultaneously
- Bright Vacuum Fluorescent Display (VFD)
- 11 Measurement Functions & 10 Math Functions
- . High Resolution: Up to 100pA Resolution with DCI and 1nA with ACI Measurements
- Temperature Measurement (RTD & Thermocouple) From -200°C ~ +1820°C
- High Data Transmission Speed: Up to 2,400 readings/s Through USB Interface
- Standard Interfaces: USB, RS-232C, Digital I/O
- . Optional Interfaces: GPIB or LAN
- Optional Scanner Card: GDM-SC1 (V ch x 16, I ch x 2)
- Free PC Software : DMM-Viewer, LabVIEW Driver



Boost Your Measurement Speed & Efficiency

The GDM-8261A is a high precision 6 ½ digit Digital Multimeter with dual measurement displays, 11 measurement functions and 10 math functions at high accuracy (35ppm DC voltage accuracy) to accommodate the most frequently performed parameter measurements in various application fields today.

The GDM-8261A adopts a scanner card, which carries 16 V-Channels and 2 I-Channels, to facilitate the measurements of multiple-test points on either a device or multiple devices all at a press of a button. With this multi-point measurement capability, the GDM-8261A can be used as a semi-auto ATE System to increase the throughput of manufacturing test or as a data logger to perform long term monitoring or characterization of a DUT. A PC Software, DMM-Viewer, is available with GDM-8261A to support multi-channel panel setting and data logging of the scanner card. Besides, a LabVIEW driver is also supported to help user create his/her own virtual instrument on the PC screen for easy programming. For ATE system measurements or remote control applications, both USB and RS-232C Interfaces are provided as standard, and either GPIB or LAN can be selected as optional interface for the GDM-8261A.

IDEAL FOR BENCH ASSIGNMENTS



The GDM-8261A includes all the basic measurement functions that are required for engineers to handle design, development and testing jobs for electronic circuits or products. The basic measurement functions include voltage, current, resistance, diode, continuity, frequency and temperature. Remarkably, the current measurement function covers a very wide range from $100\,\mu$ A to 10A for DC current (in 6 ranges) and from 1mA to 10A for AC current (in 5 ranges). In addition, the GDM-8261A features 10 Math functions (dBm, dB, compare and other mathematical operations) to accommodate specific measurement requirements and complex measurement applications.

DUAL MEASUREMENTS WITH DUAL DISPLAYS



Unlike most of the "dual display" digital multimeters, which show test result on the primary display and range information on the secondary display, the GDM-8261A is able to perform two measurement functions simultaneously and shows the test results on primary display and secondary display respectively.

1st Display	2nd Display							
	ACV	DCV	ACI	DCI	Hz/P	2W/4W*		
ACV	1	1	1	1	1	-		
DCV	1	1	1	1	1	-		
ACI	1	1	1	✓	1	-		
DCI	1	1	1	1	1	-		
Hz/P	1	1	1	✓	1	-		
2W/4W*	_	-	_	_	-	1		

The GDM-8261A supports an almost unlimited number of measurement combinations of dual measurement functions, besides the normal test result and range information displays, greatly increases the test speed of multi-function measurement tasks.

HIGH MEASUREMENT RESOLUTION & HIGH SAMPLING RATE


Mode	Resolution	DCV/DCI/Resistance Measurement Speed			
Fast	4½ digits	2,400 readings/second			
Medium	5½ digits	600 readings/second			
Slow	6½ digits	30 readings/second			

The GDM-8261A offers an exceptionally high resolution of 0.1 μ V for voltage measurement, 100pA for DC current measurement, 1nA for AC current measurement, and 100 μ Ω for Resistance measurement. This level of resolution and accuracy becomes a must for the precision measurements in specific applications. In addition, the GDM-8261A is capable of acquiring 30 measurement readings/s at the display resolution of 4 ½ digits and 2,400 readings/s at the display resolution of 6 ½ digits. The fast acquisition rate of the GDM-8261A adequately meets today's measurement demands.

2W connection



4W connection



The GDM-8261A offers two methods, both 2-wire and 4-wire, for resistance measurements. The 2-wire measurement is most commonly used for resistance measurement in the range from 100Ω to $10k\Omega$. Whereas the 4-wire connection is normally applied for resistance measurement at a value lower than 100Ω . When applied, 4-wire measurement automatically compensates the test lead resistance and connector contact resistance to get an accurate measurement result.



The GDM-8261A is able to acquire and record 2 ~ 9999 measurement readings for the "store" and "recall" functions. This allows an immediate observation of the maximum, minimum, average or standard deviation values of all the recorded data whenever the data acquisition stops.

MATH MEASUREMENT




The "Math" function of GDM-8261A includes four mathematical operations for measurements: MX+B, 1/X, Percentage and Stats. "MX+B" multiplies the measurement reading (X) by a factor (M) and adds/subtracts an offset value (B) to calculate linear offsets or scales. The "1/X" function divides 1 by the measurement reading (X), calculating the inverse of the reading. The "Percentage" function calculates the ratio of the measured value to a target value using the



following equation: (Reading X – Reference) / Reference x 100%. The "Stats" function makes statistical calculations continuously or by a user-defined measurement counts. The statistical calculations include Maximum, Minimum, Average and Standard deviation. With these mathematical operations, the GDM-8261A makes complex measurements quick and easy without the complexity of manual calculations.

TEMPERATURE MEASUREMENT




The GDM-8261A performs temperature measurement accommodating a wide range of temperature sensors of either thermocouples or RTD (Resistive Temperature Detectors). For thermocouples, the GDM-8261A uses voltage measurement terminals as the thermocouple input and calculates the temperature from the voltage fluctuation. Most of the

popular thermocouple types are supported for temperature measurement on the GDM-8261A. For RTD sensors, the GDM-8261A calculates the voltage fluctuation arisen from the resistance variation due to temperature change. Either front panel terminals or scanner card terminals can be used as the input for temperature sensor.



For system applications, the GDM-8261A provides USB interface and RS-232C interface as standard. Up to 2,400 readings/s of data can be transferred over USB in ASCII format. Either GPIB or LAN interface is available as an option to support the ATE systems currently in use.



The optional scanner card, with a field-installable design, is a self-contained multipoint measurement solution. This approach eliminates the complexities of software development for multipoint measurement and data processing. The scanner card allows users to effectively measure multiple channels connected to a single GDM-8261A.

CONVENIENT PC SOFTWARE

DMM-Viewer



Control & Data Acquisition




Data Reload & Graph



Panel Setting & Data Acquisition for All Scanner Channels

LabVIEW Driver



For the convenience of remote control and long time data acquisition, a free software, DMM-Viewer, is supported with the GDM-8261A. This software allows user to remotely control the GDM-8261A without the need to give commands or to develop programming software. DMM-Viewer's human interface resembles the GDM-8261A front panel, which significantly shortens the user's learning time. For the data capture through a PC, the software allows user to continuously observe the measurement results before saving them into a file. Further more, the saved files can be loaded and viewed as a graph for data analysis.

When GDM-8261A works with scanner card for multi-point measurements, the DMM-Viewer allows user to easily select the measurement function and range for each channel and start acquiring measurement data promptly. The GDM-8261A LabVIEW driver is also available for free download. With this driver, the user is able to create a virtue instrument on the PC for the instrument control. With DMM-Viewer & LabVIEW driver, the GDM-8261A becomes a high value semi-auto ATE system without further software/hardware investments.

PANEL INTRODUCTION

8. The Digital I/O port sends out a signal of compare measurement result for external devices control. Additionally, the Digital I/O port can also be used as a power source for TTL & COMS logic.

9. USB and RS-232C communication ports facilitate the high speed

communication



Accuracy: + (% of reading + % of range) for 1-hour warm-up at 6 ½ digits, slow mode

				Accurac	y: ± (% or reading + % o	or range for 1-nour warn	n-up at 6 ½ digits, slow mode
DC SPECIFICAT	IONS						
FUNCTION	Range (*1)	Resolution	Test Current or etc.	24 Hours 23°C ± 1°C	90 Days 23°C ± 5°C	1 Year 23°C ± 5°C	Temperature Coefficient 0°~18°C /28°~55°C
DC VOLTAGE	100.0000 m V 1.000000 V 10.00000 V 100.0000 V 1000.000 V	0.1 μV 1 μV 10 μV 0.1 mV 1 mV	10MΩ or >10GΩ 10MΩ or >10GΩ 11.11MΩ±1% 10.1MΩ±1% 10.1MΩ±1%	$\begin{array}{c} 0.0030 + 0.0030 \\ 0.0015 + 0.0004 \\ 0.0020 + 0.0006 \\ 0.0020 + 0.0006 \\ 0.0025 + 0.0006 \end{array}$	$\begin{array}{c} 0.0040 + 0.0035 \\ 0.0020 + 0.0005 \\ 0.0030 + 0.0007 \\ 0.0035 + 0.0006 \\ 0.0044 + 0.0010 \end{array}$	$\begin{array}{c} 0.0050 + 0.0035 \\ 0.0035 + 0.0005 \\ 0.0048 + 0.0007 \\ 0.0081 + 0.0006 \\ 0.0090 + 0.0010 \end{array}$	$\begin{array}{c} 0.0005 + 0.0005 \\ 0.0005 + 0.0001 \\ 0.0005 + 0.0001 \\ 0.0005 + 0.0001 \\ 0.0005 + 0.0001 \\ \end{array}$
RESISTANCE (*2)	$\begin{array}{c} 100.0000 \ \Omega \\ 1.000000 \ k\Omega \\ 10.00000 \ k\Omega \\ 10.00000 \ k\Omega \\ 1.000000 \ M\Omega \\ 10.00000 \ M\Omega \\ 10.00000 \ M\Omega \end{array}$	100 μ Ω 1 m Ω 10 m Ω 100 m Ω 1 Ω 10 Ω 100 Ω	1 mA 1 mA 100 μ A 10 μ A 3.5 μ A 350 nA 350 nA//10 MΩ	0.030 + 0.030 0.020 + 0.005 0.020 + 0.005 0.020 + 0.0051 0.020 + 0.0010 0.0150 + 0.0010 0.3000 + 0.0100	0.008 + 0.004 0.008 + 0.001 0.008 + 0.001 0.008 + 0.001 0.008 + 0.001 0.020 + 0.001 0.800 + 0.010	$\begin{array}{c} 0.010 + 0.004 \\ 0.010 + 0.001 \\ 0.010 + 0.001 \\ 0.010 + 0.001 \\ 0.010 + 0.001 \\ 0.010 + 0.001 \\ 0.040 + 0.001 \\ 0.800 + 0.010 \end{array}$	0.0008 + 0.0005 0.0008 + 0.0001 0.0008 + 0.0001 0.0008 + 0.0001 0.0010 + 0.0002 0.0030 + 0.0004 0.1500 + 0.0002
DC CURRENT	100.0000 µA 1.000000 mA 10.00000 mA 100.0000 mA 1.000000 A 10.00000 A	100pA 1nA 10nA 0.1 μA 1 μA 10 μA	< 0.015 V < 0.15 V < 0.07 V < 0.7 V < 0.8 V < 0.5 V	0.010 + 0.020 0.007 + 0.005 0.005 + 0.010 0.010 + 0.004 0.050 + 0.006 0.100 + 0.008	0.04 + 0.025 0.03 + 0.005 0.03 + 0.020 0.03 + 0.005 0.08 + 0.010 0.12 + 0.008	0.05 + 0.025 0.05 + 0.005 0.05 + 0.020 0.05 + 0.005 0.10 + 0.010 0.15 + 0.008	0.002 + 0.0030 0.002 + 0.0005 0.002 + 0.0020 0.002 + 0.0005 0.005 + 0.0010 0.005 + 0.0008
CONTINUITY	1000.000Ω	0.001Ω	1 mA	0.002 + 0.030	0.008 + 0.030	0.010 + 0.030	0.001 + 0.002
DIODE TEST (*3)	1.000000 V	1 μ V	1 mA (*4)	0.002 + 0.010	0.008 + 0.020	0.010 + 0.020	0.001 + 0.002

Note: (*1) 20% overrange on all ranges, except 1000 Vdc/750Vac, 10A range and Continuity.

- (*2) Specifications are for 4-wire ohms function, or 2-wire ohms using REL function.
- (*3) Accuracy specifications are for the voltage measured at the input terminals only.
- (*4) Variation in the current source will create some variation in the voltage drop across a diode junction.
- (*5) Specifications are for sinewave input >5% of range.
- (*6) 750 Vac range limited to 100 kHz
- (*7) Typically 30% of reading error at 1 MHz.
- (*8) Input > 100 mV. For 10 mV to 100 mV inputs, multiply % of reading error x10.
- (*9) Specifications do not include probe accuracy and relative to simulated junction

AC SPECIFICATION	ONS						
FUNCTION	Range (*1)	Resolution	Frequency or etc.	24 Hours 23°C ± 1°C	90 Days 23°C ± 5°C	1 Year 23°C ± 5°C	Temperature Coefficient 0°~18°C /28°~55°C
TRUE RMS AC VOLTAGE (*5)	100.0000mV	0.1 <i>μ</i> V	3Hz~5Hz 5Hz~10Hz 10Hz~20kHz 20kHz~50kHz 50kHz~100kHz 100 kHz~300kHz(*7)	$\begin{array}{c} 1.00+0.03\\ 0.35+0.03\\ 0.04+0.03\\ 0.10+0.05\\ 0.55+0.08\\ 4.00+0.50\\ \end{array}$	1.00 + 0.04 0.35 + 0.04 0.05 + 0.04 0.11 + 0.05 0.60 + 0.08 4.00 + 0.50	1.00 + 0.04 0.35 + 0.04 0.06 + 0.04 0.12 + 0.05 0.60 + 0.08 4.00 + 0.50	0.100 + 0.004 0.035 + 0.004 0.005 + 0.004 0.011 + 0.005 0.060 + 0.008 0.200 + 0.020
	1.000000V~ 750.000 V(*6)	1 μV~ 1mV	3Hz~5Hz 5Hz~10Hz 10Hz~20kHz 20kHz~50kHz 50kHz~100kHz 100kHz~300kHz(*7)	$ \begin{array}{c} 1.00 + 0.02 \\ 0.35 + 0.02 \\ 0.04 + 0.02 \\ 0.10 + 0.04 \\ 0.55 + 0.08 \\ 4.00 + 0.50 \end{array} $	1.00 + 0.03 0.35 + 0.03 0.05 + 0.03 0.11 + 0.05 0.60 + 0.08 4.00 + 0.50	1.00 + 0.03 0.35 + 0.03 0.06 + 0.03 0.12 + 0.05 0.60 + 0.08 4.00 + 0.50	0.100 + 0.003 0.035 + 0.003 0.005 + 0.003 0.011 + 0.005 0.060 + 0.008 0.200 + 0.020
TRUE RMS AC CURRENT (*5)	1.000000 mA	1nA	3Hz~5Hz 5Hz~10Hz 10Hz~5kHz 5kHz~10kHz	1.00+0.04 0.30+0.04 0.10+0.04 0.20+0.25	1.00+0.04 0.30+0.04 0.10+0.04 0.20+0.25	1.0+0.04 0.3+0.04 0.1+0.04 0.2+0.25	0.100 + 0.006 0.035 + 0.006 0.015 + 0.006 0.030 + 0.006
	10.00000 mA	10nA	3Hz~5Hz 5Hz~10Hz 10Hz~5kHz 5kHz~10kHz	1.10+0.06 0.35+0.06 0.15+0.06 0.35+0.70	1.10+0.06 0.35+0.06 0.15+0.06 0.35+0.70	1.10+0.06 0.35+0.06 0.15+0.06 0.35+0.70	0.200 + 0.006 0.100 + 0.006 0.015 + 0.006 0.030 + 0.006
	100.0000 mA	100nA	3Hz~5Hz 5Hz~10Hz 10Hz~5kHz 5kHz~10kHz	1.00+0.04 0.30+0.04 0.10+0.04 0.20+0.25	1.00+0.04 0.30+0.04 0.10+0.04 0.20+0.25	1.00+0.04 0.30+0.04 0.10+0.04 0.20+0.25	0.100 + 0.006 0.035 + 0.006 0.015 + 0.006 0.030 + 0.006
	1.000000 A	1μA	3Hz~5Hz 5Hz~10Hz 10Hz~5kHz 5kHz~10kHz	1.00+0.04 0.30+0.04 0.10+0.04 0.35+0.70	1.00+0.04 0.30+0.04 0.10+0.04 0.35+0.70	1.00+0.04 0.30+0.04 0.10+0.04 0.35+0.70	0.100 + 0.006 0.035 + 0.006 0.015 + 0.006 0.030 + 0.006
	10.00000 A	10μΑ	3Hz~5Hz 5Hz~10Hz 10Hz~5kHz 5kHz~10kHz	1.10+0.06 0.35+0.06 0.15+0.06 0.35+0.70	1.10+0.06 0.35+0.06 0.15+0.06 0.35+0.70	1.10+0.06 0.35+0.06 0.15+0.06 0.35+0.70	0.100 + 0.006 0.035 + 0.006 0.015 + 0.006 0.030 + 0.006
FREQUENCY (*8) PERIOD	100.0000 mV~ 750.000 V (*6)	-	3 Hz~5 Hz 5 Hz~10 Hz 10 Hz~40 Hz 40 Hz~300 kHz	0.1 0.05 0.03 0.006	0.1 0.05 0.03 0.01	0.1 0.05 0.03 0.01	0.005 0.005 0.001 0.001
TEMPERATURE(RTD)(*9)	-200 °C~600 °C	0.002°C	-	-	_	0.06°C (typical)	-
TEMPERATURE (THERMOCOUPLES)(*9)	-200 ~ +1372 °C -50 ~ +1870 °C	0.003°C 0.01°C	(J/K/N/T/E Type) (R/S/B Type)	-	-	0.2°C (typical) 1.0°C	0.004 °C / °C (typical) 0.14 °C / °C
DISPLAY	VFD, Two Colors Display						
INTERFACE	RS-232C, USB, Digital I/O						
POWER SOURCE	AC 100V/120V/220V/240V±10%, 45 Hz ~ 66 Hz and 360 Hz ~ 440 Hz						
DIMENSIONS & WEIGHT	265(W) x 107(H) x 350(D) mm, Approx. 3.1 kg						

ORDERING INFORMATION

GDM-8261A 6 ½ Digit Dual Measurement Multimeter

* Three-year warranty, excluding accessories.

ACCESSORIES

Quick star guide x 1, Power cord x 1, Test lead GTL-117 x 1, USB cable GTL-247 x 1, CD x 1 (including complete user manual, upgrade program and PC software DMM-Viewer), Calibration key GDM-01 x 1 (for firmware upgrade)

Specifications subject to change without notice.

OPTION

Opt. 01 GDM-SC1 Scanner Card (V ch x 16, I ch x 2)

Opt. 02 GPIB Card

Opt. 03 LAN Card * Either GPIB or LAN can be installed on each GDM-8261.

OPTIONAL ACCESSORIES

GTL-108A 4W Type test lead GTL-248 GPIB Cable, Approx. 2m

GTL-232 RS-232C Cable, 9-pin female to 9-pin, null modem for computer, Approx. 2m

FREE DOWNLOAD

PC Software DMM-VIEWER, RS-232C/USB Interface Supported

LabVIEW Driver, RS-232C/USB/GPIB Interface Supported

Driver USB Driver

Global Headquarters

GOOD WILL INSTRUMENT CO., LTD.

No.7-1, Jhongsing Road, Tucheng Dist., New Taipei City 236, Taiwan T +886-2-2268-0389 F +886-2-2268-0639 E-mail: marketing@goodwill.com.tw

China Subsidiary

GOOD WILL INSTRUMENT (SUZHOU) CO., LTD.

NO. 69, Lushan Road, Snd, Suzhou Jiangsu 215011 China T +86-512-6661-7177 F +86-512-6661-7277 E-mail: marketing@instek.com.cn

Malaysia Subsidiary

GOOD WILL INSTRUMENT (M) SDN. BHD.

27, Persiaran Mahsuri 1/1, Sunway Tunas, 11900 Bayan Lepas, Penang, Malaysia T +604-6309988 F +604-6309989 E-mail: sales@goodwill.com.my U.S.A. Subsidiary

INSTEK AMERICA CORP.

3661 Walnut Avenue Chino, CA 91710, U.S.A. T +1-909-5918358 F +1-909-5912280 E-mail: sales@instekamerica.com

Japan Subsidiary

INSTEK JAPAN CORPORATION

4F, Prosper Bldg, 1-3-3 Iwamoto-Cho Chiyoda-Ku, Tokyo 101-0032 Japan T+81-3-5823-5656 F+81-3-5823-5655 E-mail: info@instek.co.jp

Korea Subsidiary

GOOD WILL INSTRUMENT KOREA CO., LTD.

Room No.805, Ace Hightech-City B/D 1Dong, Mullae-Dong 3Ga 55-20, Yeongduengpo-Gu, Seoul, Korea T +82-2-3439-2205 F +82-2-3439-2207 E-mail: gwinstek@gwinstek.co.kr



DM-8261AGD1BH

www.gwinstek.com