
Heat Shrinkable Tubing 6:1, adhesive lined in 1.2 m cuts

HA67

Insulates, seals and protects large size differences between connectors and cables.

Features and benefits

- · High shrink ratio, heavy-duty heat shrinkable tubing
- · Thermoplastic adhesive-lined tubing
- Conforms well to highly variable substrate dimensions
- Simplifies cable repair
- Passes over large connectors and shrinks onto much smaller cable jackets
- Environmental sealing and excellent insulation
- Resistant to impact and abrasion




Due to the high shrink ratio HA67 is suitable for complex shapes and dimensions.

MATERIAL	Polyolefin, Chemically cross-linked (PO-X)				
Shrink Ratio	6:1				
Operating Temperature	-55 °C to +110 °C				
Min. Shrink Temperature	+120 °C				
Softening Point Adhesive	+85 °C				
Longitudinal Change After Shrinkage	-10% max.				
Dielectric Strength	20 kV/mm				
Flammability	not flame-retardant				







ТҮРЕ	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Length (L)	Colour	Tools	Article-No.
HA67-19.0/3.2	19.0	3.2	3.20	1.2 m	Black (BK)	32	321-30000
HA67-33.0/5.5	33.0	5.5	3.40	1.2 m	Black (BK)	32	321-30100
HA67-44.4/7.4	44.4	7.4	3.60	1.2 m	Black (BK)	32	321-30200
HA67-50.8/8.3	50.8	8.3	4.80	1.2 m	Black (BK)	32	321-30300
HA67-69.8/11.7	69.8	11.7	4.80	1.2 m	Black (BK)	32	321-30400
HA67-88.9/17.1	88.9	17.1	4.80	1.2 m	Black (BK)	32	321-30500
HA67-119.4/22.9	119.4	22.9	4.80	1.2 m	Black (BK)	32	321-30600

All dimensions in mm. Subject to technical changes. Minimum Order Quantity (MOQ) may differ from package content.

Recommended Tools			
	32		
	CHG900		
	565		

For more information on toolings please refer to the Application Tooling chapter.



