

KERN HCB 100K200

Handy hanging scale for higher loads

KERN



Category

Brand	KERN
Product category	Industrial scales
Product group	Hanging balances

Measuring System

Readability [d]	200 g
Weighing capacity [Max]	100 kg
Eccentric/Off-centre loading is not possible	✓
Tolerance (% of [Max])	0,5%
Reproducibility	0,2 kg
Linearity	± 0,4 kg
Weighing system	Strain gauge
Resolution	500
Units	kg lb N
Default unit	kg
Stabilization time	2 s
Warm-up time	10 min
Adjustment options	Adjusting with external weight
Recommended adjusting weight	50 kg (M3)
Possible calibration points	50 kg
Loadcell type	aluminium
Internal measuring frequency	5 Hz

Approval

CE mark	✓
---------	---

Display

Display digit height	12 mm
Languages of the user interface	Symbol language

Construction

Dimension housing (W×D×H)	82×43×153 mm
Dimensions housing - width (A)	82 mm
Dimensions housing - depth (B)	43 mm
Dimensions - total height/total length (D)	153 mm
Dimensions - inner length (E)	117 mm
Dimensions loop/top - hole diameter (F)	14 mm
Dimensions hook/bottom - hole diameter (G)	14 mm
Dimensions loop/top - thickness (H)	4 mm
Dimensions hook/bottom - thickness (I)	4 mm
Material housing	plastic
Material display housing	Plastics
Material load hook	stainless steel
Material load cell(s)	aluminium
Load cells - number	1

Functions

Number of keys for operation	3
Auto-off interval(s) in battery mode/rechargeable battery mode	off 4 min
Tare function	manual (multi)
Hold function	✓
Underfloor weighing	None
IP protection - load cell	no IP protection

Power Supply

Supplied plug-in power supply	Battery
Battery	3×1.5 V AA
Battery operating time	300 h

Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C

Packing & Shipping

Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	53×220×85 mm
Net weight approx.	0,30 kg
Gross weight approx.	0,90 kg

KERN HCB 100K200



Handy hanging scale for higher loads

Services (optional)

Article number for adjustment at the location of installation	961-249
Article number for DAkkS calibration	963-129H
Article number for certificate of conformity (verification)	969-517

Piktogramme

STANDARD



OPTION

