

PRODUCT-DETAILS

# VB7-30-01-01

## VB7-30-01-01 Mini Rev.Contactor 24V 40-450Hz



### General Information

Extended Product Type	VB7-30-01-01
Product ID	GJL1311901R0011
EAN	4013614191251
Catalog Description	VB7-30-01-01 Mini Rev.Contactor 24V 40-450Hz
Long Description	The VB7-30-01 mini reversing contactor is a compact 3 pole contactor with 1 auxiliary contact, screw terminals and normal mechanical interlock. They are ideally suited for applications where reliability is a must and space is at a premium. Mini reversing contactors are used in residential buildings, commercial buildings and industrial applications for the control of three-phase motor loads up to 5.5 kW (AC-3). Further features are the silent coil, a switch position indication and the integrated possibility for rail or wall mounting.

### Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080

### Popular Downloads

Data Sheet, Technical Information	1SBC100214C0201
Instructions and Manuals	2CDC102046M6801
Dimension Diagram	GJL1200447F0001

## Dimensions

Product Net Width	96.5 mm
Product Net Height	57.5 mm
Product Net Depth / Length	46.5 mm
Product Net Weight	0.355 kg

## Technical

Number of Poles	3
Rated Operational Voltage	Auxiliary Circuit 690 V AC Auxiliary Circuit 250 V DC Main Circuit 690 V AC Main Circuit 220 V DC
Rated Frequency (f)	Main Circuit 60 Hz Main Circuit 50 Hz Main Circuit DC
Rated Impulse Withstand Voltage ( $U_{imp}$ )	Main Circuit 6 kV
Rated Insulation Voltage ( $U_i$ )	690 V acc. to UL/CSA 600 V
Number of Main Contacts NC	0
Number of Main Contacts NO	3
Rated Operational Current AC-1 ( $I_e$ )	(220 / 240 V) 40 °C 20 A (220 / 240 V) 55 °C 16 A (380 / 440 V) 40 °C 20 A (380 / 440 V) 55 °C 16 A (690 V) 40 °C 6 A (690 V) 55 °C 6 A
Rated Operational Power AC-3 ( $P_e$ )	(230 V) Three Phase 3 kW (400 V) Three Phase 5.5 kW (500 V) Three Phase 5.5 kW (690 V) Three Phase, NO 3 kW
Rated Short-time Withstand Current ( $I_{cw}$ )	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 96 A
Number of Auxiliary Contacts NC	1
Number of Auxiliary Contacts NO	0
Conventional Free-air Thermal Current ( $I_{th}$ )	Main Circuit 20 A
Rated Control Circuit Voltage ( $U_c$ )	24 V AC
Coil Operating Limits	(acc. to IEC 60947-4-1) for AC supply 0.85 ... 1.1 x $U_c$ (at $\theta \leq 55$ °C)
Degree of Protection	Main Circuit Terminals IP20
Pollution Degree	3
Mechanical Durability	10000000 cycle
Minimum Switching Capacity	Auxiliary Circuit 17 V Auxiliary Circuit 5 mA
Maximum Electrical Switching Frequency	(AC-1) 300 cycles per hour (AC-15) 600 cycles per hour (AC-3) 600 cycles per hour (DC-1) 600 cycles per hour (DC-13) 600 cycles per hour (DC-3) 600 cycles per hour
Connecting Capacity Main Circuit	Flexible with Ferrule 1/2x 1 ... 2.5 mm <sup>2</sup> Flexible with Insulated Ferrule 1/2x 1 ... 2.5 mm <sup>2</sup> Flexible 1/2x 1 ... 2.5 mm <sup>2</sup> Rigid 1/2x 1 ... 4 mm <sup>2</sup>
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1/2x 1 ... 2.5 mm <sup>2</sup> Flexible with Insulated Ferrule 1/2x 1 ... 2.5 mm <sup>2</sup> Flexible 1/2x 1 ... 2.5 mm <sup>2</sup>

	Rigid 1/2x 1 ... 4 mm <sup>2</sup>
Connecting Capacity Control Circuit	Flexible with Ferrule 1/2x 1 ... 2.5 mm <sup>2</sup> Flexible with Insulated Ferrule 1/2x 1 ... 2.5 mm <sup>2</sup> Flexible 1/2x 1 ... 2.5 mm <sup>2</sup> Rigid 1/2x 1 ... 4 mm <sup>2</sup>
Wire Stripping Length	Auxiliary Circuit 9 mm Main Circuit 9 mm
Tightening Torque	Control Circuit 0.8 ... 1.1 N·m Main Circuit 0.8 ... 1.1 N·m
Mounting on DIN Rail	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Power Loss	at Rated Operating Conditions per Pole 2 W
Standards	IEC/EN 60947-1 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 60947-1 UL 60947-4-1

## Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 600 V AC
Full Load Amps Motor Use	(115 V AC) Single Phase 13.8 A (200 V AC) Three Phase 7.8 A (220 ... 240 V AC) Three Phase 9.6 A (230 V AC) Single Phase 10 A (440 ... 480 V AC) Three Phase 7.6 A (550 ... 600 V AC) Three Phase 6.1 A
Horsepower Rating UL/CSA	(115 V AC) Single Phase 0.75 Hp (200 V AC) Three Phase 2 Hp (220 ... 240 V AC) Three Phase 3 Hp (230 V AC) Single Phase 1.5 Hp (440 ... 480 V AC) Three Phase 5 Hp (550 ... 600 V AC) Three Phase 5 Hp
General Use Rating UL/CSA	(600 V AC) 16 A
Connecting Capacity Main Circuit UL/CSA	Stranded 1/2x 22-10 AWG
Connecting Capacity Auxiliary Circuit UL/CSA	Stranded 1/2x 22-10 AWG
Tightening Torque UL/CSA	Auxiliary Circuit 7 in-lb Control Circuit 7 in-lb Main Circuit 7 in-lb

## Environmental

Ambient Air Temperature	Operation -20 ... +55 °C Storage -40 ... +80 °C
Maximum Operating Altitude Permissible	2000 m
Resistance to Shock acc. to IEC 60068-2-27	11 ms Pulse 15g
Resistance to Vibrations acc. to IEC 60068-2-6	5g / 5 ... 150 Hz
RoHS Status	Following EU Directive 2011/65/EU

## Certificates and Declarations (Document Number)

CB Certificate	1SAA938000-2002
CQC Certificate	CQC2003010304064033
cULus Certificate	cUL_E191658
Declaration of Conformity - CCC	2020980304001854
Declaration of Conformity	1SAD938517-0001

- CE

Declaration of Conformity - UKCA	1SAD938500-1001
DNV GL Certificate	1SAA938000-0306
EAC Certificate	1SAA920000-2702
Environmental Information	1SAC200068H0009
Instructions and Manuals	2CDC102046M6801
KC Certificate	1SAA938000-1501
RMRS Certificate	1SAA938000-0704
RoHS Information	1SAD938517-0001

## Container Information

Package Level 1 Units	5 piece
Package Level 1 Width	115 mm
Package Level 1 Height	54 mm
Package Level 1 Depth / Length	280 mm
Package Level 1 Gross Weight	1.845 kg
Package Level 1 EAN	4013614417344

## Classifications

Object Classification Code	Q
ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 5	EC000010 - Starter combination
ETIM 6	EC000010 - Combination of contactors
ETIM 7	EC000010 - Combination of contactors
eClass	V11.0 : 27371009
UNSPSC	39121529

## Categories

Low Voltage Products and Systems → Control Products → Contactors → Mini Contactors

